

INTERCONNECTS

SERIES 301, 310, 350, 399 • .100" GRID (.018" DIA.) PINS, STRAIGHT AND RIGHT ANGLE • SINGLE ROW STRIPS




FIG. 1




FIG. 2




FIG. 3




FIG. 4





FIG. 5

- Series 3XX are available with straight and right angle solder tails
- Series 350 & 399...009 use MM #3404 and #5011 pins. See pages 212 & 214 for details
- Series 301, 310 & 399...003 use MM #0156, #1001 & #1103 receptacles. See pages 165 and 166 for details
- Receptacles use Hi-Rel, 4-finger #30 BeCu contact rated at 3 amps. See page 253 for details
- Insulators are high temperature thermoplastic, suitable for all soldering operations



ORDERING INFORMATION

FIG. 1	Series 350...006		Straight Pin Header	
	350-XX-1-00-006000 Specify number of pins 01-64			
FIG. 2	Series 399...009		Right Angle Pin Header	
	399-XX-1-10-009000 Specify number of pins 02-64			
RoHS-2 2011/65/EU XX=Plating Code See Below For Electrical, Mechanical & Environmental Data, See page 264				
SPECIFY PLATING CODE XX=				
10 90 40				
Pin Plating  10 μ" Au 200 μ" Sn/Pb 200 μ" Sn				
FIG. 3	Series 310...001		Solder Tail Socket	
	310-XX-1-41-001000 Specify number of pins 01-64			
FIG. 4	Series 301...056		Socket with Retention Pins	
	301-43-1-41-560000 Specify number of pins 03-64			
FIG. 5	Series 399...003		Right Angle Socket	
	399-XX-1-10-003000 Specify number of pins 02-64			
RoHS-2 2011/65/EU XX=Plating Code See Below For Electrical, Mechanical & Environmental Data, See page 264				
SPECIFY PLATING CODE XX=				
11 13 91 93 99 41 43 44 47				
Sleeve (Pin)  10 μ" Au 10 μ" Au 200 μ" Sn/Pb 200 μ" Sn/Pb 200 μ" Sn/Pb 200 μ" Sn 200 μ" Sn 200 μ" Sn 200 μ" Sn				
Contact (Clip)  10 μ" Au 30 μ" Au 10 μ" Au 30 μ" Au 100 μ" Sn/Pb 10 μ" Au 30 μ" Au 100 μ" Sn Au Flash				

★ 41, 91 & 99 Platings Non-Standard

