




REVISIONS			
REV	DESCRIPTION, ECN, EAR NO.	DATE	APP'D
A	PROPOSAL	25/01/06	L.CHAN
B	CORRECT DRAWING	MAY.9/14	



FRONT VIEW



SIDE VIEW



RECOMMENDED P.C.B. LAYOUT
(COMPONENT SIDE OF BOARD)

MATERIALS:

PLASTIC HOUSING: ENGINEERING THERMOPLASTIC
FLAMMABILITY RATING UL94V-0. COLOUR, BLACK.


CONTACTS:

PHOSPHOR BRONZE
PLATING: REFER TO PART NUMBER FOR GOLD
THICKNESS ON MATING SURFACES.
50 μ " [1.27 MICRONS]
MIN. NICKEL UNDERPLATE.
100 μ " [2.54 MICRONS]
MIN. MATTE-TIN OR GOLD FLASH
ON CONTACT TAILS.



AMPHENOL PART NUMBER: RJE05-188-0X10

GOLD PLATING
1 = 6 μ INCH
2 = 15 μ INCH
3 = 30 μ INCH
4 = 50 μ INCH



RECOMMENDED PANEL CUTOUT

UNLESS SPECIFIED OTHERWISE		DRAWN	CHIGOW	25/01/06	Amphenol Canada Corp. www.amphenolcanada.com	
PRIMARY UNITS	INCHES	CHECKED	L.CHAN	25/01/06		
SECONDARY	MILLIMETERS	M.E. APP'D			RJE05 SERIES MODULAR JACK, 8 POSITION, 8 CONTACTS, UNSHIELDED ULTRA LOW PROFILE - RoHS COMPLIANT	
REFERENCE IN PARENTHESES		Q.A. APP'D				
1 DECIMAL PLACE		DWG APP'D			DWG NO.	P-RJE05-188-0X10
2 DECIMAL PLACES		ENG. REL. NO.				
3 DECIMAL PLACES	±0.015	REF.			DO NOT SCALE DRAWING	REV B
ANGULAR DEGREES	±1.5°	THIRD ANGLE PROJECTION				
THIS DOCUMENT CONTAINS PROPRIETARY INFORMATION AND SUCH INFORMATION MAY NOT BE DISCLOSED TO OTHERS FOR ANY PURPOSE OR USED FOR MANUFACTURING PURPOSES WITHOUT WRITTEN PERMISSION FROM AMPHENOL CANADA CORP.		CODE ID NO.	03554	DWG SIZE	SCALE	SHEET 1 OF 1