

# SSR330DIN-DC22

Relay, SE Relays, solid state, SPST NO, 30A,  
0...60 VAC, 4...32 VDC U<sub>c</sub>, MOSFET, Dc  
switching, 22 mmm



## Main

Range	Legacy
Product Type	Solid state relay
Maximum output current	30 A
Mounting Support	Panel DIN rail
Network Number of Phases	1 phase
Output Voltage	0...60 V DC

## Complementary

Input Current Limits	11 mA at 32 V DC typical
Switch Function	SPST
Contacts Type and Composition	NO
Tightening Torque	0.6...0.7 N.m for input 0.6...0.7 N.m for output
Connections Terminals	Input screw AWG 10) Output screw AWG 10)
Local Signalling	For input status 1 LED (green)
Switching Voltage	4 V DC turn-on 1 V DC turn-off
Switching Device	Mosfet output DC switching
Maximum Peak Voltage	60 V
Surge Current	90 A 10 ms
Voltage Drop	<0.5 V on-state
Resistance	16 mOhm on-state
Leakage Current	0.1 mA at off-state
Response Time	1 ms (turn-on, turn-off)
Height	3.85 in (97.7 mm)
Width	0.88 in (22.4 mm)
Depth	3.15 in (80 mm)
Product Weight	9.88 oz (280 g)

## Environment

Product Certifications	CE
Ambient Air Temperature for Operation	-40...176 °F (-40...80 °C)
Ambient Air Temperature for Storage	-40...257 °F (-40...125 °C)

## Ordering and shipping details

GTIN	3606480282867
Nbr. of units in pkg.	1
Package weight(Lbs)	9.59 oz (272.0 g)


## Packing Units

Unit Type of Package 1	PCE
Package 1 Height	3.53 in (8.97 cm)
Package 1 width	0.88 in (2.24 cm)
Package 1 Length	3.85 in (9.77 cm)

## Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Nickel compounds, which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a>
REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	<a href="#">End Of Life Information</a>
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.

Approximate Dimensions



Connections and Wiring Diagrams

