


# Altech Corp.®

*Serving the Automation & Control Industry since 1984*



Quality  
Endorsed  
Company



Alligator Clips



Plunger Style  
Test Clips



Test Probes



Oscilloscope  
Probes



Test Jacks



Test Plugs



Sets



Measuring Leads


## Test & Measurement



# Test and Measurement

Since 1984, Altech Corporation has grown to become a leading supplier of automation and industrial control components. Headquartered in Flemington, NJ, Altech a supplier of electronic components has an experienced staff of engineering, manufacturing and sales personnel to provide the highest quality products with superior service. This is the Altech Commitment!

Our well trained technical experts welcome the opportunity to answer your technical questions and provide solutions to your automation and control needs. Give us a call or visit [www.altechcorp.com](http://www.altechcorp.com).



## Quality Commitment


Altech's control components meet diverse national and international standards such as UL, NEC, CSA, IEC, VDE and more. Altech provides superior customer service and delivery through Total Quality Management and Continuous Process Improvement. Altech is ISO 9001 approved. We perform these services with honesty and integrity and are committed to achieve these goals.









**Plunger Style Test Clips.....4**  
0.64 mm System .....5-7  
2 mm System .....7-8  
4 mm System .....8-10



**Measuring Leads.....26**  
0.64 mm System .....27  
2 mm System .....28  
4 mm System .....29-39




**Test Probes .....12**  
2 mm System .....13  
4 mm System .....14-17



**Test Plugs.....40**  
2 mm System .....41-42  
4 mm System .....43-53



**Oscilloscope Test Probes..18**  
High Frequency  
Measurement .....18-19



**Test Jacks .....54**  
2 mm System .....55-58  
4 mm System .....59-71




**Alligator Clips .....20**  
0.64 mm System .....21  
2 mm System .....22  
4 mm System .....23-25



**Sets**  
.....72-78

**Glossary.....80-81**  
**Index by Type No. ....82-83**  
**Index by Part No. ....84-85**  
**Terms & Conditions.....86**





## Plunger Style Test Clips



Altech Plunger Style Test clips are easy to work with Test & Measurement Tools. They can handle high voltages, allow accessing difficult to reach areas and keep your hands free for other tasks. The grabber can access every measurement point even on the smallest Device or PCB Board circuit. The KLEPS 2700 is patented and its stainless steel piercing tip allows access to the wire without stripping.

- Measuring “difficult to access” testing points
- Various designs for different applications
- Handle with multiple connection points
- Patented KLEPS 2700 with special design steel tip for accessing connected wire





# Plunger Style Test Clips

## 0.64 mm System



### Type

#### MICRO-KLEPS

Mini plunger style test probe with rotating pincers, insulated shaft bendable up to 35°, suitable for very thin wires and densely packed contact points, fits MKL and MAL leads.

Clamping range  
Clamp type

2 mm (0.079")  
Rotating Pincers

PART NO. / Housing color

973972100 ●  
973972101 ●



#### KLEPS 3 ST

Mini plunger style test probe with rotating pincers, suitable for very thin wires and densely packed contact points, fits MKL and MAL leads.

3.5 mm (0.138")  
Rotating Pincers

973592100 ●  
973592101 ●



### Technical Data

|                                 |                                   |
|---------------------------------|-----------------------------------|
| Connection Type                 | 2x pin Ø 0.64 mm                  |
| Voltage Rating                  | 30 VAC / 60 VDC                   |
| Measurement Category (IEC61010) | CAT I                             |
| Current Rating*                 | 2 A                               |
| Contact Resistance              | 10 mOhm                           |
| <b>Material Specifications</b>  |                                   |
| Pincers/ hook                   | tin plated spring steel           |
| Connection pin/ socket          | nickel plated brass               |
| Contact Spring                  | -                                 |
| Housing                         | PBT                               |
| <b>Environmental Conditions</b> |                                   |
| Temperature Range               | -25 °C to +100 °C (13°F to 212°F) |
| <b>Flamability Rating</b>       |                                   |
| Housing                         | UL 94 HB                          |

|                                 |                                   |
|---------------------------------|-----------------------------------|
| pin Ø 0.64 mm                   |                                   |
| 30 VAC / 60 VDC                 |                                   |
| CAT I                           |                                   |
| 2 A                             |                                   |
| 10 mOhm                         |                                   |
| <b>Material Specifications</b>  |                                   |
| tin plated spring steel         |                                   |
| nickel plated brass             |                                   |
| -                               |                                   |
| PBT                             |                                   |
| <b>Environmental Conditions</b> |                                   |
| Temperature Range               | -25 °C to +100 °C (13°F to 212°F) |
| <b>Flamability Rating</b>       |                                   |
| UL 94 HB                        |                                   |


### Drawing

Measurements are shown in millimeters.  
Multiply by 0.03937 to convert to inches.



\* Please consider derating graph on page 80.





# Plunger Style Test Clips

## 0.64 mm System



### KLEPS FP 2B

For connecting to QFPIC's 0.5-0.8mm lead pitch. Slim design allows to test QFPIC's with several clips simultaneously, delivered in pairs of 2.



### KLEPS 064 PCH

Compact design allows usage with very small components up to 1mm, fits MKL and MAL leads.

Clamping range  
Clamp type

0.5 - 0.8 mm (0,020" - 0.031")  
Micro grip jaws

PART NO. / Housing color

974101188 ● ●

1 mm (0.039")  
contact hook

974201100 ●  
974201101 ●  
974201102 ●  
974201103 ●  
974201104 ●  
974201106 ●  
974201107 ○



#### Technical Data

|                                 |                               |
|---------------------------------|-------------------------------|
| Connection Type                 | pin Ø0.73mm                   |
| Voltage Rating                  | 30 VAC / 60 VDC               |
| Measurement Category (IEC61010) | CAT I                         |
| Current Rating*                 | -                             |
| Contact Resistance              | -                             |
| <b>Material Specifications</b>  |                               |
| Pincers/ hook                   | nickel plated spring steel    |
| Connection pin/ socket          | -                             |
| Contact Spring                  | -                             |
| Housing                         | ABS                           |
| <b>Environmental Conditions</b> |                               |
| Temperature Range               | 0°C to +60 °C (32°F to 140°F) |
| <b>Flamability Rating</b>       |                               |
| Housing                         |                               |

|                               |
|-------------------------------|
| pin Ø0.64mm                   |
| 30 VAC / 60 VDC               |
| CAT I                         |
| -                             |
| -                             |
| gold plated copper-beryllium  |
| phosphor bronze               |
| -                             |
| -                             |
| 0°C to +70 °C (32°F to 158°F) |

#### Drawing

Measurements are shown in millimeters.  
Multiply by 0.03937 to convert to inches.



\* Please consider derating graph on page 80.



# Plunger Style Test Clips

## 0.64 mm/4mm System



### Type

#### KLEPS 2

Mini plunger style test probe with solder connection, gold plated phosphorus bronze contact hook for wires up to 2mm.

Clamping range  
Clamp type

2 mm (0.079")  
contact hook

PART NO. / Housing color

931467100 ●  
931467101 ●



#### KLEPS 2 BU

Mini plunger style test probe with 2mm socket terminals, gold plated phosphorus bronze contact hook for wires up to 2mm, gold plated contact spring.

2 mm (0.079")  
contact hook

973501100 ●  
973501101 ●

### Technical Data

|                                 |                 |
|---------------------------------|-----------------|
| Connection Type                 | Solder Terminal |
| Voltage Rating                  | 30 VAC / 60 VDC |
| Measurement Category (IEC61010) | CAT I           |
| Current Rating*                 | 6 A             |
| Contact Resistance              | 15 mOhm         |

### Material Specifications

|                        |                                |
|------------------------|--------------------------------|
| Pincers/ hook          | gold plated phosphorous bronze |
| Connection pin/ socket | -                              |
| Contact Spring         | -                              |
| Housing                | Polyamide                      |

### Environmental Conditions

Temperature Range -25 °C to +100 °C (13°F to 212°F)

### Flamability Rating

Housing UL 94 V-2

|                             |
|-----------------------------|
| Spring-loaded socket Ø 2 mm |
| 30 VAC / 60 VDC             |
| CAT I                       |
| 6 A                         |
| 15 mOhm                     |



|                                |
|--------------------------------|
| gold plated phosphorous bronze |
| -                              |
| gold plated copper-beryllium   |
| Polyamide                      |

-25 °C to +100 °C (13°F to 212°F)


UL 94 V-2

### Drawing

Measurements are shown in millimeters.  
Multiply by 0.03937 to convert to inches.



\* Please consider derating graph on page 80.



# Plunger Style Test Clips 2 mm/4mm System



## KLEPS 1600

Safety plunger style test probe with rotating pincers and flexible shaft. Special design of pincers allows clamping wires up to 4mm, 2mm gold plated brass socket terminal.



## KLEPS 30

Plunger style test probe with rotating pincers and flexible shaft. Special design of pincers allows clamping wires up to 4mm, 4mm brass socket and screw terminals.



## KLEPS 60

Plunger style test probe with rotating pincers and flexible shaft. Special design of pincers allows clamping wires up to 4mm, 4mm brass socket and screw terminals.

Clamping range  
Clamp type

3 mm (0.118")  
rotating pincers

4 mm (0.157")  
rotating pincers

4 mm (0.157")  
rotating pincers

PART NO. / Housing color

975106100 ●  
975106101 ●

930113100 ●  
930113101 ●




973053100 ●  
973053101 ●

### Technical Data

|                                 |                                  |                                  |                                  |
|---------------------------------|----------------------------------|----------------------------------|----------------------------------|
| Connection Type                 | Socket Ø2 mm                     | Socket Ø 4 mm, screw terminal    | Socket Ø 4 mm, screw terminal    |
| Voltage Rating                  | AC/DC 1000V                      | 30 VAC / 60 VDC                  | 30 VAC / 60 VDC                  |
| Measurement Category (IEC61010) | CAT III                          | CAT I                            | CAT I                            |
| Current Rating*                 | 3 A                              | 4 A                              | 4 A                              |
| Contact Resistance              | 50 mOhm                          | 50 mOhm                          | 50 mOhm                          |
| <b>Material Specifications</b>  |                                  |                                  |                                  |
| Pincers/ hook                   | nickel plated spring steel       | nickel plated spring steel       | nickel plated spring steel       |
| Connection pin/ socket          | gold plated brass                | brass                            | brass                            |
| Contact Spring                  | -                                | -                                | -                                |
| Housing                         | Polyamide                        | PF                               | PP, PS                           |
| <b>Environmental Conditions</b> |                                  |                                  |                                  |
| Temperature Range               | -25 °C to +70 °C (13°F to 158°F) | -25 °C to +80 °C (13°F to 176°F) | -25 °C to +60 °C (13°F to 140°F) |
| <b>Flamability Rating</b>       |                                  |                                  |                                  |
| Housing                         | UL 94 V-2                        | UL 94 V-0                        | UL 94 HB                         |

### Drawing

Measurements are shown in millimeters.  
Multiply by 0.03937 to convert to inches.



\* Please consider derating graph on page 80.

For the latest on Altech Test & Measurement specifications please visit [www.altechcorp.com/test-equipment](http://www.altechcorp.com/test-equipment)



# Plunger Style Test Clips 4mm System



## Type

### KLEPS 250

Touch proof plunger style test probe with rotating pincers and flexible shaft, allows to clamp wires up to 4mm, 4mm brass socket, fits MLN and MLB leads.

Clamping range  
Clamp type

4 mm (0.157")  
rotating pincers

PART NO. / Housing color

973528100 ●  
973528101 ●



### KLEPS 2600

Safety plunger style test probe with rotating pincers and flexible shaft, allows to clamp wires up to 4mm, 4mm brass socket.

4 mm (0.157")  
rotating pincers

972306100 ●  
972306101 ●



## Technical Data

|                                 |                                  |
|---------------------------------|----------------------------------|
| Connection Type                 | socket Ø 4 mm                    |
| Voltage Rating                  | 30 VAC / 60 VDC                  |
| Measurement Category (IEC61010) | CAT I                            |
| Current Rating*                 | 4 A                              |
| Contact Resistance              | 100 mOhm                         |
| <b>Material Specifications</b>  |                                  |
| Pincers/ hook                   | nickel plated spring steel       |
| Connection pin/ socket          | nickel plated brass              |
| Contact Spring                  | -                                |
| Housing                         | PF                               |
| <b>Environmental Conditions</b> |                                  |
| Temperature Range               | -25 °C to +80 °C (13°F to 176°F) |
| <b>Flamability Rating</b>       |                                  |
| Housing                         | UL 94 V-0                        |

|                                  |
|----------------------------------|
| socket Ø 4 mm                    |
| AC/DC 1000 V                     |
| CAT III                          |
| 4 A                              |
| 50 mOhm                          |
| nickel plated spring steel       |
| nickel plated brass              |
| -                                |
| PBT                              |
| -25 °C to +80 °C (13°F to 176°F) |
| UL 94 HB                         |

## Drawing

Measurements are shown in millimeters.  
Multiply by 0.03937 to convert to inches.




\* Please consider derating graph on page 80.



# Plunger Style Test Clips 4 mm Safety System



Type




**KLEPS 2700**

Safety plunger style test probe with spring loaded stainless steel tip, for wires up to 3.5mm, no stripping necessary, 4mm brass socket.



**KLEPS 2800**

Safety plunger style test probe with wide opening alligator clip, for wires and areas with large cross sections, fits safety measurement leads.



**KLEPS 2900**

Safety plunger style test probe with stationary contact hook, fits safety measurement leads.

Clamping range  
Clamp type

3.5 mm (0.138")  
spring-loaded stainless steel tip

10 mm (0.394")  
alligator clips

5.5 mm (0.217")  
contact hook

PART NO. / Housing color

**972307100** ●  
**972307101** ●

**972308100** ●  
**972308101** ●

**972309100** ●  
**972309101** ●

## Technical Data

Connection Type socket Ø 4 mm  
Voltage Rating AC/DC 1000 V  
Measurement Category (IEC61010) CAT III  
Current Rating\* 10 A  
Contact Resistance 100 mOhm

### Material Specifications

Pincers/ hook stainless steel  
Connection pin/ socket nickel plated brass  
Contact Spring -  
Housing PBT

### Environmental Conditions

Temperature Range -25 °C to +80 °C (13°F to 176°F)

### Flamability Rating

Housing UL 94 HB

socket Ø 4 mm  
AC/DC 1000 V  
CAT III  
20 A  
100 mOhm

nickel plated spring steel  
nickel plated brass  
-  
PBT

-25 °C to +80 °C (13°F to 176°F)

UL 94 HB

socket Ø 4 mm  
AC/DC 1000 V  
CAT III  
20 A  
50 mOhm




nickel plated brass  
nickel plated brass  
-  
PBT

-25 °C to +80 °C (13°F to 176°F)

UL 94 HB

## Drawing

Measurements are shown in millimeters.  
Multiply by 0.03937 to convert to inches.



\* Please consider derating graph on page 80.

For the latest on Altech Test & Measurement specifications please visit [www.altechcorp.com/test-equipment](http://www.altechcorp.com/test-equipment)



## Altech Digital Panel Meters



### Digital Multi Function Meters

MFM Series (Power, Energy, Voltage, Current, Frequency, Power Factor)  
VAF Series (Voltage, Current, Frequency)  
EM Series (Power, Energy)

### Digital Ampere Meters

MA12 Series (LED Display)  
MA Series (LCD Display)

### Digital Voltage Meters

MV15 Series (LED Series)  
MV Series (LCD Display)


### Digital Frequency Meter

MF16 Series

### Digital Power Factor Meter

MP14 Series




**Disconnect and Test Terminal Block**  
For Meter Circuits



## Test Probes

Altech offers the proper test probe for every specific application. Due to small dimensions in electronic devices, test probes need to be very precise. The Test probes on the following pages meet these high standards.

- Slim and compact body for easy access
- Stainless steel tips
- Spring-loaded tips guarantee contact without damaging test object
- Suitable for testing through oxidation and insulation layers





# Test Probes 2 mm System



## Type

### MICRO-PRUEF MPS 2 0,64 FT

Miniature test probe with spring loaded stainless steel probe tip for sampling extremely small measuring points and SMD components. Because the probe tip is sprung, it cannot slip off and provides constant pressure. Connects with MKL 0.64/25-0.25 and MAL N 4-0.64/100-0.25.

Tip diameter

0.75 mm (0.029 in.)

PART NO. / Housing color

973995100 ●  
973995101 ●



### PRUEF 1

Miniature test probe for sampling extremely small measuring points. Shatter-proof grip, may be unscrewed. The stainless steel tip easily penetrates insulation and oxide layers. Solder connection up to 0.5 mm<sup>2</sup>.

1 mm (0.039 in.)

931376100 ●  
931376101 ●

## Technical Data

Connection Type spring-loaded tip  
Voltage Rating fixed pin Ø 0.64 mm  
Measurement Category (IEC61010) 30 VAC / 60 VDC  
Current Rating\* CAT I  
Contact Resistance 1 A

## Material Specifications

Tip stainless steel  
Connection pin/ socket nickel plated brass  
Contact Spring –  
Housing PBT

## Environmental Conditions

Temperature range -25 °C to +80 °C (13°F to 176°F)

## Flamability Rating

Housing UL 94 HB



stationary tip  
solder connection up to 0.5 mm<sup>2</sup>  
30 VAC / 60 VDC  
CAT I  
1 A

stainless steel  
nickel plated brass  
–  
PVC-P


-25 °C to +60 °C (13°F to 140°F)

## Drawing

Measurements are shown in millimeters.  
Multiply by 0.03937 to convert to inches.



\* Please consider derating graph on page 80.



# Test Probes 2 mm System



## Type

### MPS 1

Miniature test probe for sampling very small measuring points. The stainless steel tip easily penetrates insulation and oxide layers. Socket connection through a 2 mm diameter gold-plated socket with contact spring.

Tip diameter 1 mm (0.039 in.)

PART NO. / Housing color

973531100 ●  
973531101 ●



### PRUEF 1610 FT Au

Safety test probe with shatter-proof insulated sleeve, spring-loaded and slender stainless steel tip. 2 mm diameter gold-plated brass socket connection, stackable with 2 mm safety measuring lead MVL S WS. Insulation and oxide layers can be penetrated by this test probe.

0.75 mm (0.029 in.)

975018700 ●  
975018701 ●



### PRUEF 1600 Au

Safety test probe with shatter-proof insulated sleeve and slender stainless steel tip. 2 mm diameter gold-plated brass socket connection, stackable with 2 mm safety measuring lead MVL S WS. Insulation and oxide layers can be penetrated by this test probe.

1.4 mm (0.055 in.)

975017700 ●  
975017701 ●

## Technical Data




|                                 |                                  |
|---------------------------------|----------------------------------|
| Connection Type                 | stationary tip                   |
| Voltage Rating                  | spring-loaded socket Ø 2 mm      |
| Measurement Category (IEC61010) | 30 VAC / 60 VDC                  |
| Current Rating*                 | CAT I                            |
| Contact Resistance              | 1 A                              |
| <b>Material Specifications</b>  | 100 mOhm                         |
| Tip                             | stainless steel                  |
| Connection pin/ socket          | gold plated copper-beryllium     |
| Contact Spring                  | -                                |
| Housing                         | PE                               |
| <b>Environmental Conditions</b> |                                  |
| Temperature range               | -25 °C to +60 °C (13°F to 140°F) |
| <b>Flamability Rating</b>       |                                  |
| Housing                         | -                                |

|                                 |                                |
|---------------------------------|--------------------------------|
| Connection Type                 | spring-loaded tip              |
| Voltage Rating                  | fixed socket Ø 2mm             |
| Measurement Category (IEC61010) | AC/DC 1000V                    |
| Current Rating*                 | CAT II                         |
| Contact Resistance              | 10 A                           |
| Contact Resistance              | 20 mOhm                        |
| Tip                             | stainless steel                |
| Connection pin/ socket          | gold plated copper-beryllium   |
| Contact Spring                  | -                              |
| Housing                         | PA                             |
| <b>Environmental Conditions</b> |                                |
| Temperature range               | -25°C to +70°C (13°F to 158°F) |
| <b>Flamability Rating</b>       |                                |
| Housing                         | UL 94 V-2                      |

|                                 |                                |
|---------------------------------|--------------------------------|
| Connection Type                 | stationary tip                 |
| Voltage Rating                  | fixed socket Ø 2 mm            |
| Measurement Category (IEC61010) | AC/DC 1000V                    |
| Current Rating*                 | CAT III                        |
| Contact Resistance              | 10 A                           |
| Contact Resistance              | 20 mOhm                        |
| Tip                             | stainless steel                |
| Connection pin/ socket          | gold plated brass              |
| Contact Spring                  | -                              |
| Housing                         | PA                             |
| <b>Environmental Conditions</b> |                                |
| Temperature range               | -25°C to +70°C (13°F to 158°F) |
| <b>Flamability Rating</b>       |                                |
| Housing                         | UL 94 V-2                      |

## Drawing

Measurements are shown in millimeters.  
Multiply by 0.03937 to convert to inches.



\* Please consider derating graph on page 80.



# Test Probes 4 mm System



## Type

### MZS 1 - PRUEF

Needle-shaped, long stainless steel test probe with shatter-proof insulated sleeve and unsprung 4 mm connecting socket. During state of connection or operation of test leads, it is possible to measure with the test probe from the back side of the closed connector.

Tip diameter

1 mm (0.039 in.)

PART NO. / Housing color

973601100 ●  
973601101 ●



### PRUEF 2

Test probe with shatter-proof insulated sleeve. Insulation and oxide layers can be penetrated by the slender stainless steel tip. 4 mm diameter brass socket connection. Accessory (optional): tip protector / IC tap SS 260

2 mm (0.079 in.)

973368100 ●  
973368101 ●



## Technical Data

|                                 |                                 |
|---------------------------------|---------------------------------|
| Connection Type                 | stationary tip                  |
| Voltage Rating                  | fixed socket Ø 4 mm             |
| Measurement Category (IEC61010) | 30 VAC / 60 VDC                 |
| Current Rating*                 | CAT I                           |
| Contact Resistance              | 1 A                             |
| <b>Material Specifications</b>  | 50 mOhm                         |
| Tip                             | stainless steel                 |
| Connection pin/ socket          | nickel plated brass             |
| Contact Spring                  | -                               |
| Housing                         | PP                              |
| <b>Environmental Conditions</b> |                                 |
| Temperature range               | -20°C to + 60°C (-4°F to 140°F) |
| <b>Flamability Rating</b>       |                                 |
| Housing                         | UL 94 HB                        |


|                                  |
|----------------------------------|
| stationary tip                   |
| fixed socket Ø 4 mm              |
| 30 VAC / 60 VDC                  |
| CAT I                            |
| 1 A                              |
| 50 mOhm                          |
| stainless steel                  |
| nickel plated brass              |
| -                                |
| PP                               |
| -25 °C to +80 °C (13°F to 176°F) |
| UL 94 HB                         |

## Drawing

Measurements are shown in millimeters.  
Multiply by 0.03937 to convert to inches.



\* Please consider derating graph on page 80.



# Test Probes

## 4 mm Safety System



CE



CE

### Type

#### PRUEF 2600 C2

Test probe shatter - proof insulating sleeve and slender stainless steel tip. Tip for penetration of insulation and oxide layers. 4mm diameter brass socket connection. Connection with safety measuring leads. Accessory (optional): protector and IC - tap SS 260

Tip diameter 2 mm (0.079 in.)

**PART NO. / Housing color**  
**972327100** ●  
**972327101** ●

#### SS 260

Tip protection and IC tap. Clipping onto the PRUEF 2, PRUEF 2 S and PRUEF 2600 C2 test probe covers the needle tip and provides protection against injury. Contact is made with ICs without short circuiting or slipping off.

—  
**973865001** ○

#### PRUEF 2610 FT

Test probe with insulated sleeve and slender, sprung stainless steel tip. This allows a constant pressure to be applied without the tip slipping off the component, even in the smallest measuring points. 4 mm diameter brass socket connection.

0.75 mm (0.029 in.)

**972318100** ●  
**972318101** ●

### Technical Data

Connection Type stationary tip  
 Voltage Rating fixed socket Ø 4 mm  
 Measurement Category (IEC61010) AC/DC 1000V  
 Current Rating\* CAT II  
 Contact Resistance 1 A

**Material Specifications**  
 Tip 50 mOhm  
 stainless steel  
 Connection pin/ socket nickel plated brass  
 Contact Spring —  
 Housing PP




**Environmental Conditions**  
 Temperature range -20°C to +60°C (-4°F to 140°F)  
**Flamability Rating**  
 Housing UL 94 HB

—  
—  
—  
—  
—  
—  
—  
—  
—  
—  
—  
—

spring-loaded tip  
 fixed socket Ø 4 mm  
 AC/DC 1000 V  
 CAT II  
 1 A  
 50 mOhm  
 stainless steel  
 nickel plated brass  
 —  
 PP  
 -25 °C to +80 °C (13°F to 176°F)  
 UL 94 HB

### Drawing

Measurements are shown in millimeters.  
 Multiply by 0.03937 to convert to inches.



\* Please consider derating graph on page 80.

# Test Probes 4 mm Safety System



## Type

### PRUEF 2700

Safety test probe with dual function. Tip for penetrating insulation and oxide layers and 4 mm diameter pin for insertion in sockets. 4 mm diameter brass socket connection. Connects with safety measuring leads.

Tip diameter

4 mm (0.157 in.)

PART NO. / Housing color

972319100 ●  
972319101 ●



### PRUEF 2600

Test probe with elastic, shatter-proof insulated sleeve and slender stainless steel tip. Tip for penetration of insulation and oxide layers. 4 mm diameter brass socket connection. Connects with safety measuring leads. Accessory tip protector and IC tap SS 260.

2 mm (0.78 in.)

972317100 ●  
972317101 ●



## Technical Data

|                                 |                                  |
|---------------------------------|----------------------------------|
| Connection Type                 | stationary tip                   |
| Voltage Rating                  | fixed socket Ø 4 mm              |
| Measurement Category (IEC61010) | AC/DC 1000 V                     |
| Current Rating*                 | CAT II                           |
| Contact Resistance              | 32 A                             |
| <b>Material Specifications</b>  | 2 mOhm                           |
| Tip                             | nickel plated brass              |
| Connection pin/ socket          | nickel plated brass              |
| Contact Spring                  | -                                |
| Housing                         | PP                               |
| <b>Environmental Conditions</b> |                                  |
| Temperature range               | -25 °C to +80 °C (13°F to 176°F) |
| <b>Flamability Rating</b>       |                                  |
| Housing                         | UL 94 HB                         |

|                                  |
|----------------------------------|
| stationary tip                   |
| fixed socket Ø 4 mm              |
| AC/DC 1000 V                     |
| CAT III                          |
| 1 A                              |
| 50 mOhm                          |
| stainless steel                  |
| nickel plated brass              |
| -                                |
| PP                               |
| -25 °C to +80 °C (13°F to 176°F) |
| UL 94 HB                         |

## Drawing

Measurements are shown in millimeters.  
Multiply by 0.03937 to convert to inches.



\* Please consider derating graph on page 80.







# Oscilloscope Test Probes

## High Frequency Measurement

Altech High Frequency Test Probes are for direct connection to oscilloscopes. The line consists of a standard 5mm series with adjustable probe ratio and 2.5mm series with fixed 10:1 ratio.

- 10:1 probe ratio
- Exchangable spring tip
- Low Input Capacitance



### Type

### TKO 5 - PMS 221A

Passive High Impedance Miniature Test Probe with 150 MHz Bandwidth and Probe Ratio 10:1 (Switchable, 20 MHz @ Probe Ratio 1:1). The probe is adjustable for low frequencies.

#### Features:

- Modular Probe
- Coaxial Design
- Coaxial Reed Switch
- New IC contact system for 0.003" to 0.004" grids
- Interchangeable Spring Contact Tip for reliable Contacting

### PART NO.


974312000

#### Technical Data

|                      |                   |                  |
|----------------------|-------------------|------------------|
| Probe Ratio          | 1:1               | 10:1             |
| Input Resistance     | -                 | 10 MΩ            |
| Input Capacitance    | 78 pF inkl. Oszi. | 13 pF            |
| Oscilloscope Input   | 1 MΩ AC/DC        | 1 MΩ AC/DC       |
| Probe bandwidth      | 20 MHz            | 150 MHz          |
| Risetime             | 18 nsec           | 2,4 nsec         |
| Compensation Range   |                   | 15 ... 40 pF     |
| Measurement category | 55 V eff. CAT II  | 300 V rms CAT II |
| Pollution degree     | 2                 | 2                |
| Safety standard      | IEC 61010-031     |                  |
| Cable length         | 1.2 m (3.94 ft.)  |                  |

#### Drawing

Measurements are shown in millimeters. Multiply by 0.03937 to convert to inches.



#### Contents



- Test Probe
- Manual
- Ground Lead 0.22m (0.72")
- Spring Tip 0.8mm (0.003")
- Solid Tip CuBe 0.8mm (0.003")
- Ground Blade 5.0mm (0.016")
- Isolation Cover 5.0mm (0.016")
- Protection Cover 5.0mm (0.016")
- IC covers 0.8 to 1.27mm (0.003-0.004")
- Spring Hook 5.0mm (0.016")
- Adjustment Tool T

# Oscilloscope Test Probes

## High Frequency Measurement



### Type

#### TKO 2,5 - PML 711A

Passive High Impedance Miniature Test Probe with 500 MHz Bandwidth and Probe Ratio 10:1. Designed for Oscilloscopes having 1MOhm Input resistance.

#### Features:

- Compact Size (0.008" probe tip) ideal for measuring SMD Components
- 0.002" gold plated spring loaded changeable Probe tip
- Innovative IC contact system for 0.002" to 0.004" grids
- With ReadOut (RO)

### PART NO.

974301000



#### TKO 5 - PMT 221A

Passive High Impedance Miniature Test Probe with 250 MHz Bandwidth and Probe Ratio 10:1 (Switchable, 30 MHz @ Probe Ratio 1:1). The probe is adjustable for low frequencies.

#### Features:

- Modular Probe
- Coaxial Design
- Coaxial Reed Switch
- Innovative IC contact system for 0.003" to 0.004" grids
- Interchangeable Spring Contact Tip for reliable Contacting
- HF- Adjustment

### PART NO.

974311000



### Technical Data

|                       |                    |
|-----------------------|--------------------|
| Probe Ratio           | 10:1               |
| Input Impedence       | 10 M $\Omega$      |
| Input Capacitence     | 9,5 pF             |
| Oscilloscope Input    | 1 M $\Omega$ AC/DC |
| Probe bandwidth (3dB) | 500 MHz            |
| Risetime (10% - 90%)  | 700 psec           |
| Compensation Range    | 10 ... 25 pF       |
| Measurement category  | 300 V CAT II       |
| Pollution degree      | 2                  |
| Safety standard       | IEC 61010-031      |
| Cable length          | 1.3 m (4.27 ft.)   |

|                    |                    |
|--------------------|--------------------|
| 1:1                | 10:1               |
| -                  | 10 M $\Omega$      |
| 80 pF inkl. Oszi.  | 13 pF              |
| 1 M $\Omega$ AC/DC | 1 M $\Omega$ AC/DC |
| 30 MHz             | 250 MHz            |
| 12 nsec            | 1,4 nsec           |
| -                  | 10...35 pF (**)    |
| 55 V eff. CAT II   | 300 V rms CAT II   |
| 2                  | 2                  |
| IEC 61010-031      |                    |
| 1.2 m (3.94 ft.)   |                    |

### Drawing

Measurements are shown in millimeters. Multiply by 0.03937 to convert to inches.



### Contents



- Test Probe
- Manual
- Spring Tip gold plated 0.5mm (0.002")
- Solid Tip CuBe 0.5mm (0.002")
- Coding Rings (3x4 colors)
- Ground Lead 0.11m (0.36")
- Ground Blade 2.5mm (0.008")
- 2 self adhesive Cu Pads
- Isolation Cover 2.5mm (0.008")
- Protection Cover 2.5mm (0.008")
- IC covers 0.5 to 1.27mm (0.002-0.004")
- Spring Hook 2.5mm (0.008")
- Ground Spring 2.5mm (0.008")
- PCB Adapter Kit 2.5mm (0.008")
- 2 Foot Positioner
- Adjustment Tool T

- Test Probe
- Manual
- Ground Lead 0.22m (0.72")
- Spring Tip 0.8mm (0.003")
- Solid Tip CuBe 0.8mm (0.003")
- Ground Blade 5.0mm (0.016")
- Isolation Cover 5.0mm (0.016")
- Protection Cover 5.0mm (0.016")
- IC covers 0.8 to 1.27mm (0.003-0.004")
- Spring Hook 5.0mm (0.016")
- BNC Adapter 5.0mm (0.016")
- 2 Foot Positioner
- Adjustment Tool T





## Alligator Clips

Altech Alligator clips have the proper jaw opening and grabbing strength for every application. From a Micro SMD clip for measuring smallest surface-mount components up to a 30mm (1.18in) “big mouth” a wide range of alligator clips is available.


- Various clamping ranges
- Stainless steel versions for use in galvanic and acid environments
- Soldering connections for “do it yourself” connections



“Big Mouth” AK 2B 2540 1 with wide pin opening is especially suitable for cars.



Special solution for very small SMD components  
MICRO-SMD CLIP 1.





# Alligator Clips

## 0.64 and 2 mm System



### Type

#### MICRO-SMD CLIP 1

Spring loaded 2 pole test clip designed for MSD components; gold plated, hardened tip; flat nose for testing individual components; insulated spring, 0.64mm connection pin terminal.

Clamping range

0 mm to 8 mm (0.31")

PART NO. / Housing color

972416100 ●



#### AGF 1

Mini alligator clip for small components, silver plated, solder/ crimp terminal max. 0.5mm<sup>2</sup>.

1 mm (0.04")

930476001 ●

### Technical Data

|                                 |                 |
|---------------------------------|-----------------|
| Contact Type                    | alligator clip  |
| Connection Type                 | 2x pin 0.64 mm  |
| Voltage Rating                  | 30 VAC / 60 VDC |
| Measurement Category (IEC61010) | CAT I           |
| Current Rating*                 | 1 A             |
| Contact Resistance              | 6 mOhm          |

#### Material Specifications

|                |                              |
|----------------|------------------------------|
| Alligator Clip | gold plated copper beryllium |
| Housing        | PBT                          |

#### Environmental Conditions

|                   |                                   |
|-------------------|-----------------------------------|
| Temperature Range | -30 °C to +100 °C (22°F to 212°F) |
|-------------------|-----------------------------------|

#### Flamability Rating

|         |          |
|---------|----------|
| Housing | UL 94 HB |
|---------|----------|

|                                  |
|----------------------------------|
| alligator clip                   |
| solder, crimp 0.5mm <sup>2</sup> |
| 30 VAC / 60 VDC                  |
| CAT I                            |
| 3 A                              |
| 15 mOhm                          |



|                     |
|---------------------|
| silver plated brass |
| —                   |

|                                  |
|----------------------------------|
| -25°C to +100 °C (13°F to 212°F) |
|----------------------------------|

|   |
|---|
| — |
|---|

### Drawing

Measurements are shown in millimeters.  
Multiply by 0.03937 to convert to inches.



\* Please consider derating graph on page 80.



# Alligator Clips 2 mm System



## Type

### MA 1 Crimp

Mini Alligator Clip, high-strength insulation, nickel plated brass/ bronze jaws, crimp terminal 0.25mm 2-0.5mm<sup>2</sup> for suitable crimp tool insert.

### MA 1

Mini Alligator Clip, high-strength insulation, nickel plated brass/ bronze jaws, 2mm system socket terminal.

### MA 1 S

Mini Alligator Clip, high-strength insulation, stainless steel spring, nickel plated brass/ bronze jaws, 2mm system socket terminal.

Clamping range

4 mm (0.16")

PART NO. / Housing color

930318100 ● 930318104 ●  
930318101 ● 930318106 ●  
930318102 ● 930318107 ○  
930318103 ●

4 mm (0.16")

930317800 ● 930317804 ●  
930317801 ● 930317806 ●  
930317802 ● 930317807 ○  
930317803 ●

4 mm (0.16")

973584100 ● 973584104 ●  
973584101 ● 973584106 ●  
973584102 ● 973584107 ○  
973584103 ●

## Technical Data

Contact Type alligator clip  
Connection Type crimp 0.25 mm<sup>2</sup> up to 0.5 mm<sup>2</sup>  
Voltage Rating 30 VAC / 60 VDC  
Measurement Category (IEC61010) CAT I  
Current Rating\* 8 A  
Contact Resistance 5 mOhm

### Material Specifications

Alligator Clip nickel plated brass / bronze  
Housing PP

### Environmental Conditions

Temperature Range -25°C to +100 °C (13°F to 212°F)

### Flamability Rating

Housing UL 94 HB

Contact Type alligator clip  
Connection Type spring-loaded socket Ø 2 mm  
Voltage Rating 30 VAC / 60 VDC  
Measurement Category (IEC61010) CAT I  
Current Rating\* 8 A  
Contact Resistance 5 mOhm

Alligator Clip nickel plated brass / bronze  
Housing PP

Temperature Range -25°C to +100 °C (13°F to 212°F)

Housing UL 94 HB

Contact Type alligator clip  
Connection Type spring-loaded socket Ø 2 mm  
Voltage Rating 30 VAC / 60 VDC  
Measurement Category (IEC61010) CAT I  
Current Rating\* 8 A  
Contact Resistance 5 mOhm




Alligator Clip tin plated brass / bronze  
Housing PP

Temperature Range -25°C to +100 °C (13°F to 212°F)

Housing UL 94 HB

## Drawing

Measurements are shown in millimeters.  
Multiply by 0.03937 to convert to inches.



\* Please consider derating graph on page 80.

# Alligator Clips 4 mm System



## Type

### AGF 2

Extra small Alligator Clip, for extremely small dense contact points, jaws insulated on the outside, 2mm and 4mm system socket terminal.

Clamping range

4 mm (0.16")

PART NO. / Housing color

**931272100** ●  
**931272101** ●



### AGF 20

Steel Alligator Clip, nickel plated, max, jaw opening 12mm, 4mm system socket and solder terminal.

12 mm (0.47")

**930120000**



### AGF 30

Stainless Steel Alligator Clip, max, jaw opening 10mm, 4mm system socket and solder terminal.

10 mm (0.40")

**930122000**

## Technical Data




|                                 |                                 |
|---------------------------------|---------------------------------|
| Contact Type                    | alligator clip                  |
| Connection Type                 | socket Ø 4mm and Ø 2mm          |
| Voltage Rating                  | 30 VAC / 60 VDC                 |
| Measurement Category (IEC61010) | CAT I                           |
| Current Rating*                 | 6 A                             |
| Contact Resistance              | 300 mOhm                        |
| <b>Material Specifications</b>  |                                 |
| Alligator Clip                  | stainless steel                 |
| Housing                         | PVC-P                           |
| <b>Environmental Conditions</b> |                                 |
| Temperature Range               | -25°C to +80 °C (13°F to 176°F) |
| <b>Flamability Rating</b>       |                                 |
| Housing                         | —                               |

|                                 |                                  |
|---------------------------------|----------------------------------|
| Contact Type                    | alligator clip                   |
| Connection Type                 | socket Ø 4 mm, solder terminal   |
| Voltage Rating                  | 30 VAC / 60 VDC                  |
| Measurement Category (IEC61010) | CAT I                            |
| Current Rating*                 | 4 A                              |
| Contact Resistance              | 15 mOhm                          |
| <b>Material Specifications</b>  |                                  |
| Alligator Clip                  | nickel plated steel              |
| Housing                         | —                                |
| <b>Environmental Conditions</b> |                                  |
| Temperature Range               | -25°C to +100 °C (13°F to 212°F) |
| <b>Flamability Rating</b>       |                                  |
| Housing                         | —                                |

|                                 |                                  |
|---------------------------------|----------------------------------|
| Contact Type                    | alligator clip                   |
| Connection Type                 | socket Ø 4 mm, solder terminal   |
| Voltage Rating                  | 30 VAC / 60 VDC                  |
| Measurement Category (IEC61010) | CAT I                            |
| Current Rating*                 | 4 A                              |
| Contact Resistance              | 15 mOhm                          |
| <b>Material Specifications</b>  |                                  |
| Alligator Clip                  | stainless steel                  |
| Housing                         | —                                |
| <b>Environmental Conditions</b> |                                  |
| Temperature Range               | -25°C to +100 °C (13°F to 212°F) |
| <b>Flamability Rating</b>       |                                  |
| Housing                         | —                                |

## Drawing

Measurements are shown in millimeters.  
Multiply by 0.03937 to convert to inches.



\* Please consider derating graph on page 80.





# Alligator Clips 4 mm System



## Type

### AGS 20

Steel Alligator Clip, nickel plated, max. jaw opening mm, 4mm system socket and solder/ screw terminal.

### AK 10

Insulated Alligator Clip, tin plated brass insert, suitable for very thin wires, 4mm system socket terminal.

### AK 2 S

High Strength Alligator Clip, insulated, nickel plated brass, 4mm system socket and screw terminal max. 1.5mm<sup>2</sup>.

Clamping range

5 mm (0.20")

6 mm (0.24")

9.5 mm (0.37")

PART NO. / Housing color

603006001

930126100 ●  
930126101 ●  
930126102 ●  
930126103 ●  
930126104 ●

932146100 ●  
932146101 ●

## Technical Data

Contact Type alligator clip  
Connection Type socket Ø 4 mm, solder screw terminal  
Voltage Rating 30 VAC / 60 VDC  
Measurement Category (IEC61010) CAT I  
Current Rating\* 4 A  
Contact Resistance 10 mOhm

### Material Specifications

Alligator Clip nickel plated steel  
Housing -

### Environmental Conditions

Temperature Range -25°C to +100 °C (13°F to 212°F)

### Flamability Rating

Housing -

Contact Type alligator clip  
Connection Type socket Ø 4 mm  
Voltage Rating 30 VAC / 60 VDC  
Measurement Category CAT I  
Current Rating 6 A  
Contact Resistance 15 mOhm

tin plated brass  
PS

-25°C to +100 °C (13°F to 212°F)

UL 94 HB

Contact Type alligator clip  
Connection Type socket Ø 4 mm, screw terminal  
Voltage Rating 30 VAC / 60 VDC  
Measurement Category CAT I  
Current Rating 25 A  
Contact Resistance 10 mOhm




nickel plated brass  
PP

-25°C to +80 °C (13°F to 176°F)

UL 94 HB

## Drawing

Measurements are shown in millimeters.  
Multiply by 0.03937 to convert to inches.



\* Please consider derating graph on page 80.

# Alligator Clips 4 mm System



CE



CE



CE

## Type

### MA 260 SH

Touch proof mini Alligator Clip, nickel plated bronze, jaw opening 6mm, 4mm system socket and solder terminal.

### AK 2 B

High Strength Alligator Clip, touch proof, nickel plated brass, 9.5mm jaw opening, 4mm system socket terminal.

### AK 2 B 2540 I

High Strength wide opening Alligator Clip, touch proof, nickel plated brass, 30mm jaw opening, 4mm system socket terminal.

Clamping range

6 mm (0.24")

9.5 mm (0.37")

30 mm (1.18")

PART NO. / Housing color

973889100 ●  
973889101 ●

932435100 ●  
932435101 ●

972405100 ●  
972405101 ●  
972405102 ●  
972405103 ●  
972405104 ●  
972405188 ●

## Technical Data

Contact Type alligator clip  
Connection Type socket Ø 4 mm, solder terminal  
Voltage Rating AC/DC 300 V  
Measurement Category (IEC61010) CAT II  
Current Rating\* 15 A  
Contact Resistance 5 mOhm

### Material Specifications

Alligator Clip nickel plated bronze  
Housing PA

### Environmental Conditions

Temperature Range -25°C to +80 °C (13°F to 176°F)

### Flamability Rating

Housing UL 94 HB

Contact Type alligator clip  
Connection Type socket Ø 4 mm  
Voltage Rating AC/DC 300 V  
Measurement Category (IEC61010) CAT II  
Current Rating\* 25 A  
Contact Resistance 10 mOhm

Alligator Clip nickel plated brass  
Housing PP

Temperature Range -25°C to +80 °C (13°F to 176°F)

Housing UL 94 HB

Contact Type alligator clip  
Connection Type socket Ø 4 mm  
Voltage Rating AC/DC 1000 V  
Measurement Category (IEC61010) CAT II  
Current Rating\* 32 A  
Contact Resistance 10 mOhm




Alligator Clip nickel plated brass  
Housing PP

Temperature Range -30°C to +90 °C (22°F to 194°F)

Housing UL 94 HB

## Drawing

Measurements are shown in millimeters.  
Multiply by 0.03937 to convert to inches.





\* Please consider derating graph on page 80.



## Measuring Leads

Altech Test & Measurement Leads are often exposed to extensive wear and tear and other extreme conditions. They must be robust, flexible, carry heavy loads and long lasting. Therefore they are manufactured in a closely monitored process with high quality materials.

- Wide variety of colors, length and connections
- Double insulation
- Highly flexible also at low temperatures
- Silicone version for solder resistance
- Built-in white color indicator for damage identification
- Up to 1000V CAT III
- Wire size up to 2.5mm<sup>2</sup> for 32A
- Safety Systems
- Nickel and Gold plating





# Measuring Leads 0.64 mm System



## Type

### BNC AL 0,64

BNC adapter lead with insulated sockets for 0.64 mm round and rectangular pin. Red inner lead, black shielding; cable type RG 58 A/U, 50 Ohm. For use with oscilloscopes, PC cards, etc.

### MAL N 4-0,64/100-0,25

Injection-moulded measuring lead with spring loaded 4 mm diameter plug and 4 mm diameter socket for further connection and insulated socket for 0.64 mm round and rectangular pin. Highly flexible 0.25 mm<sup>2</sup> stranded wire.

### MKL 0,64/25-0,25

Measuring lead with two insulated sockets for 0.64 mm round and rectangular pin. Highly flexible 0.25 mm<sup>2</sup> stranded wire with two 0.64 mm diameter sockets.

|                                 |                                      |
|---------------------------------|--------------------------------------|
| Cable length                    | 1.2m (47.2") BNC + 0.1m (3.9") wires |
| Cable size                      | –                                    |
| Cable material                  | –                                    |
| Pin dimensions                  | –                                    |
| Cable type                      | RG 58 A/U                            |
| <b>PART NO. / Housing color</b> | ● 933844001                          |

|                                 |                               |
|---------------------------------|-------------------------------|
| Cable length                    | 0.1m (39.4")                  |
| Cable size                      | 0.25 mm <sup>2</sup> (24 AWG) |
| Cable material                  | PVC                           |
| Pin dimensions                  | 4 mm (0.157")                 |
| Cable type                      | LIY                           |
| <b>PART NO. / Housing color</b> | ● 934160100<br>● 934160101    |




|                                 |                               |
|---------------------------------|-------------------------------|
| Cable length                    | 25 mm                         |
| Cable size                      | 0.25 mm <sup>2</sup> (24 AWG) |
| Cable material                  | PVC                           |
| Pin dimensions                  | 4 mm (0.157")                 |
| Cable type                      | LIY                           |
| <b>PART NO. / Housing color</b> | ● 973604100<br>● 973604101    |

## Technical Data

|                                 |                                                                  |                                                                      |                                                      |
|---------------------------------|------------------------------------------------------------------|----------------------------------------------------------------------|------------------------------------------------------|
| Contact Type                    | BNC conector, 2x0.64 mm (0.025") spring loaded square pin socket | pin (spring-loaded), 0.64mm (0.025") spring loaded square pin socket | 2x0.64mm (0.025 in.) spring loaded square pin socket |
| Voltage Rating                  | 30 VAC / 60 VDC                                                  | 30 VAC / 60 VDC                                                      | 30 VAC / 60 VDC                                      |
| Measurement Category (IEC61010) | CAT I                                                            | CAT I                                                                | CAT I                                                |
| Current Rating*                 | –                                                                | 3 A                                                                  | 3 A                                                  |
| Contact Resistance              | –                                                                | 70 mOhm                                                              | 20 mOhm                                              |
| <b>Material Specifications</b>  |                                                                  |                                                                      |                                                      |
| Contact Pin                     | –                                                                | nickel plated brass                                                  | gold plated copper beryllium                         |
| Contact Spring                  | –                                                                | nickel plated copper beryllium                                       | –                                                    |
| Housing                         | –                                                                | PVC                                                                  | PPO                                                  |
| <b>Environmental Conditions</b> |                                                                  |                                                                      |                                                      |
| Temperature Range               | -15 °C to +70 °C (5°F to 158°F)                                  | -15°C to +70°C (5°F to 158°F)                                        | -40 °C to +60 °C (-40°F to 140°F)                    |
| <b>Flamability Rating</b>       |                                                                  |                                                                      |                                                      |
| Housing                         | –                                                                | –                                                                    | UL 94 HB                                             |

## Drawing

Measurements are shown in millimeters.  
Multiply by 0.03937 to convert to inches.



\* Please consider derating graph on page 80.



# Measuring Leads 2 mm System



CE

## Type

### MVL 2/25; MVL 2/50; MVL 2/100

Injection-moulded measuring lead, at either end 2 mm diameter nickel-plated brass connector and 2 mm diameter socket with contact spring, for tower constructions. Highly flexible stranded lead, grip and lead shatter-proof.

### MAL S WS 2-4 100/1

Safety measuring lead according to IEC 61010, one end with 2 mm safety plug and other end with 4 mm safety plug, as well as 2 mm and 4 mm socket for onward connection capability. Gold-plated / nickel-plated copper-beryllium contact spring. Highly flexible, double insulated stranded lead and shatter-proof grip sleeves. Built in colour indicator for easy identification of insulation damages.

|                                 |                                          |
|---------------------------------|------------------------------------------|
| Cable length                    | 0.25m (9.8"), 0.5m (19.7"), 1.0m (39.4") |
| Cable size                      | 0.5 mm <sup>2</sup> (20AWG)              |
| Cable material                  | PVC                                      |
| Pin dimensions                  | 2 mm (0.078")                            |
| Cable type                      | LF-Y                                     |
| <b>PART NO. / Housing color</b> |                                          |
|                                 | 0.25 m 973594100 ● 973594101 ●           |
|                                 | 0.5 m 973595100 ● 973595101 ●            |
|                                 | 1.0 m 973596100 ● 973596101 ●            |

|                               |
|-------------------------------|
| 100 m (39.4")                 |
| 1 mm <sup>2</sup> (18 AWG)    |
| PVC                           |
| 2 mm (0.078") / 4 mm (0.157") |
| LEH-XY                        |
| ● 975163100 ● 975163105       |
| ● 975163101 ● 975163106       |
| ● 975163102 ● 975163107       |
| ● 975163103 ● 975163109       |
| ● 975163104                   |

## Technical Data

Contact Type stationary pin

Voltage Rating 30 VAC / 60 VDC

Measurement Category (IEC61010) CAT I

Current Rating\* 6 A

Contact Resistance 26 mOhm

### Material Specifications

Contact Pin nickel plated brass

Contact Spring copper beryllium

Housing Polypropylene

### Environmental Conditions

Temperature Range -40 °C to +60 °C (-40°F to 140°F)

### Flamability Rating

Housing UL 94 HB

spring-loaded pin

AC/DC 1000V

CAT II

10 A

21 mOhm

nickel plated brass

gold plated copper beryllium



Polyamide

-15 °C to +70 °C (5°F to 158°F)

UL 94 V-2

## Drawing

Measurements are shown in millimeters.  
Multiply by 0.03937 to convert to inches.



\* Please consider derating graph on page 80.

# Measuring Leads 2 mm System




| Type                                                                                                                                                                                                                                                                                                                                        | MVL S WS 25/1 Au           | MVL S WS 50/1 Au           | MVL S WS 100/1 Au          | MVL S WS 200/1 Au          |
|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|----------------------------|----------------------------|----------------------------|----------------------------|
| Safety measuring lead according to IEC 61010, with 2 mm safety plugs on both sides and 2 mm sockets for onward connection capability. Gold-plated copper-beryllium contact spring. Highly flexible, double insulated stranded lead and shatter-proof grip sleeves. Built in colour indicator for easy identification of insulation damages. |                            |                            |                            |                            |
| Cable length                                                                                                                                                                                                                                                                                                                                | 0.25m (9.8")               | 0.5m (19.7")               | 1.0m (39.4")               | 2.0m (78.7")               |
| Cable size                                                                                                                                                                                                                                                                                                                                  | 1 mm <sup>2</sup> (18 AWG) | 1 mm <sup>2</sup> (18 AWG) | 1 mm <sup>2</sup> (18 AWG) | 1 mm <sup>2</sup> (18 AWG) |
| Cable material                                                                                                                                                                                                                                                                                                                              | PVC                        | PVC                        | PVC                        | PVC                        |
| Pin dimensions                                                                                                                                                                                                                                                                                                                              | 2 mm (0.078")              | 2 mm (0.078")              | 2 mm (0.078")              | 2 mm (0.078")              |
| Cable type                                                                                                                                                                                                                                                                                                                                  | LEH-XY                     | LEH-XY                     | LEH-XY                     | LEH-XY                     |
| PART NO. / Housing color                                                                                                                                                                                                                                                                                                                    | ● 975694700                | ● 975695700                | ● 975696700                | ● 975698700                |
|                                                                                                                                                                                                                                                                                                                                             | ● 975694701                | ● 975695701                | ● 975696701                | ● 975698701                |
|                                                                                                                                                                                                                                                                                                                                             | ● 975694702                | ● 975695702                | ● 975696702                | ● 975698702                |
|                                                                                                                                                                                                                                                                                                                                             | ● 975694703                | ● 975695703                | ● 975696703                | ● 975698703                |
|                                                                                                                                                                                                                                                                                                                                             | ● 975694704                | ● 975695704                | ● 975696704                | ● 975698704                |
|                                                                                                                                                                                                                                                                                                                                             | ● 975694705                | ● 975695705                | ● 975696705                | ● 975698705                |
|                                                                                                                                                                                                                                                                                                                                             | ● 975694706                | ● 975695706                | ● 975696706                | ● 975698706                |
|                                                                                                                                                                                                                                                                                                                                             | ○ 975694707                | ○ 975695707                | ○ 975696707                | ○ 975698707                |
|                                                                                                                                                                                                                                                                                                                                             | ● 975694709                | ● 975695709                | ● 975696709                | ● 975698709                |

| Technical Data                  |                                 |                      |                      |                      |
|---------------------------------|---------------------------------|----------------------|----------------------|----------------------|
| Contact Type                    | 2x spring-loaded pin            | 2x spring-loaded pin | 2x spring-loaded pin | 2x spring-loaded pin |
| Voltage Rating                  | AC/DC 1000V                     | AC/DC 1000V          | AC/DC 1000V          | AC/DC 1000V          |
| Measurement Category (IEC61010) | CAT III                         | CAT III              | CAT III              | CAT III              |
| Current Rating*                 | 10A                             | 10A                  | 10A                  | 10A                  |
| Contact Resistance              | 10 mOhm                         | 15 mOhm              | 24 mOhm              | 44 mOhm              |
| Material Specifications         |                                 |                      |                      |                      |
| Contact Pin                     | gold plated brass               |                      |                      |                      |
| Contact Spring                  | gold plated copper-beryllium    |                      |                      |                      |
| Housing                         | Polyamide                       |                      |                      |                      |
| Environmental Conditions        |                                 |                      |                      |                      |
| Temperature Range               | -15 °C to +70 °C (5°F to 158°F) |                      |                      |                      |
| Flamability Rating              |                                 |                      |                      |                      |
| Housing                         | UL 94 V-2                       |                      |                      |                      |

## Drawing

Measurements are shown in millimeters.  
Multiply by 0.03937 to convert to inches.




\* Please consider derating graph on page 80.





# Measuring Leads

## 4 mm Solder Resistant System



### Type

MLN SIL 25/1      MLN SIL 50/1      MLN SIL 100/1      MLN SIL 150/1      MLN SIL 200/1

Measuring lead, at either end 4mm diameter plug with caged spring and 4mm diameter socket for tower construction. Nickel-plated copper beryllium contact spring. Highly flexible, double insulated stranded lead, grip and lead shatter-proof. Built in colour indicator for easy identification of insulation damages.

|                |                            |                            |                            |                            |                            |
|----------------|----------------------------|----------------------------|----------------------------|----------------------------|----------------------------|
| Cable length   | 0.25m (9.8")               | 0.5m (19.7")               | 1.0m (39.4")               | 1.5m (59.1")               | 2.0m (78.7")               |
| Cable size     | 1 mm <sup>2</sup> (18 AWG) | 1 mm <sup>2</sup> (18 AWG) | 1 mm <sup>2</sup> (18 AWG) | 1 mm <sup>2</sup> (18 AWG) | 1 mm <sup>2</sup> (18 AWG) |
| Cable material | Silicone                   | Silicone                   | Silicone                   | Silicone                   | Silicone                   |
| Pin dimensions | 4 mm (0.157")              | 4 mm (0.157")              | 4 mm (0.157")              | 4 mm (0.157")              | 4 mm (0.157")              |
| Cable type     | LEH-XY                     | LEH-XY                     | LEH-XY                     | LEH-XY                     | LEH-XY                     |

### PART NO. / Housing color

|             |             |             |             |             |
|-------------|-------------|-------------|-------------|-------------|
| ● 934090100 | ● 934091100 | ● 934092100 | ● 934093100 | ● 934094100 |
| ● 934090101 | ● 934091101 | ● 934092101 | ● 934093101 | ● 934094101 |
| ● 934090102 | ● 934091102 | ● 934092102 | ● 934093102 | ● 934094102 |
| ● 934090103 | ● 934091103 | ● 934092103 | ● 934093103 | ● 934094103 |
| ● 934090104 | ● 934091104 | ● 934092104 | ● 934093104 | ● 934094104 |

### Technical Data

|                                 |                      |                      |                      |                      |                      |
|---------------------------------|----------------------|----------------------|----------------------|----------------------|----------------------|
| Contact Type                    | 2x spring-loaded pin | 2x spring-loaded pin | 2x spring-loaded pin | 2x spring-loaded pin | 2x spring-loaded pin |
| Voltage Rating                  | 30 VAC / 60 VDC      | 30 VAC / 60 VDC      | 30 VAC / 60 VDC      | 30 VAC / 60 VDC      | 30 VAC / 60 VDC      |
| Measurement Category (IEC61010) | CAT I                | CAT I                | CAT I                | CAT I                | CAT I                |
| Current Rating*                 | 16A                  | 16A                  | 16A                  | 16A                  | 16A                  |
| Contact Resistance              | 8.5 mOhm             | 13 mOhm              | 22 mOhm              | 34 mOhm              | 40 mOhm              |

### Material Specifications

|                |                                |
|----------------|--------------------------------|
| Contact Pin    | nickel plated brass            |
| Contact Spring | nickel plated copper-beryllium |
| Housing        | Polyamide                      |

### Environmental Conditions


|                   |                                 |
|-------------------|---------------------------------|
| Temperature Range | -15 °C to +70 °C (5°F to 158°F) |
|-------------------|---------------------------------|

### Flamability Rating

|         |           |
|---------|-----------|
| Housing | UL 94 V-2 |
|---------|-----------|

### Drawing

Measurements are shown in millimeters.  
Multiply by 0.03937 to convert to inches.



\* Please consider derating graph on page 80.

# Measuring Leads

## 4 mm Retractable Sleeve System



| Type                                                                                                                                                                                                                                                                                                                                                                                           | MLB 25/1 V                 | MLB 50/1 V                 | MLB 100/1 V                | MLB 200/1 V                |
|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|----------------------------|----------------------------|----------------------------|----------------------------|
| Contact-protected measuring lead, at either end: 4 mm diameter plug, insulated by latching and sprung insulated sleeve which is only released by pressure on the side mounted locking spring. 4 mm diameter nickel-plated. Highly flexible, double insulated stranded conductor. Color indicator for the recognition of damage to the insulation. 4 mm diameter socket for tower construction. |                            |                            |                            |                            |
| Cable length                                                                                                                                                                                                                                                                                                                                                                                   | 0.25m (9.8")               | 0.5m (19.7")               | 1.0m (39.4")               | 2.0m (78.7")               |
| Cable size                                                                                                                                                                                                                                                                                                                                                                                     | 1 mm <sup>2</sup> (18 AWG) | 1 mm <sup>2</sup> (18 AWG) | 1 mm <sup>2</sup> (18 AWG) | 1 mm <sup>2</sup> (18 AWG) |
| Cable material                                                                                                                                                                                                                                                                                                                                                                                 | PVC                        | PVC                        | PVC                        | PVC                        |
| Pin dimensions                                                                                                                                                                                                                                                                                                                                                                                 | 4 mm (0.157")              | 4 mm (0.157")              | 4 mm (0.157")              | 4 mm (0.157")              |
| Cable type                                                                                                                                                                                                                                                                                                                                                                                     | LEH-XY                     | LEH-XY                     | LEH-XY                     | LEH-XY                     |
| PART NO. / Housing color                                                                                                                                                                                                                                                                                                                                                                       | ● 973644100                | ● 973645100                | ● 973646100                | ● 973647100                |
|                                                                                                                                                                                                                                                                                                                                                                                                | ● 973644101                | ● 973645101                | ● 973646101                | ● 973647101                |
|                                                                                                                                                                                                                                                                                                                                                                                                | ● 973644102                | ● 973645102                | ● 973646102                | ● 973647102                |
|                                                                                                                                                                                                                                                                                                                                                                                                | ● 973644103                | ● 973645103                | ● 973646103                | ● 973647103                |
|                                                                                                                                                                                                                                                                                                                                                                                                | ● 973644104                | ● 973645104                | ● 973646104<br>● 973646188 | ● 973647104                |

### Technical Data

|                                 |                   |                   |                   |                   |
|---------------------------------|-------------------|-------------------|-------------------|-------------------|
| Contact Type                    | spring-loaded pin | spring-loaded pin | spring-loaded pin | spring-loaded pin |
| Voltage Rating                  | 30 VAC / 60 VDC   | 30 VAC / 60 VDC   | 30 VAC / 60 VDC   | 30 VAC / 60 VDC   |
| Measurement Category (IEC61010) | CAT I             | CAT I             | CAT I             | CAT I             |
| Current Rating*                 | 16 A              | 16 A              | 16 A              | 16 A              |
| Contact Resistance              | 8.5 mOhm          | 13 mOhm           | 22 mOhm           | 40 mOhm           |

### Material Specifications

|                |                     |
|----------------|---------------------|
| Contact Pin    | nickel plated brass |
| Contact Spring | copper-beryllium    |
| Housing        | Polyamide           |

### Environmental Conditions


|                   |                                 |
|-------------------|---------------------------------|
| Temperature Range | -15 °C to +70 °C (5°F to 158°F) |
|-------------------|---------------------------------|

### Flamability Rating


|         |           |
|---------|-----------|
| Housing | UL 94 V-2 |
|---------|-----------|

### Drawing

Measurements are shown in millimeters.  
Multiply by 0.03937 to convert to inches.



\* Please consider derating graph on page 80.



## MLN 200/1

- 934065100
- 934065101
- 934065102
- 934065103
- 934065104

32



# Measuring Leads 4 mm System



## 2.5 mm<sup>2</sup> (14 AWG) Nickel plated contacts

| Type                     | MLN 25/2.5                                                                                                                                         | MLN 50/2.5                                                                                                                                         | MLN 100/2.5                                                                                                                                        | MLN 150/2.5                                                                                                                                        | MLN 200/2.5                                                                                                                                        |
|--------------------------|----------------------------------------------------------------------------------------------------------------------------------------------------|----------------------------------------------------------------------------------------------------------------------------------------------------|----------------------------------------------------------------------------------------------------------------------------------------------------|----------------------------------------------------------------------------------------------------------------------------------------------------|----------------------------------------------------------------------------------------------------------------------------------------------------|
| PART NO. / Housing color | ● 934059100<br>● 934059101<br>● 934059102<br>● 934059103<br>● 934059104<br>● 934059105<br>● 934059106<br>● 934059107<br>● 934059109<br>● 934059188 | ● 934061100<br>● 934061101<br>● 934061102<br>● 934061103<br>● 934061104<br>● 934061105<br>● 934061106<br>● 934061107<br>● 934061109<br>● 934061188 | ● 934063100<br>● 934063101<br>● 934063102<br>● 934063103<br>● 934063104<br>● 934063105<br>● 934063106<br>● 934063107<br>● 934063109<br>● 934063188 | ● 934507100<br>● 934507101<br>● 934507102<br>● 934507103<br>● 934507104<br>● 934507105<br>● 934507106<br>● 934507107<br>● 934507109<br>● 934507188 | ● 934066100<br>● 934066101<br>● 934066102<br>● 934066103<br>● 934066104<br>● 934066105<br>● 934066106<br>● 934066107<br>● 934066109<br>● 934066188 |

## 2.5 mm<sup>2</sup> (14 AWG) Gold plated contacts

| Type                     | MLN 25/2.5 Au                                                                                                                                      | MLN 50/2.5 Au                                                                                                                                      | MLN 100/2.5 Au                                                                                                                                     | MLN 150/2.5 Au                                                                                                                                     | MLN 200/2.5 Au                                                                                                                                     |
|--------------------------|----------------------------------------------------------------------------------------------------------------------------------------------------|----------------------------------------------------------------------------------------------------------------------------------------------------|----------------------------------------------------------------------------------------------------------------------------------------------------|----------------------------------------------------------------------------------------------------------------------------------------------------|----------------------------------------------------------------------------------------------------------------------------------------------------|
| PART NO. / Housing color | ● 934059700<br>● 934059701<br>● 934059702<br>● 934059703<br>● 934059704<br>● 934059705<br>● 934059706<br>● 934059707<br>● 934059709<br>● 934059788 | ● 934061700<br>● 934061701<br>● 934061702<br>● 934061703<br>● 934061704<br>● 934061705<br>● 934061706<br>● 934061707<br>● 934061709<br>● 934061788 | ● 934063700<br>● 934063701<br>● 934063702<br>● 934063703<br>● 934063704<br>● 934063705<br>● 934063706<br>● 934063707<br>● 934063709<br>● 934063788 | ● 934507700<br>● 934507701<br>● 934507702<br>● 934507703<br>● 934507704<br>● 934507705<br>● 934507706<br>● 934507707<br>● 934507709<br>● 934507788 | ● 934066700<br>● 934066701<br>● 934066702<br>● 934066703<br>● 934066704<br>● 934066705<br>● 934066706<br>● 934066707<br>● 934066709<br>● 934066788 |

|                                 |                   |                   |                                     |                   |                   |
|---------------------------------|-------------------|-------------------|-------------------------------------|-------------------|-------------------|
| <b>Technical Data</b>           | spring-loaded pin | spring-loaded pin | spring-loaded pin                   | spring-loaded pin | spring-loaded pin |
| Contact Type                    |                   |                   |                                     |                   |                   |
| Voltage Rating                  | 30 VAC / 60 VDC   | 30 VAC / 60 VDC   | 30 VAC / 60 VDC                     | 30 VAC / 60 VDC   | 30 VAC / 60 VDC   |
| Measurement Category (IEC61010) | CAT I             | CAT I             | CAT I                               | CAT I             | CAT I             |
| Current Rating*                 | 32A               | 32A               | 32A                                 | 32A               | 32A               |
| Contact Resistance              | 6 mOhm            | 8 mOhm            | 12 mOhm                             | 16 mOhm           | 20 mOhm           |
| <b>Material Specifications</b>  |                   |                   |                                     |                   |                   |
| Contact Pin                     |                   |                   | nickel /gold plated brass           |                   |                   |
| Contact Spring                  |                   |                   | nickel/gold plated copper-beryllium |                   |                   |
| Housing                         |                   |                   | Polyamide                           |                   |                   |
| <b>Environmental Conditions</b> |                   |                   |                                     |                   |                   |
| Temperature Range               |                   |                   | -15 °C to +70 °C                    |                   |                   |
| <b>Flamability Rating</b>       |                   |                   |                                     |                   |                   |
| Housing                         |                   |                   | UL 94 V-2                           |                   |                   |

\* Please consider derating graph on page 80.



# Measuring Leads

## 4.0 mm Safety Plug System



### Type

**MLS GG 25/1**  
**MLS GG 25/2,5**

**MLS GG 50/1**  
**MLS GG 50/2,5**

**MLS GG 100/1**  
**MLS GG 100/2,5**

**MLS GG 200/1**  
**MLS GG 200/2,5**

Safety measuring lead, at either end 4 mm diameter safety connector with straight outlet. Nickel-plated copper beryllium contact spring. Highly flexible, double insulated stranded lead, shatter-proof grip sleeve and lead. Built in colour indicator for easy identification of insulation damages.

Cable length  
Cable size  
Cable material  
Pin dimensions  
Cable type

**0.25m (9.8")**  
1 mm<sup>2</sup> (18 AWG)  
PVC  
4 mm (0.157")  
LEH-XY

**0.5m (19.7")**  
1 mm<sup>2</sup> (18 AWG)  
PVC  
4 mm (0.157")  
LEH-XY

**1.0m (39.4")**  
1 mm<sup>2</sup> (18 AWG)  
PVC  
4 mm (0.157")  
LEH-XY

**2.0m (78.7")**  
1 mm<sup>2</sup> (18 AWG)  
PVC  
4 mm (0.157")  
LEH-XY

### 1 mm<sup>2</sup> (18 AWG)

**PART NO. / Housing color**

● 934070100  
● 934070101  
● 934070102  
● 934070103  
● 934070104

● 934072100  
● 934072101  
● 934072102  
● 934072103  
● 934072104

● 934074100  
● 934074101  
● 934074102  
● 934074103  
● 934074104

● 934076100  
● 934076101  
● 934076102  
● 934076103  
● 934076104

### 2.5 mm<sup>2</sup> (14 AWG)

**PART NO. / Housing color**

● 934071100  
● 934071101  
● 934071102  
● 934071103  
● 934071104  
● 934071105  
● 934071106  
● 934071107  
● 934071109  
● 934071188

● 934073100  
● 934073101  
● 934073102  
● 934073103  
● 934073104  
● 934073105  
● 934073106  
● 934073107  
● 934073109  
● 934073188

● 934075100  
● 934075101  
● 934075102  
● 934075103  
● 934075104  
● 934075105  
● 934075106  
● 934075107  
● 934075109  
● 934075188

● 934077100  
● 934077101  
● 934077102  
● 934077103  
● 934077104  
● 934077105  
● 934077106  
● 934077107  
● 934077109  
● 934077188

### Technical Data

|                                 |                    |                   |                    |                    |
|---------------------------------|--------------------|-------------------|--------------------|--------------------|
| Contact Type                    | spring-loaded pin  | spring-loaded pin | spring-loaded pin  | spring-loaded pin  |
| Voltage Rating                  | AC/DC 1000V        | AC/DC 1000V       | AC/DC 1000V        | AC/DC 1000V        |
| Measurement Category (IEC61010) | CAT III            | CAT III           | CAT III            | CAT III            |
| Current Rating*                 | 16 A<br>32 A       | 16 A<br>32 A      | 16 A<br>32 A       | 16 A<br>32 A       |
| Contact Resistance              | 8.5 mOhm<br>6 mOhm | 13 mOhm<br>8 mOhm | 22 mOhm<br>12 mOhm | 40 mOhm<br>20 mOhm |

### Material Specifications

|                |                     |
|----------------|---------------------|
| Contact Pin    | nickel plated brass |
| Contact Spring | copper-beryllium    |
| Housing        | Polyamide           |

### Environmental Conditions


|                   |                                 |
|-------------------|---------------------------------|
| Temperature Range | -15 °C to +70 °C (5°F to 158°F) |
|-------------------|---------------------------------|

### Flamability Rating

|         |           |
|---------|-----------|
| Housing | UL 94 V-2 |
|---------|-----------|

### Drawing

Measurements are shown in millimeters.  
Multiply by 0.03937 to convert to inches.



\* Please consider derating graph on page 80.

# Measuring Leads

## 4.0 mm Safety Plug System




| Type                                                                                                                                                                                                                                                                                                             | MLS WG 25/1<br>MLS WG 25/2.5                                                           | MLS WG 50/1<br>MLS WG 50/2.5                                                           | MLS WG 100/1<br>MLS WG 100/2.5                                                         | MLS WG 200/1<br>MLS WG 200/2.5                                                         |
|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|----------------------------------------------------------------------------------------|----------------------------------------------------------------------------------------|----------------------------------------------------------------------------------------|----------------------------------------------------------------------------------------|
| Safety measuring lead, at either end 4mm diameter safety connector with straight and angled outlet. Nickel-plated copper beryllium contact spring. Highly flexible, double insulated stranded lead, shatter-proof grip sleeve and lead. Built in colour indicator for easy identification of insulation damages. |                                                                                        |                                                                                        |                                                                                        |                                                                                        |
| Cable length                                                                                                                                                                                                                                                                                                     | 0.25m (9.8")                                                                           | 0.5m (19.7")                                                                           | 1.0m (39.4")                                                                           | 2.0m (78.7")                                                                           |
| Cable size                                                                                                                                                                                                                                                                                                       | 1 mm <sup>2</sup> (18 AWG)<br>2.5 mm <sup>2</sup> (14 AWG)                             | 1 mm <sup>2</sup> (18 AWG)<br>2.5 mm <sup>2</sup> (14 AWG)                             | 1 mm <sup>2</sup> (18 AWG)<br>2.5 mm <sup>2</sup> (14 AWG)                             | 1 mm <sup>2</sup> (18 AWG)<br>2.5 mm <sup>2</sup> (14 AWG)                             |
| Cable material                                                                                                                                                                                                                                                                                                   | PVC                                                                                    | PVC                                                                                    | PVC                                                                                    | PVC                                                                                    |
| Pin dimensions                                                                                                                                                                                                                                                                                                   | 4 mm (0.157")                                                                          | 4 mm (0.157")                                                                          | 4 mm (0.157")                                                                          | 4 mm (0.157")                                                                          |
| Cable type                                                                                                                                                                                                                                                                                                       | LEH-XY                                                                                 | LEH-XY                                                                                 | LEH-XY                                                                                 | LEH-XY                                                                                 |
| <b>1 mm<sup>2</sup></b>                                                                                                                                                                                                                                                                                          |                                                                                        |                                                                                        |                                                                                        |                                                                                        |
| <b>PART NO. / Housing color</b>                                                                                                                                                                                                                                                                                  | ● 934078100<br>● 934078101<br>● 934078102<br>● 934078103<br>● 934078104                | ● 934080100<br>● 934080101<br>● 934080102<br>● 934080103<br>● 934080104                | ● 934082100<br>● 934082101<br>● 934082102<br>● 934082103<br>● 934082104                | ● 934084100<br>● 934084101<br>● 934084102<br>● 934084103<br>● 934084104                |
| <b>2.5 mm<sup>2</sup></b>                                                                                                                                                                                                                                                                                        |                                                                                        |                                                                                        |                                                                                        |                                                                                        |
| <b>PART NO. / Housing color</b>                                                                                                                                                                                                                                                                                  | ● 934079100<br>● 934079101<br>● 934079102<br>● 934079103<br>● 934079104<br>● 934079188 | ● 934081100<br>● 934081101<br>● 934081102<br>● 934081103<br>● 934081104<br>● 934081188 | ● 934083100<br>● 934083101<br>● 934083102<br>● 934083103<br>● 934083104<br>● 934083188 | ● 934085100<br>● 934085101<br>● 934085102<br>● 934085103<br>● 934085104<br>● 934085188 |

| Technical Data                  |                                 |                   |                    |                    |
|---------------------------------|---------------------------------|-------------------|--------------------|--------------------|
| Contact Type                    | spring-loaded pin               | spring-loaded pin | spring-loaded pin  | spring-loaded pin  |
| Voltage Rating                  | AC/DC 1000V                     | AC/DC 1000V       | AC/DC 1000V        | AC/DC 1000V        |
| Measurement Category (IEC61010) | CAT III                         | CAT III           | CAT III            | CAT III            |
| Current Rating*                 | 16 A<br>32 A                    | 16 A<br>32 A      | 16 A<br>32 A       | 16 A<br>32 A       |
| Contact Resistance              | 8 mOhm<br>6 mOhm                | 13 mOhm<br>8 mOhm | 22 mOhm<br>12 mOhm | 40 mOhm<br>20 mOhm |
| Material Specifications         |                                 |                   |                    |                    |
| Contact Pin                     | nickel plated brass             |                   |                    |                    |
| Contact Spring                  | copper-beryllium                |                   |                    |                    |
| Housing                         | Polyamide                       |                   |                    |                    |
| Environmental Conditions        |                                 |                   |                    |                    |
| Temperature Range               | -15 °C to +70 °C (5°F to 158°F) |                   |                    |                    |
| Flamability Rating              |                                 |                   |                    |                    |
| Housing                         | UL 94 V-2                       |                   |                    |                    |

### Drawing

Measurements are shown in millimeters.  
Multiply by 0.03937 to convert to inches.



\* Please consider derating graph on page 80.



# Measuring Leads

## 4 mm - Safety Plug System



### Type

#### MLS WS 25/1 MLS WS 25/2,5

#### MLS WS 50/1 MLS WS 50/2,5

#### MLS WS 100/1 MLS WS 100/2,5

#### MLS WS 200/1 MLS WS 200/2,5

Safety measuring lead, at either end 4 mm diameter safety connector with onward connection capability (4mm socket). Nickel-plated copper beryllium contact spring. Highly flexible, double insulated stranded lead, shatter-proof grip sleeve and lead. Built in colour indicator for easy identification of insulation damages.

Cable length  
Cable size

**0.25m (9.8")**  
1 mm<sup>2</sup> (18 AWG)  
2.5 mm<sup>2</sup> (14 AWG)

**0.5m (19.7")**  
1 mm<sup>2</sup> (18 AWG)  
2.5 mm<sup>2</sup> (14 AWG)

**1.0m (39.4")**  
1 mm<sup>2</sup> (18 AWG)  
2.5 mm<sup>2</sup> (14 AWG)

**2.0m (78.7")**  
1 mm<sup>2</sup> (18 AWG)  
2.5 mm<sup>2</sup> (14 AWG)

Cable material  
Pin dimensions  
Cable type

PVC  
4 mm (0.157")  
LEH-XY

PVC  
4 mm (0.157")  
LEH-XY

PVC  
4 mm (0.157")  
LEH-XY

PVC  
4 mm (0.157")  
LEH-XY

### 1 mm<sup>2</sup>

PART NO. / Housing color

● 934067100  
● 934067101  
● 934067102  
● 934067103  
● 934067104

● 934068100  
● 934068101  
● 934068102  
● 934068103  
● 934068104

● 934095100  
● 934095101  
● 934095102  
● 934095103  
● 934095104

● 934069100  
● 934069101  
● 934069102  
● 934069103  
● 934069104

### 2.5 mm<sup>2</sup>

PART NO. / Housing color

● 934086100  
● 934086101  
● 934086102  
● 934086103  
● 934086104  
● 934086105  
● 934086106  
● 934086107  
● 934086109  
● 934086188

● 934087100  
● 934087101  
● 934087102  
● 934087103  
● 934087104  
● 934087105  
● 934087106  
● 934087107  
● 934087109  
● 934087188

● 934088100  
● 934088101  
● 934088102  
● 934088103  
● 934088104  
● 934088105  
● 934088106  
● 934088107  
● 934088109  
● 934088188

● 934089100  
● 934089101  
● 934089102  
● 934089103  
● 934089104  
● 934089105  
● 934089106  
● 934089107  
● 934089109  
● 934089188

### Technical Data

|                                 |                   |                   |                    |                    |
|---------------------------------|-------------------|-------------------|--------------------|--------------------|
| Contact Type                    | spring-loaded pin | spring-loaded pin | spring-loaded pin  | spring-loaded pin  |
| Voltage Rating                  | AC/DC 1000V**     | AC/DC 1000V**     | AC/DC 1000V**      | AC/DC 1000V**      |
| Measurement Category (IEC61010) | CAT II**          | CAT II**          | CAT II**           | CAT II**           |
| Current Rating*                 | 16 A<br>32 A      | 16 A<br>32 A      | 16 A<br>32 A       | 16 A<br>32 A       |
| Contact Resistance              | 8 mOhm<br>6 mOhm  | 13 mOhm<br>8 mOhm | 22 mOhm<br>12 mOhm | 40 mOhm<br>20 mOhm |

### Material Specifications

|                |                     |
|----------------|---------------------|
| Contact Pin    | nickel plated brass |
| Contact Spring | copper-beryllium    |
| Housing        | Polyamide           |

### Environmental Conditions


|                   |                                 |
|-------------------|---------------------------------|
| Temperature Range | -15 °C to +70 °C (5°F to 158°F) |
|-------------------|---------------------------------|

### Flamability Rating

|         |           |
|---------|-----------|
| Housing | UL 94 V-2 |
|---------|-----------|

### Drawing

Measurements are shown in millimeters.  
Multiply by 0.03937 to convert to inches.



\* Please consider derating graph on page 80.

\*\* 600V AC/DC CAT III

# Measuring Leads

## 4 mm - Safety Plug System



### Type

#### PL 2600 S

Safety measuring lead with dual function safety test probe. Tip for penetration of insulation and oxide layers and 4 mm diameter pin for insertion into sockets. 4 mm diameter safety connector with straight outlet. Incl. Tip protection

|                |                                  |
|----------------|----------------------------------|
| Cable length   | 1.0m (39.4")                     |
| Conductor size | <b>1 mm<sup>2</sup> (18 AWG)</b> |
| Cable material | PVC                              |
| Pin dimensions | 4 mm (0.157")                    |
| Clamp type     | LEH-XY                           |

PART NO. / Housing color

- 934159100
- 934159101
- 934159102



#### PL 2600 S W

Safety measuring lead with dual function safety test probe. Tip for penetration of insulation and oxide layers and 4 mm diameter pin for insertion into sockets. 4 mm diameter safety connector with right-angled outlet. Incl. Tip protection

|                |                                  |
|----------------|----------------------------------|
| Cable length   | 1.0m (39.4")                     |
| Conductor size | <b>1 mm<sup>2</sup> (18 AWG)</b> |
| Cable material | PVC                              |
| Pin dimensions | 4 mm (0.157")                    |
| Clamp type     | LEH-XY                           |

- 934158100
- 934158101

### Technical Data

|                                 |                                   |
|---------------------------------|-----------------------------------|
| Contact Type                    | spring-loaded pin, stationary tip |
| Voltage Rating                  | AC/DC 1000 V                      |
| Measurement Category (IEC61010) | CAT II                            |
| Current Rating*                 | 16 A                              |
| Contact Resistance              | 20 mOhm                           |

### Material Specifications

|                |                                |
|----------------|--------------------------------|
| Contact Pin    | nickel plated brass            |
| Contact Spring | nickel plated copper-beryllium |
| Housing        | PA, PP                         |

### Environmental Conditions

|                   |                               |
|-------------------|-------------------------------|
| Temperature Range | -15°C to +70°C (5°F to 158°F) |
|-------------------|-------------------------------|

### Flamability Rating

|         |          |
|---------|----------|
| Housing | UL 94 HB |
|---------|----------|

|                                 |                                   |
|---------------------------------|-----------------------------------|
| Contact Type                    | spring-loaded pin, stationary tip |
| Voltage Rating                  | AC/DC 1000 V                      |
| Measurement Category (IEC61010) | CAT II                            |
| Current Rating*                 | 16 A                              |
| Contact Resistance              | 20 mOhm                           |



|                |                                |
|----------------|--------------------------------|
| Contact Pin    | nickel plated brass            |
| Contact Spring | nickel plated copper-beryllium |
| Housing        | PA, PP                         |

|                   |                               |
|-------------------|-------------------------------|
| Temperature Range | -15°C to +70°C (5°F to 158°F) |
|-------------------|-------------------------------|


|         |          |
|---------|----------|
| Housing | UL 94 HB |
|---------|----------|

### Drawing

Measurements are shown in millimeters.  
Multiply by 0.03937 to convert to inches.



\* Please consider derating graph on page 80.



# Measuring Leads

## 4 mm Safety System



**LMLH 50**  
Laboratory test lead holder with plastic brackets. Measuring leads can be laid neatly on walls, cabinets, etc. Consists: one aluminium profile rail, 30 plastic brackets, fastening kit.



**TW 120 BAN**  
SMD Test Tweezer for 2 wire measurements with multimeters. The gold-plating ensures lowest transition resistance. Available with BNC Connectors or Banana Plugs. Contacts gold-plated. Other cable lengths on request.

### Type

|                |   |
|----------------|---|
| Cable length   | – |
| Conductor size | – |
| Cable material | – |
| Pin dimensions | – |
| Clamp type     | – |

|              |
|--------------|
| 1.2m (47.2") |
| –            |
| –            |
| –            |
| RG 174       |

**PART NO. / Housing color** ● 973919001

● 974330000

### Technical Data

|                                 |   |
|---------------------------------|---|
| Contact Type                    | – |
| Voltage Rating                  | – |
| Measurement Category (IEC61010) | – |
| Current Rating*                 | – |
| Contact Resistance              | – |

### Material Specifications

|                |   |
|----------------|---|
| Contact Pin    | – |
| Contact Spring | – |
| Housing        | – |

### Environmental Conditions

|                   |   |
|-------------------|---|
| Temperature Range | – |
|-------------------|---|



### Flamability Rating

|         |   |
|---------|---|
| Housing | – |
|---------|---|

|                                                             |
|-------------------------------------------------------------|
| 2 gold-plated 4 mm banana plugs to gold-plated tweezer tips |
| 30 VAC / 60 VDC                                             |
| CAT I                                                       |
| –                                                           |
| –                                                           |
| –                                                           |
| –                                                           |
| –                                                           |
| –                                                           |

### Drawing

Measurements are shown in millimeters.  
Multiply by 0.03937 to convert to inches.



\* Please consider derating graph on page 80.



# Measuring Leads

## 4 mm Safety System



|                          |                                                                                                                                                                                                                                                                     |
|--------------------------|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Type                     | TKL 065 BAN                                                                                                                                                                                                                                                         |
|                          | High quality Kelvin Measuring Leads for 4 wire measurements with LCR measuring bridges and multimeters. The gold-plating ensures lowest transition resistance. Available with BNC Connectors or Banana Plugs. Contacts gold-plated. Other cable lengths on request. |
| Cable length             | 0.65m (25.6")                                                                                                                                                                                                                                                       |
| Conductor size           | —                                                                                                                                                                                                                                                                   |
| Cable material           | —                                                                                                                                                                                                                                                                   |
| Pin dimensions           | 4 mm (0.157")                                                                                                                                                                                                                                                       |
| Clamp type               | RG 174                                                                                                                                                                                                                                                              |
| PART NO. / Housing color | ● 974340000                                                                                                                                                                                                                                                         |




|                                                                                                                                                                                                                                                                                                             |
|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| SML 100/1                                                                                                                                                                                                                                                                                                   |
| Silicone measuring lead, 4 mm plug with caged spring on both sides. Nickel-plated copper beryllium contact spring. Highly flexible, double insulated stranded lead, resistant against soldering iron, grip and lead shatter-proof. Built in colour indicator for easy identification of insulation damages. |
| 1m (39.37")                                                                                                                                                                                                                                                                                                 |
| 1 mm² (18 AWG)                                                                                                                                                                                                                                                                                              |
| silicone                                                                                                                                                                                                                                                                                                    |
| 4 mm (0.157")                                                                                                                                                                                                                                                                                               |
| LEH-XY                                                                                                                                                                                                                                                                                                      |

- 973388100
- 973388101
- 973388102
- 973388103
- 973388104


| Technical Data                  |                                   |
|---------------------------------|-----------------------------------|
| Contact Type                    | spring-loaded pin, stationary tip |
| Voltage Rating                  | 30 VAC / 60 VDC                   |
| Measurement Category (IEC61010) | CAT I                             |
| Current Rating*                 | —                                 |
| Contact Resistance              | —                                 |
| Material Specifications         |                                   |
| Contact Pin                     | —                                 |
| Contact Spring                  | —                                 |
| Housing                         | —                                 |
| Environmental Conditions        |                                   |
| Temperature Range               | —                                 |
| Flamability Rating              |                                   |
| Housing                         | —                                 |

**Drawing**

Measurements are shown in millimeters.  
Multiply by 0.03937 to convert to inches.





\* Please consider derating graph on page 80.



## Test Plugs

Test Plugs from the inventor of the Banana Plug. Altech and SKS Hirschmann offers endless possibilities and solutions for different contact and connection systems. Various Plugs are also available for “Do it yourself” measurement leads.

- Large color spectrum
- Various connection types
- Different cross sections
- Safety plugs according to IEC61010



# Test Plugs 2 mm System



## Type

### MST 201

2mm mini connector pin for PCB boards, fits MKU1 and MBU2 (for stacking PCB boards), pin spacing 5mm and up.

Pin diameter

2 mm (0.078")

PART NO. / Housing color

931338001

### MST 3

2mm mini connector, nickel plated brass pin with solder connection, flexible and shatter proof insulated sleeve, connecting leads up to 1.9mm.

2 mm (0.078")

- 973509100
- 973509101
- 973509102
- 973509103
- 973509104
- 973509106

## Technical Data

|                                 |                 |
|---------------------------------|-----------------|
| Contact Type                    | pin             |
| Connection Type                 | solder terminal |
| Voltage Rating                  | 30 VAC / 60 VDC |
| Measurement Category (IEC61010) | CAT I           |
| Current Rating*                 | 6A              |
| Contact Resistance              | 6 mOhm          |

## Material Specifications

|                |                     |
|----------------|---------------------|
| Plug           | nickel plated brass |
| Contact Spring | -                   |
| Housing        | -                   |

## Environmental Conditions

|                   |                                |
|-------------------|--------------------------------|
| Temperature range | -20 °C to +60 °C (-4 to 140°F) |
|-------------------|--------------------------------|

## Flamability Rating

|         |   |
|---------|---|
| Housing | - |
|---------|---|

|                   |
|-------------------|
| spring loaded pin |
| solder terminal   |
| 30 VAC / 60 VDC   |
| CAT I             |
| 6A                |
| 6 mOhm            |



|                     |
|---------------------|
| nickel plated brass |
| -                   |
| PVC-P               |

|                                |
|--------------------------------|
| -20 °C to +60 °C (-4 to 140°F) |
|--------------------------------|


|   |
|---|
| - |
|---|

## Drawing

Measurements are shown in millimeters.  
Multiply by 0.03937 to convert to inches.



\* Please consider derating graph on page 80.



# Test Plugs 2 mm System



Type

**MZS 2**

Shrouded Adapter 2mm plug to 4mm jack.

Pin diameter

2 mm (0.078")

PART NO. / Housing color

● 973600100

● 973600101



CE

**MST S WS 30 AU**

2mm safety plug, spring loaded pin, gold plated, solder terminal 0.5mm2-1.0mm2, 1000V system.

2 mm (0.078")

● 975090700

● 975090701

● 975090702

● 975090703

● 975090704

● 975090705

● 975090706

● 975090707

● 975090709

## Technical Data

|                                 |                 |
|---------------------------------|-----------------|
| Contact Type                    | stationary      |
| Connection Type                 | jack Ø4mm       |
| Voltage Rating                  | 30 VAC / 60 VDC |
| Measurement Category (IEC61010) | CAT I           |
| Current Rating*                 | 6A              |
| Contact Resistance              | 6 mOhm          |

## Material Specifications

|                |                     |
|----------------|---------------------|
| Plug           | nickel plated brass |
| Contact Spring | -                   |
| Housing        | PP                  |

## Environmental Conditions

|                   |                                |
|-------------------|--------------------------------|
| Temperature range | -20 °C to +60 °C (-4 to 140°F) |
|-------------------|--------------------------------|

## Flamability Rating

|         |         |
|---------|---------|
| Housing | UL94 HB |
|---------|---------|

|                   |
|-------------------|
| spring loaded pin |
| solder terminal   |
| AC/DC 1000V       |
| CAT III           |
| 10A               |
| 2 mOhm            |



|                              |
|------------------------------|
| gold plated copper-beryllium |
| gold plated brass            |
| Polyamide                    |

|                              |
|------------------------------|
| -15°C to +70°C (-5 to 158°F) |
|------------------------------|

-

## Drawing

Measurements are shown in millimeters.  
Multiply by 0.03937 to convert to inches.



\* Please consider derating graph on page 80.



# Test Plugs 4 mm System



## Type

**VST 100**

4mm spring loaded connector pin, nickel plated brass, screw terminal up to 1.5mm².

Pin diameter

4 mm (0.157")

**PART NO. / Housing color**

**930581000**



**VST 20**

4mm spring loaded connector pin, nickel plated brass, M4 thread/ screw terminal up to 2mm².

4 mm (0.157")

**930050000**

## Technical Data

|                                 |                            |
|---------------------------------|----------------------------|
| Contact Type                    | spring loaded pin          |
| Connection Type                 | screw terminal max. 1.5mm² |
| Voltage Rating                  | 30 VAC / 60 VDC            |
| Measurement Category (IEC61010) | CAT I                      |
| Current Rating*                 | 16A                        |
| Contact Resistance              | 3 mOhm                     |

## Material Specifications

|                |                     |
|----------------|---------------------|
| Plug           | nickel plated brass |
| Contact Spring | —                   |
| Housing        | —                   |

## Environmental Conditions

|                   |                                 |
|-------------------|---------------------------------|
| Temperature range | -25 °C to +100°C (-13 to 212°F) |
|-------------------|---------------------------------|

## Flamability Rating

|         |   |
|---------|---|
| Housing | — |
|---------|---|

|                                 |  |
|---------------------------------|--|
| spring loaded pin               |  |
| M4 thread / soldering max. 2mm² |  |
| 30 VAC / 60 VDC                 |  |
| CAT I                           |  |
| 16A                             |  |
| 3 mOhm                          |  |

nickel plated brass

—



—

-25 °C to +100°C (-13 to 212°F)


—

## Drawing

Measurements are shown in millimeters.  
Multiply by 0.03937 to convert to inches.



\* Please consider derating graph on page 80.



# Test Plugs 4 mm System

## MZS 4

Shrouded Adapter 4mm plug to 2mm jack.

Pin diameter 4 mm (0.157")

- 973599100
- 973599101

## KB 2

Fork type cable lug, nickel plated brass, flexible insulation sleeve, screw terminal up to 2.5mm<sup>2</sup>.

Fork

- 930584100
- 930584101

### Technical Data

|                                 |                             |
|---------------------------------|-----------------------------|
| Contact Type                    | spring loaded pin           |
| Connection Type                 | spring-loaded jack (Ø 2 mm) |
| Voltage Rating                  | 30 VAC / 60 VDC             |
| Measurement Category (IEC61010) | CAT I                       |
| Current Rating*                 | 6A                          |
| Contact Resistance              | 6 mOhm                      |

### Material Specifications

|                |                                |
|----------------|--------------------------------|
| Plug           | nickel plated brass            |
| Contact Spring | nickel plated copper-beryllium |
| Housing        | PP                             |

### Environmental Conditions

|                   |                                |
|-------------------|--------------------------------|
| Temperature range | -20 °C to +60 °C (-4 to 140°F) |
|-------------------|--------------------------------|

### Flamability Rating

|         |   |
|---------|---|
| Housing | - |
|---------|---|

|                                        |
|----------------------------------------|
| fork cable lug                         |
| screw terminal max. 2.5mm <sup>2</sup> |
| 30 VAC / 60 VDC                        |
| CAT I                                  |
| 30A                                    |
| 1 mOhm                                 |



|                     |
|---------------------|
| nickel plated brass |
| -                   |
| PVC-P               |

|                                 |
|---------------------------------|
| -25 °C to +70 °C (-13 to 158°F) |
|---------------------------------|

|   |
|---|
| - |
|---|

### Drawing

Measurements are shown in millimeters.  
Multiply by 0.03937 to convert to inches.



\* Please consider derating graph on page 80.

# Test Plugs 4 mm System



## Type

### LAS 30 / LAS 30 Au

4mm spring loaded plug, nickel/ gold plated contact spring, solder terminal up to 1.5mm².

Pin diameter

4 mm (0.157")

PART NO. / Housing color

#### Nickel Plated

- 972518100
- 972518101
- 972518102
- 972518103
- 972518104

#### Gold Plated

- 972518700
- 972518701
- 972518702
- 972518703
- 972518704



### BUELA 20 K

4mm multi spring plug, flexible, insulated sleeve with 4mm cross hole, nickel plated brass, screw terminal max. 1.5mm².

4 mm (0.157")

- 930726100
- 930726101
- 930726102
- 930726103
- 930726104
- 930726107

## Technical Data

|                                 |                             |
|---------------------------------|-----------------------------|
| Contact Type                    | spring loaded pin           |
| Connection Type                 | solder terminal max. 1.5mm² |
| Voltage Rating                  | 30 VAC / 60 VDC             |
| Measurement Category (IEC61010) | CAT I                       |
| Current Rating*                 | 32A                         |
| Contact Resistance              | 3 mOhm                      |

## Material Specifications

|                |                                                        |
|----------------|--------------------------------------------------------|
| Plug           | nickel plated brass; gold plated brass                 |
| Contact Spring | nickel pl. copper-beryllium; gold pl. copper-beryllium |
| Housing        | PVC-P                                                  |

## Environmental Conditions

|                   |                                |
|-------------------|--------------------------------|
| Temperature range | -25 °C to +70°C (-13 to 158°F) |
|-------------------|--------------------------------|

## Flamability Rating

|         |   |
|---------|---|
| Housing | - |
|---------|---|

|                            |  |
|----------------------------|--|
| spring loaded pin          |  |
| screw terminal max. 1.5mm² |  |
| 30 VAC / 60 VDC            |  |
| CAT I                      |  |
| 16A                        |  |
| 3 mOhm                     |  |



|                     |  |
|---------------------|--|
| nickel plated brass |  |
| -                   |  |
| PVC-P               |  |

|                                |  |
|--------------------------------|--|
| -25 °C to +70°C (-13 to 158°F) |  |
|--------------------------------|--|


|   |  |
|---|--|
| - |  |
|---|--|

## Drawing

Measurements are shown in millimeters.  
Multiply by 0.03937 to convert to inches.



\* Please consider derating graph on page 80.



# Test Plugs 4 mm System

Type

## BUELA 30 K

4mm multi spring plug, flexible, insulated sleeve with 4mm cross hole, nickel plated brass, solder terminal max. 2.5mm<sup>2</sup>.

Pin diameter

4 mm (0.157")

PART NO. / Housing color

- 930727100
- 930727101
- 930727102
- 930727103
- 930727104
- 930727107



## BUELA 300 K

4mm multi spring plug, flexible, insulated sleeve with 4mm cross hole, nickel plated brass, solder terminal max. 2.5mm<sup>2</sup>.

4 mm (0.157")

- 931667100
- 931667101
- 931667102
- 931667103
- 931667104

### Technical Data

|                                 |                                         |
|---------------------------------|-----------------------------------------|
| Contact Type                    | spring loaded pin                       |
| Connection Type                 | solder terminal max. 2.5mm <sup>2</sup> |
| Voltage Rating                  | 30 VAC / 60 VDC                         |
| Measurement Category (IEC61010) | CAT I                                   |
| Current Rating*                 | 30A                                     |
| Contact Resistance              | 3 mOhm                                  |

### Material Specifications

|                |                     |
|----------------|---------------------|
| Plug           | nickel plated brass |
| Contact Spring | —                   |
| Housing        | PVC-P               |

### Environmental Conditions

|                   |                                |
|-------------------|--------------------------------|
| Temperature range | -25 °C to +70°C (-13 to 158°F) |
|-------------------|--------------------------------|

### Flamability Rating

|         |   |
|---------|---|
| Housing | — |
|---------|---|

|                                         |  |
|-----------------------------------------|--|
| fork cable lug                          |  |
| solder terminal max. 2.5mm <sup>2</sup> |  |
| 30 VAC / 60 VDC                         |  |
| CAT I                                   |  |
| 30A                                     |  |
| 3 mOhm                                  |  |



|                     |  |
|---------------------|--|
| nickel plated brass |  |
| —                   |  |
| PVC-P               |  |

|                                |  |
|--------------------------------|--|
| -25 °C to +70°C (-13 to 158°F) |  |
|--------------------------------|--|

—

### Drawing

Measurements are shown in millimeters.  
Multiply by 0.03937 to convert to inches.



\* Please consider derating graph on page 80.



# Test Plugs 4 mm System



## Type

### LAS N WS / LAS N WS Au

4mm stackable plug, nickel/ gold plated contact spring, screw terminal 0.5-1.5mm<sup>2</sup>.

Pin diameter

4 mm (0.157")

PART NO. / Housing color

#### Nickel Plated

- 934100100
- 934100101
- 934100102
- 934100103
- 934100104
- 934100105
- 934100106
- 934100107
- 934100109

#### Gold Plated

- 934100700
- 934100701
- 934100702
- 934100703
- 934100704
- 934100705
- 934100706
- 934100707
- 934100709



### BSB 20 K

4mm multi spring plug with cable gland, nickel plated brass, screw terminal max. 2.5mm<sup>2</sup>.

4 mm (0.157")

- 930729100
- 930729101
- 930729102
- 930729103
- 930729104

## Technical Data

Contact Type  
Connection Type  
Voltage Rating  
Measurement Category (IEC61010)  
Current Rating\*  
Contact Resistance

spring loaded pin  
screw terminal max. 1.5mm<sup>2</sup>  
30 VAC / 60 VDC  
CAT I  
24A  
3 mOhm

## Material Specifications

Plug  
Contact Spring  
Housing

nickel plated brass; gold plated brass  
nickel pl. copper-beryllium; gold pl. copper-beryllium  
Polyamide

## Environmental Conditions

Temperature range

-15 °C to +70°C (5 to 158°F)

## Flamability Rating

Housing

UL 94 V-2

spring loaded pin  
screw terminal max. 2.5mm<sup>2</sup>  
30 VAC / 60 VDC  
CAT I  
30A  
3 mOhm



brass  
nickel  
PP

-25 °C to +100°C (-13 to 212°F)


UL 94 HB

## Drawing

Measurements are shown in millimeters.  
Multiply by 0.03937 to convert to inches.



\* Please consider derating graph on page 80.



# Test Plugs 4 mm System



## BSB 300

4mm multi spring wire plug with parallel adapter for shorting proof connection, nickel plated brass, solder terminal max. 1.5mm<sup>2</sup>.

## VSB 20

4mm spring loaded plug with cable gland, stackable (4mm jack), screw terminal max. 2.5mm<sup>2</sup>.



### Type

Pin diameter

4 mm (0.157")

PART NO. / Housing color

- 931294100
- 931294101
- 931294102
- 931294103
- 931294104

- 930435100
- 930435101
- 930435102
- 930435103
- 930435104

### Technical Data

|                                 |                                         |
|---------------------------------|-----------------------------------------|
| Contact Type                    | spring loaded pin                       |
| Connection Type                 | solder terminal max. 1.5mm <sup>2</sup> |
| Voltage Rating                  | 30 VAC / 60 VDC                         |
| Measurement Category (IEC61010) | CAT I                                   |
| Current Rating*                 | 16A                                     |
| Contact Resistance              | 3 mOhm                                  |

### Material Specifications

|                |                     |
|----------------|---------------------|
| Plug           | nickel plated brass |
| Contact Spring | -                   |
| Housing        | PP                  |

### Environmental Conditions

|                   |                                 |
|-------------------|---------------------------------|
| Temperature range | -25 °C to +100°C (-13 to 212°F) |
|-------------------|---------------------------------|

### Flamability Rating

|         |          |
|---------|----------|
| Housing | UL 94 HB |
|---------|----------|

|                                        |
|----------------------------------------|
| spring loaded pin                      |
| screw terminal max. 2.5mm <sup>2</sup> |
| 30 VAC / 60 VDC                        |
| CAT I                                  |
| 30A                                    |
| 3 mOhm                                 |



|                     |
|---------------------|
| nickel plated brass |
| -                   |
| PP                  |

|                                 |
|---------------------------------|
| -25 °C to +70 °C (-13 to 158°F) |
|---------------------------------|

|          |
|----------|
| UL 94 HB |
|----------|

### Drawing

Measurements are shown in millimeters.  
Multiply by 0.03937 to convert to inches.



\* Please consider derating graph on page 80.

# Test Plugs 4 mm System



## Type

### VON 20

4mm spring loaded plug, flexible insulation sleeve, nickel plated brass, screw terminal max. 1.5mm<sup>2</sup>.

Pin diameter

4 mm (0.157")

PART NO. / Housing color

- 930046100
- 930046101
- 930046102
- 930046103
- 930046104



### VON 30

4mm spring loaded plug, flexible insulation sleeve, nickel plated brass, solder terminal max. 2.5mm<sup>2</sup>.

4 mm (0.157")

- 930047100
- 930047101
- 930047102
- 930047103
- 930047104

## Technical Data

|                                 |                                        |
|---------------------------------|----------------------------------------|
| Contact Type                    | spring loaded pin                      |
| Connection Type                 | screw terminal max. 1.5mm <sup>2</sup> |
| Voltage Rating                  | 30 VAC / 60 VDC                        |
| Measurement Category (IEC61010) | CAT I                                  |
| Current Rating*                 | 16A                                    |
| Contact Resistance              | 3 mOhm                                 |

## Material Specifications

|                |                     |
|----------------|---------------------|
| Plug           | nickel plated brass |
| Contact Spring | —                   |
| Housing        | PVC-P               |

## Environmental Conditions

|                   |                               |
|-------------------|-------------------------------|
| Temperature range | -25°C to +70°C (-13 to 158°F) |
|-------------------|-------------------------------|

## Flamability Rating

|         |   |
|---------|---|
| Housing | — |
|---------|---|

|                                        |  |
|----------------------------------------|--|
| spring loaded pin                      |  |
| screw terminal max. 2.5mm <sup>2</sup> |  |
| 30 VAC / 60 VDC                        |  |
| CAT I                                  |  |
| 30A                                    |  |
| 3 mOhm                                 |  |



|                     |  |
|---------------------|--|
| nickel plated brass |  |
| —                   |  |
| PVC-P               |  |

|                               |  |
|-------------------------------|--|
| -25°C to +70°C (-13 to 158°F) |  |
|-------------------------------|--|


|   |  |
|---|--|
| — |  |
|---|--|

## Drawing

Measurements are shown in millimeters.  
Multiply by 0.03937 to convert to inches.



\* Please consider derating graph on page 80.



# Test Plugs 4 mm System

Type

## VQ 20

4mm spring loaded plug with 4mm cross hole, flexible insulation sleeve, nickel plated brass, screw terminal max. 1.5mm<sup>2</sup>.

Pin diameter

4 mm (0.157")

PART NO. / Housing color

- 930058100
- 930058101
- 930058102
- 930058103
- 930058104
- 930058107

## VQ 30

4mm spring loaded plug with 4mm cross hole, flexible insulation sleeve, nickel plated brass, solder terminal max. 2.5mm<sup>2</sup>.

4 mm (0.157")

- 930061100
- 930061101
- 930061102
- 930061103
- 930061104
- 930061107

### Technical Data

|                                 |                                        |
|---------------------------------|----------------------------------------|
| Contact Type                    | spring loaded pin                      |
| Connection Type                 | screw terminal max. 1.5mm <sup>2</sup> |
| Voltage Rating                  | 30 VAC / 60 VDC                        |
| Measurement Category (IEC61010) | CAT I                                  |
| Current Rating*                 | 16A                                    |
| Contact Resistance              | 3 mOhm                                 |

### Material Specifications

|                |                     |
|----------------|---------------------|
| Plug           | nickel plated brass |
| Contact Spring | -                   |
| Housing        | PVC-P               |

### Environmental Conditions

|                   |                               |
|-------------------|-------------------------------|
| Temperature range | -25°C to +70°C (-13 to 158°F) |
|-------------------|-------------------------------|

### Flamability Rating

|         |   |
|---------|---|
| Housing | - |
|---------|---|

|                                         |                                         |
|-----------------------------------------|-----------------------------------------|
| spring loaded pin                       | spring loaded pin                       |
| solder terminal max. 2.5mm <sup>2</sup> | solder terminal max. 2.5mm <sup>2</sup> |
| 30 VAC / 60 VDC                         | 30 VAC / 60 VDC                         |
| CAT I                                   | CAT I                                   |
| 30A                                     | 30A                                     |
| 3 mOhm                                  | 3 mOhm                                  |



|                     |                     |
|---------------------|---------------------|
| nickel plated brass | nickel plated brass |
| -                   | -                   |
| PP                  | PP                  |

|                                |                                |
|--------------------------------|--------------------------------|
| -25°C to +70 °C (-13 to 158°F) | -25°C to +70 °C (-13 to 158°F) |
|--------------------------------|--------------------------------|

|   |   |
|---|---|
| - | - |
|---|---|

### Drawing

Measurements are shown in millimeters.  
Multiply by 0.03937 to convert to inches.



\* Please consider derating graph on page 80.



# Test Plugs

## 4 mm Retractable Plug System



### Type

#### SLS 10 B

4mm touch proof banana plug, sliding sleeve system, solder terminal max. 2.5mm<sup>2</sup> leads.

Pin diameter

4 mm (0.157")

PART NO. / Housing color

- 931824100
- 931824101
- 931824102
- 931824103
- 931824104
- 931824107



#### SLS 20 B

4mm touch proof banana plug, sliding sleeve system, screw terminal max. 1.5mm<sup>2</sup> leads.

4 mm (0.157")

- 931825100
- 931825101
- 931825102
- 931825103
- 931825104
- 931825107

### Technical Data

|                                 |                                         |
|---------------------------------|-----------------------------------------|
| Contact Type                    | spring loaded plug                      |
| Connection Type                 | solder terminal max. 2.5mm <sup>2</sup> |
| Voltage Rating                  | 30 VAC / 60 VDC                         |
| Measurement Category (IEC61010) | CAT I                                   |
| Current Rating*                 | 30A                                     |
| Contact Resistance              | 5 mOhm                                  |

### Material Specifications

|                |                                |
|----------------|--------------------------------|
| Plug           | nickel plated brass            |
| Contact Spring | nickel plated copper-beryllium |
| Housing        | POM                            |

### Environmental Conditions

|                   |                               |
|-------------------|-------------------------------|
| Temperature range | -25°C to +70°C (-13 to 158°F) |
|-------------------|-------------------------------|

### Flamability Rating

|         |          |
|---------|----------|
| Housing | UL 94 HB |
|---------|----------|

|                                 |                                        |
|---------------------------------|----------------------------------------|
| Contact Type                    | spring loaded plug                     |
| Connection Type                 | screw terminal max. 1.5mm <sup>2</sup> |
| Voltage Rating                  | 30 VAC / 60 VDC <sup>1</sup>           |
| Measurement Category (IEC61010) | CAT I                                  |
| Current Rating*                 | 16A                                    |
| Contact Resistance              | 5 mOhm                                 |



|                |                                |
|----------------|--------------------------------|
| Plug           | nickel plated brass            |
| Contact Spring | nickel plated copper-beryllium |
| Housing        | POM                            |

|                   |                               |
|-------------------|-------------------------------|
| Temperature range | -25°C to +70°C (-13 to 158°F) |
|-------------------|-------------------------------|

|         |          |
|---------|----------|
| Housing | UL 94 HB |
|---------|----------|

### Drawing


Measurements are shown in millimeters.  
Multiply by 0.03937 to convert to inches.



\* Please consider derating graph on page 80.

<sup>1</sup>For this two types up to DC 150 V, CAT II according IEC/EN 61010-31 item 6.4., comment 4 allowed for devices with not yet protected sockets.

Altech Corp.® • 35 Royal Road • Flemington, NJ 08822-6000 • Phone (908)806-9400 • FAX (908)806-9490



# Test Plugs

## 4 mm System Retractable Plug

Type

### SLS 200

4mm touch proof banana plug, stackable, sliding sleeve system, screw terminal max. 2.5mm<sup>2</sup> leads.

Pin diameter

PART NO. / Housing color

4 mm (0.157")

- 932153100
- 932153101
- 932153102
- 932153103
- 932153104



### LAS S W

4mm safety banana plug, angled, 1000V system, screw terminal 0.5-1.5mm<sup>2</sup> leads.

4 mm (0.157")

- 934098100
- 934098101
- 934098102
- 934098103
- 934098104

### Technical Data

|                                 |                                        |
|---------------------------------|----------------------------------------|
| Contact Type                    | spring loaded plug                     |
| Connection Type                 | screw terminal max. 2.5mm <sup>2</sup> |
| Voltage Rating                  | 30 VAC / 60 VDC <sup>1</sup>           |
| Measurement Category (IEC61010) | CAT I                                  |
| Current Rating*                 | 30A                                    |
| Contact Resistance              | 5 mOhm                                 |

### Material Specifications

|                |                                |
|----------------|--------------------------------|
| Plug           | nickel plated brass            |
| Contact Spring | nickel plated copper-beryllium |
| Housing        | PP                             |

### Environmental Conditions

|                   |                               |
|-------------------|-------------------------------|
| Temperature range | -25°C to +70°C (-13 to 158°F) |
|-------------------|-------------------------------|

### Flamability Rating

|         |          |
|---------|----------|
| Housing | UL 94 HB |
|---------|----------|

|                                       |
|---------------------------------------|
| spring loaded plug                    |
| screw terminal 0.5-1.5mm <sup>2</sup> |
| AC/DC 1000V                           |
| CAT III                               |
| 24A                                   |
| -                                     |



|                                |
|--------------------------------|
| nickel plated brass            |
| nickel plated copper-beryllium |
| Polyamide                      |

|                               |
|-------------------------------|
| -25°C to +70°C (-13 to 158°F) |
|-------------------------------|

|           |
|-----------|
| UL 94 V-2 |
|-----------|

### Drawing

Measurements are shown in millimeters.  
Multiply by 0.03937 to convert to inches.



\* Please consider derating graph on page 80.

<sup>1</sup>For this two types up to DC 150 V, CAT II according IEC/EN 61010-31 item 6.4., comment 4 allowed for devices with not yet protected sockets.

For the latest on Altech Test & Measurement specifications please visit [www.altechcorp.com/test-equipment](http://www.altechcorp.com/test-equipment)

# Test Plugs 4 mm System



## Type

### LAS S WS

4mm safety banana plug,  
stackable, 1000V system,  
screw terminal 0.5-1.5mm<sup>2</sup>  
leads.

Pin diameter

4 mm (0.157")

PART NO. / Housing color

- 934099100
- 934099101
- 934099102
- 934099103
- 934099104
- 934099105
- 934099106
- 934099107
- 934099109



### LAS S G

4mm safety banana plug,  
stackable, 1000V system,  
screw terminal 0.5-1.5mm<sup>2</sup>  
leads.

4 mm (0.157")

- 934097100
- 934097101
- 934097102
- 934097103
- 934097104
- 934097105
- 934097106
- 934097107
- 934097109



### KST S WS

4mm dual safety plug,  
stackable, 1000V system,  
nickel plated, 4mm jack.

4 mm (0.157")

- 932200100
- 932200101
- 932200102
- 932200103
- 932200104

## Technical Data

|                                 |                                       |
|---------------------------------|---------------------------------------|
| Contact Type                    | spring loaded plug                    |
| Connection Type                 | screw terminal 0.5-1.5mm <sup>2</sup> |
| Voltage Rating                  | AC/DC 1000 V                          |
| Measurement Category (IEC61010) | CAT II                                |
| Current Rating*                 | 24A                                   |
| Contact Resistance              | –                                     |

## Material Specifications

|                |                                |
|----------------|--------------------------------|
| Plug           | nickel plated brass            |
| Contact Spring | nickel plated copper-beryllium |
| Housing        | Polyamide                      |

## Environmental Conditions

|                   |                             |
|-------------------|-----------------------------|
| Temperature range | -15°C to +70°C (5 to 158°F) |
|-------------------|-----------------------------|

## Flamability Rating

|         |           |
|---------|-----------|
| Housing | UL 94 V-2 |
|---------|-----------|

|                                 |                                       |
|---------------------------------|---------------------------------------|
| Contact Type                    | spring loaded plug                    |
| Connection Type                 | screw terminal 0.5-1.5mm <sup>2</sup> |
| Voltage Rating                  | AC/DC 1000 V                          |
| Measurement Category (IEC61010) | CAT III                               |
| Current Rating*                 | 24A                                   |
| Contact Resistance              | –                                     |

|                |                                |
|----------------|--------------------------------|
| Plug           | nickel plated brass            |
| Contact Spring | nickel plated copper-beryllium |
| Housing        | Polyamide                      |

|                   |                             |
|-------------------|-----------------------------|
| Temperature range | -15°C to +70°C (5 to 158°F) |
|-------------------|-----------------------------|

|         |           |
|---------|-----------|
| Housing | UL 94 V-2 |
|---------|-----------|

|                                 |                       |
|---------------------------------|-----------------------|
| Contact Type                    | 2x spring loaded plug |
| Connection Type                 | jack Ø 4 mm           |
| Voltage Rating                  | AC/DC 1000 V          |
| Measurement Category (IEC61010) | CAT II                |
| Current Rating*                 | 32A                   |
| Contact Resistance              | 8 mOhm                |




|                |                                |
|----------------|--------------------------------|
| Plug           | nickel plated copper-beryllium |
| Contact Spring | nickel plated brass            |
| Housing        | Polyamide                      |

|                   |                             |
|-------------------|-----------------------------|
| Temperature range | -15°C to +70°C (5 to 158°F) |
|-------------------|-----------------------------|


|         |           |
|---------|-----------|
| Housing | UL 94 V-2 |
|---------|-----------|

## Drawing

Measurements are shown in millimeters.  
Multiply by 0.03937 to convert to inches.




\* Please consider derating graph on page 80.



## Test Jacks

Quick mounting and durability are 2 attributes that characterize Altech test jacks and sockets. They can be used as connecting sockets in power supplies, connecting points in service devices or test jacks in test & measurement applications and devices.

- Large variety in colors
- Tin/ nickel/ gold plating
- Screw-in and press-in versions
- Regular and spring loaded jacks/ sockets
- Up to 1000V CAT III voltage rating





# Test Jacks 2 mm System



## Type

### MKU 1

2mm mini Adapter, tin plated Copper-Beryllium contact spring with solder terminal. Flexible, shatter-proof insulation sleeve, max. connecting lead diameter 2mm.

Pin Diameter

2 mm

**PART NO. / Housing color**

- 930320100
- 930320101
- 930320102
- 930320103
- 930320104
- 930320107



### MBI 1 / MBI 1 Au

2mm panel mount mini test jack, tin/ gold plated Copper-Beryllium contact spring with solder terminal. Installation in equipment chassis and switch panels, max. wall thickness 5mm.

2 mm

#### Nickel Plated

- 930308100
- 930308101
- 930308102
- 930308103
- 930308104
- 930308106

#### Gold Plated

- 930308700
- 930308701
- 930308702
- 930308703
- 930308704
- 930308706

## Technical Data

|                                 |                            |
|---------------------------------|----------------------------|
| Contact Type                    | spring-loaded jack Ø 2 mm  |
| Connection Type                 | solder terminal max Ø 2 mm |
| Voltage Rating                  | 30 VAC / 60 VDC            |
| Measurement Category (IEC61010) | CAT I                      |
| Current Rating*                 | 6 A                        |
| Contact Resistance              | 6 mOhm                     |
| Mounting Type                   | –                          |

## Material Specifications

|                |                             |
|----------------|-----------------------------|
| Jack Body      | –                           |
| Contact Spring | tin plated copper-beryllium |
| Housing        | PVC-P                       |

## Environmental Conditions

|                   |                               |
|-------------------|-------------------------------|
| Temperature Range | -20°C to +60 °C (-4 to 140°F) |
|-------------------|-------------------------------|

## Flamability Rating

|         |   |
|---------|---|
| Housing | – |
|---------|---|

spring-loaded jack Ø 2 mm

|                 |
|-----------------|
| solder terminal |
| 30 VAC / 60 VDC |
| CAT I           |
| 6 A             |
| 6 mOhm          |
| screw thread M5 |



|                                                            |
|------------------------------------------------------------|
| –                                                          |
| tin plated copper-beryllium   gold plated copper-beryllium |
| Polyamide                                                  |

-20°C to +60 °C (-4 to 140°F)

UL 94 HB

## Drawing

Measurements are shown in millimeters.  
Multiply by 0.03937 to convert to inches.



\* Please consider derating graph on page 80.



# Test Jacks 2 mm System

## Type

### MBU 1

2mm panel mount mini test jack, nickel plated brass, spring loaded with solder terminal. max. installation wall thickness 8mm.

Pin Diameter

2 mm

PART NO. / Housing color

930312000



### MBU 2

2mm mini metal test jack, tin plated brass, spring loaded with PCB soldering terminal. Fits MST3, MVL 2 and MST201.

2 mm

931337000

## Technical Data

|                                 |                           |
|---------------------------------|---------------------------|
| Contact Type                    | spring-loaded jack Ø 2 mm |
| Connection Type                 | solder terminal           |
| Voltage Rating                  | 30 VAC / 60 VDC           |
| Measurement Category (IEC61010) | CAT I                     |
| Current Rating*                 | 6 A                       |
| Contact Resistance              | 6 mOhm                    |
| Mounting Type                   | screw thread M5           |

## Material Specifications

|                |                             |
|----------------|-----------------------------|
| Jack Body      | nickel plated brass         |
| Contact Spring | tin plated copper-beryllium |
| Housing        | –                           |

## Environmental Conditions

|                   |                               |
|-------------------|-------------------------------|
| Temperature Range | -20°C to +60 °C (-4 to 140°F) |
|-------------------|-------------------------------|

## Flamability Rating

|         |   |
|---------|---|
| Housing | – |
|---------|---|

|                           |
|---------------------------|
| spring-loaded jack Ø 2 mm |
| solder terminal           |
| 30 VAC / 60 VDC           |
| CAT I                     |
| 6 A                       |
| 6 mOhm                    |
| screw                     |



|                              |
|------------------------------|
| tin plated brass             |
| gold plated copper-beryllium |
| –                            |

|                               |
|-------------------------------|
| -20°C to +60 °C (-4 to 140°F) |
|-------------------------------|

|   |
|---|
| – |
|---|

## Drawing

Measurements are shown in millimeters.  
Multiply by 0.03937 to convert to inches.



\* Please consider derating graph on page 80.

# Test Jacks 2 mm System



## Type

### MPB 1

2mm mini test jack, dimensions according to DIN41649. Suitable for testing PCB boards during operation.

Pin Diameter

2 mm

PART NO. / Housing color

● 930224100

● 930224101



### MPK 1

2mm insulated panel mount binding post with cross hole, gold plated Copper-Beryllium contact spring, tin plated brass thread bold with solder terminal. max. panel thickness 8mm

2 mm

● 930268100

● 930268101

## Technical Data

Contact Type spring-loaded jack Ø 2 mm

Connection Type solder terminal

Voltage Rating 30 VAC / 60 VDC

Measurement Category (IEC61010) CAT I

Current Rating\* 6 A

Contact Resistance 6 mOhm

Mounting Type PCB

## Material Specifications

Jack Body –

Contact Spring tin plated bronze

Housing PC

## Environmental Conditions

Temperature Range -20°C to +60 °C (-4 to 140°F)

## Flamability Rating

Housing UL 94 HB

spring-loaded jack Ø 2 mm, cross hole Ø 2 mm

solder terminal

30 VAC / 60 VDC

CAT I

6 A

6 mOhm

screw thread M3

gold plated copper-beryllium

–



Polyamide

-20°C to +60 °C (-4 to 140°F)

UL 94 V-2

## Drawing

Measurements are shown in millimeters.  
Multiply by 0.03937 to convert to inches.



\* Please consider derating graph on page 80.



# Test Jacks 2 mm System



## MSEB 2600 G M3 Au

2mm panel mount safety test jack, gold plated brass with M3 thread and solder terminal. max. installation wall thickness 8mm.



## MSEB 2610 F2.8 Au

2mm panel mount safety test jack, gold plated brass with flat 2.8x0.8mm DIN46244 terminal. max. installation wall thickness 8mm.



## MSEB 2630 S1.9 Au

2mm panel mount safety test jack, gold plated brass with 1.9mm solder pin terminal. max. installation wall thickness 8mm.

Pin Diameter

PART NO. / Housing color

2 mm

- 975454700
- 975454701
- 975454702
- 975454703
- 975454704
- 975454705
- 975454706
- 975454707
- 975454709

2 mm

- 975455700
- 975455701
- 975455702
- 975455703
- 975455704
- 975455705
- 975455706
- 975455707
- 975455709

2 mm

- 975459700
- 975459701
- 975459702
- 975459703
- 975459704
- 975459705
- 975459706
- 975459707
- 975459709

### Technical Data

|                                 |                            |
|---------------------------------|----------------------------|
| Contact Type                    | jack Ø 2 mm                |
| Connection Type                 | M3 thread, solder terminal |
| Voltage Rating                  | AC/DC 1000V                |
| Measurement Category (IEC61010) | CAT III                    |
| Current Rating*                 | 10 A                       |
| Contact Resistance              | 5 mOhm                     |
| Mounting Type                   | screw thread M8            |

### Material Specifications

|                |                   |
|----------------|-------------------|
| Jack Body      | gold plated brass |
| Contact Spring | -                 |
| Housing        | Polyamide         |

### Environmental Conditions

|                   |                             |
|-------------------|-----------------------------|
| Temperature Range | -15°C to +70°C (5 to 158°F) |
|-------------------|-----------------------------|

### Flamability Rating

|         |           |
|---------|-----------|
| Housing | UL 94 V-2 |
|---------|-----------|

|                             |
|-----------------------------|
| jack Ø 2 mm                 |
| flat 2.8x0.8 mm push in tab |
| AC/DC 1000V                 |
| CAT III                     |
| 10 A                        |
| 5 mOhm                      |
| screw thread M8             |

|                   |
|-------------------|
| gold plated brass |
| -                 |
| Polyamide         |

|                             |
|-----------------------------|
| -15°C to +70°C (5 to 158°F) |
|-----------------------------|

|           |
|-----------|
| UL 94 V-2 |
|-----------|

|                 |
|-----------------|
| jack Ø 2 mm     |
| solder terminal |
| AC/DC 1000V     |
| CAT III         |
| 10 A            |
| 5 mOhm          |
| screw thread M8 |




|                   |
|-------------------|
| gold plated brass |
| -                 |
| Polyamide         |

|                             |
|-----------------------------|
| -15°C to +70°C (5 to 158°F) |
|-----------------------------|

|           |
|-----------|
| UL 94 V-2 |
|-----------|

### Drawing

Measurements are shown in millimeters.  
Multiply by 0.03937 to convert to inches.



\* Please consider derating graph on page 80.



# Test Jacks 4 mm System



## Type

### KUN 30 / KUN 30 Au

4mm Adapter, nickel/ gold plated brass with solder terminal max 2.5mm<sup>2</sup>. Flexible, shatter-proof insulation sleeve

Pin Diameter

4 mm

PART NO. / Housing color

#### Nickel Plated

● 931804100

● 931804101

● 931804102

● 931804103

● 931804104

○ 931804107

nickel

#### Gold Plated

● 931804700

● 931804701

● 931804702

● 931804703

● 931804704

○ 931804707

gold



### PB 4

4mm test jack, dimensions according to DIN41649. Suitable for testing PCB boards during operation.

4 mm

● 973582100

● 973582101

## Technical Data

|                                 |                                            |
|---------------------------------|--------------------------------------------|
| Contact Type                    | jack Ø 4 mm                                |
| Connection Type                 | solder terminal (max. 2.5mm <sup>2</sup> ) |
| Voltage Rating                  | 30 VAC / 60 VDC                            |
| Measurement Category (IEC61010) | CAT I                                      |
| Current Rating*                 | 16 A                                       |
| Contact Resistance              | 3 mOhm                                     |
| Mounting Type                   | –                                          |

### Material Specifications

|                |                                         |
|----------------|-----------------------------------------|
| Jack Body      | nickel plated brass   gold plated brass |
| Contact Spring | –                                       |
| Housing        | PVC-P                                   |

### Environmental Conditions

|                   |                                |
|-------------------|--------------------------------|
| Temperature Range | -25°C to +70 °C (-13 to 158°F) |
|-------------------|--------------------------------|

### Flamability Rating

|         |   |
|---------|---|
| Housing | – |
|---------|---|

|                 |
|-----------------|
| jack Ø 4 mm     |
| solder          |
| 30 VAC / 60 VDC |
| CAT I           |
| 16 A            |
| 5 mOhm          |
| PCB             |

tin plated brass

–



PC

-25°C to +70 °C (-13 to 158°F)

UL 94 HB

## Drawing

Measurements are shown in millimeters.  
Multiply by 0.03937 to convert to inches.



\* Please consider derating graph on page 80.



# Test Jacks 4 mm System

## Type

### KD 10

4mm Insulated Adapter, nickel plated brass, for two 4mm plugs

### KUN 10

4mm Insulated Adapter, tin plated brass jack and screw terminal max 1.5mm<sup>2</sup>

Pin Diameter

4 mm

4 mm

PART NO. / Housing color

● 930109100  
● 930109101

● 930189100  
● 930189101

## Technical Data

|                                 |                 |
|---------------------------------|-----------------|
| Contact Type                    | jack Ø 4 mm     |
| Connection Type                 | jack (Ø 4 mm)   |
| Voltage Rating                  | 30 VAC / 60 VDC |
| Measurement Category (IEC61010) | CAT I           |
| Current Rating*                 | 10 A            |
| Contact Resistance              | 5 mOhm          |
| Mounting Type                   | –               |

## Material Specifications

|                |                     |
|----------------|---------------------|
| Jack Body      | nickel plated brass |
| Contact Spring | –                   |
| Housing        | PS                  |

## Environmental Conditions

|                   |                                |
|-------------------|--------------------------------|
| Temperature Range | -25°C to +70 °C (-13 to 158°F) |
|-------------------|--------------------------------|

## Flamability Rating

|         |          |
|---------|----------|
| Housing | UL 94 HB |
|---------|----------|

|                                        |
|----------------------------------------|
| jack Ø 4 mm                            |
| screw terminal max. 1.5mm <sup>2</sup> |
| 30 VAC / 60 VDC                        |
| CAT I                                  |
| 16 A                                   |
| 3 mOhm                                 |
| –                                      |



|                  |
|------------------|
| tin plated brass |
| –                |
| PS               |

|                                |
|--------------------------------|
| -25°C to +70 °C (-13 to 158°F) |
|--------------------------------|

|          |
|----------|
| UL 94 HB |
|----------|

## Drawing

Measurements are shown in millimeters.  
Multiply by 0.03937 to convert to inches.



\* Please consider derating graph on page 80.

# Test Jacks 4 mm System



## Type

### BO 10

4mm panel mount test jack, nickel plated brass, M6 thread screw terminal. panel thickness 1.5-8mm

Pin Diameter

4 mm

**PART NO. / Housing color**

**930160000**



### BU 10 / BU 10 Au

4mm panel mount test jack, nickel/gold plated brass, M6 thread screw/ solder terminal. max. panel thickness 11mm

4 mm

**930147000**

(Nickel plated)

**930147700**

(Gold plated)



## Technical Data

|                                 |                                |
|---------------------------------|--------------------------------|
| Contact Type                    | jack Ø 4 mm                    |
| Connection Type                 | M6 thread                      |
| Voltage Rating                  | 30 VAC / 60 VDC                |
| Measurement Category (IEC61010) | CAT I                          |
| Current Rating*                 | 16 A                           |
| Contact Resistance              | 5 mOhm                         |
| Mounting Type                   | screw thread M6                |
| <b>Material Specifications</b>  |                                |
| Jack Body                       | nickel plated brass            |
| Contact Spring                  | -                              |
| Housing                         | -                              |
| <b>Environmental Conditions</b> |                                |
| Temperature Range               | -25°C to +70 °C (-13 to 158°F) |
| <b>Flamability Rating</b>       |                                |
| Housing                         | -                              |

|                                |
|--------------------------------|
| jack Ø 4 mm                    |
| M6 thread, solder terminal     |
| 30 VAC / 60 VDC                |
| CAT I                          |
| 16 A                           |
| 5 mOhm                         |
| screw thread M6                |
| nickel / gold plated brass     |
| -                              |
| -                              |
| -25°C to +70 °C (-13 to 158°F) |
| -                              |

## Drawing

Measurements are shown in millimeters.  
Multiply by 0.03937 to convert to inches.



\* Please consider derating graph on page 80.



# Test Jacks 4 mm System

## Type

### BU 20

4mm panel mount test jack, nickel plated brass, M6 thread screw/ solder terminal. max. panel thickness 13.5mm



### BIL 20 / BIL 20 Au

4mm panel mount test jack, tin/ gold plated brass, M6 thread screw/ solder terminal, max. panel thickness 2mm



Pin Diameter

4 mm

PART NO. / Housing color

930177000

4 mm

#### Nickel Plated

- 930176100
- 930176101
- 930176102
- 930176103
- 930176104
- 930176105
- 930176106
- 930176107
- 930176109

#### Gold Plated

- 930176700
- 930176701
- 930176702
- 930176703
- 930176704
- 930176705
- 930176706
- 930176707
- 930176709



## Technical Data

|                                 |                                |
|---------------------------------|--------------------------------|
| Contact Type                    | jack Ø 4 mm                    |
| Connection Type                 | M6 thread, solder terminal     |
| Voltage Rating                  | 30 VAC / 60 VDC                |
| Measurement Category (IEC61010) | CAT I                          |
| Current Rating*                 | 16 A                           |
| Contact Resistance              | 5 mOhm                         |
| Mounting Type                   | screw thread M6                |
| <b>Material Specifications</b>  |                                |
| Jack Body                       | nickel plated brass            |
| Contact Spring                  | nickel                         |
| Housing                         | –                              |
| <b>Environmental Conditions</b> |                                |
| Temperature Range               | -25°C to +70 °C (-13 to 158°F) |
| <b>Flamability Rating</b>       |                                |
| Housing                         | –                              |

|                                |
|--------------------------------|
| jack Ø 4 mm                    |
| M6 thread, solder terminal     |
| 30 VAC / 60 VDC                |
| CAT I                          |
| 32 A                           |
| 5 mOhm                         |
| screw thread M6                |
| tin / gold plated brass        |
| –                              |
| Polyamide                      |
| -25°C to +70 °C (-13 to 158°F) |
| UL 94 V-2                      |

## Drawing

Measurements are shown in millimeters.  
Multiply by 0.03937 to convert to inches.



\* Please consider derating graph on page 80.



# Test Jacks 4 mm System



## Type

### BIL 30 / BIL 30 Au

4mm panel mount test jack, tin/ gold plated brass, M6 thread screw/ solder terminal, max. panel thickness 4mm

Pin Diameter

4 mm

PART NO. / Housing color

| Nickel Plated | Gold Plated |
|---------------|-------------|
| ● 930166100   | ● 930166700 |
| ● 930166101   | ● 930166701 |
| ● 930166102   | ● 930166702 |
| ● 930166103   | ● 930166703 |
| ● 930166104   | ● 930166704 |
| ● 930166105   | ● 930166705 |
| ● 930166106   | ● 930166706 |
| ● 930166107   | ● 930166707 |
| ● 930166109   | ● 930166709 |



### BUG 10 / BUG 10 Au

4mm panel mount test jack, tin/ gold plated brass, M6 thread screw/ solder terminal, max. panel thickness 8mm

4 mm

| Nickel Plated | Gold Plated |
|---------------|-------------|
| ● 930175100   | ● 930175700 |
| ● 930175101   | ● 930175701 |
| ● 930175102   | ● 930175702 |
| ● 930175103   | ● 930175703 |
| ● 930175104   | ● 930175704 |
| ○ 930175107   | ○ 930175707 |



## Technical Data

|                                 |                                |
|---------------------------------|--------------------------------|
| Contact Type                    | jack Ø 4 mm                    |
| Connection Type                 | M6 thread, solder terminal     |
| Voltage Rating                  | 30 VAC / 60 VDC                |
| Measurement Category (IEC61010) | CAT I                          |
| Current Rating*                 | 32 A                           |
| Contact Resistance              | 5 mOhm                         |
| Mounting Type                   | screw thread M6                |
| <b>Material Specifications</b>  |                                |
| Jack Body                       | tin / gold plated brass        |
| Contact Spring                  | –                              |
| Housing                         | Polyamide                      |
| <b>Environmental Conditions</b> |                                |
| Temperature Range               | -25°C to +85 °C (-13 to 185°F) |
| <b>Flamability Rating</b>       |                                |
| Housing                         | UL 94 V-2                      |

|                                |
|--------------------------------|
| jack Ø 4 mm                    |
| M6 thread, solder terminal     |
| 30 VAC / 60 VDC                |
| CAT I                          |
| 16 A                           |
| 5 mOhm                         |
| screw thread M6                |
| tin / gold plated brass        |
| –                              |
| Polyamide                      |
| -25°C to +85 °C (-13 to 185°F) |
| UL 94 V-2                      |

## Drawing

Measurements are shown in millimeters.  
Multiply by 0.03937 to convert to inches.



\* Please consider derating graph on page 80.



# Test Jacks 4 mm System



## PK 110

4mm insulated panel mount binding post with 2mm cross hole, nickel plated brass M4 thread terminal.



## PKI 110

4mm insulated panel mount binding post with 2mm cross hole, nickel plated brass, M4 thread terminal, max. panel thickness 3.5mm.

### Type

Pin Diameter

4 mm

PART NO. / Housing color

● 931713100  
● 931713101

4 mm

● 931714100  
● 931714101  
● 931714102  
● 931714103  
● 931714104  
● 931714188

### Technical Data

|                                 |                                |
|---------------------------------|--------------------------------|
| Contact Type                    | jack Ø 4 mm, cross hole Ø 2 mm |
| Connection Type                 | M4 thread terminal             |
| Voltage Rating                  | 30 VAC / 60 VDC                |
| Measurement Category (IEC61010) | CAT I                          |
| Current Rating*                 | 35 A                           |
| Contact Resistance              | 2 mOhm                         |
| Mounting Type                   | screw thread M4                |

### Material Specifications

|                |                     |
|----------------|---------------------|
| Jack Body      | nickel plated brass |
| Contact Spring | -                   |
| Housing        | Polyamide           |

### Environmental Conditions

|                   |                                 |
|-------------------|---------------------------------|
| Temperature Range | -25°C to +100 °C (-13 to 212°F) |
|-------------------|---------------------------------|

### Flamability Rating

|         |           |
|---------|-----------|
| Housing | UL 94 V-2 |
|---------|-----------|

|                                |
|--------------------------------|
| jack Ø 4 mm, cross hole Ø 2 mm |
| M4 thread terminal             |
| 30 VAC / 60 VDC                |
| CAT I                          |
| 35 A                           |
| 2 mOhm                         |
| screw thread M4                |

nickel plated brass

-



Polyamide

-25°C to +100 °C (-13 to 212°F)

UL 94 V-2

### Drawing

Measurements are shown in millimeters.  
Multiply by 0.03937 to convert to inches.



\* Please consider derating graph on page 80.

# Test Jacks 4 mm System



## Type

### PKI 100

4mm insulated panel mount binding post with 2mm cross hole, nickel plated brass, M4 thread terminal, max. panel thickness 3.5mm.

Pin Diameter

4 mm

PART NO. / Housing color

- 930757100
- 930757101
- 930757102
- 930757103
- 930757104
- 930757188



### PKI 10 A / PKI 10 A Au

4mm insulated panel mount binding post with 2mm cross hole, nickel/ gold plated brass, M4 thread terminal, max. panel thickness 2mm

4 mm

#### Nickel Plated

- 930103100
- 930103101
- 930103102
- 930103103
- 930103104
- 930103188

#### Gold Plated

- 930103700
- 930103701
- 930103702
- 930103703
- 930103704
- 930103788

## Technical Data

|                                 |                                |
|---------------------------------|--------------------------------|
| Contact Type                    | jack Ø 4 mm, cross hole Ø 2 mm |
| Connection Type                 | M4 thread terminal             |
| Voltage Rating                  | 30 VAC / 60 VDC                |
| Measurement Category (IEC61010) | CAT I                          |
| Current Rating*                 | 32 A                           |
| Contact Resistance              | 2 mOhm                         |
| Mounting Type                   | screw thread M4                |

### Material Specifications

|                |                     |
|----------------|---------------------|
| Jack Body      | nickel plated brass |
| Contact Spring | -                   |
| Housing        | Polyamide           |

### Environmental Conditions

|                   |                                 |
|-------------------|---------------------------------|
| Temperature Range | -25°C to +100 °C (-13 to 212°F) |
|-------------------|---------------------------------|

### Flamability Rating

|         |           |
|---------|-----------|
| Housing | UL 94 V-2 |
|---------|-----------|

|                                |
|--------------------------------|
| jack Ø 4 mm, cross hole Ø 2 mm |
| M 4 thread terminal            |
| 30 VAC / 60 VDC                |
| CAT I                          |
| 35 A                           |
| 2 mOhm                         |
| screw thread M4                |

nickel plated brass | gold plated brass

-



PF

-25°C to +100 °C (-13 to 212°F)

-

## Drawing

Measurements are shown in millimeters.  
Multiply by 0.03937 to convert to inches.



\* Please consider derating graph on page 80.



# Test Jacks 4 mm System

## Type

### PK 10 A

4mm insulated panel mount binding post with 2mm cross hole, nickel plated brass, M4 thread terminal



### PKN 10 B

4mm insulated panel mount binding post with 2.6mm cross hole, nickel plated brass, M6 thread terminal

Pin Diameter

4 mm

4 mm

PART NO. / Housing color

- 930099100
- 930099101
- 930099102
- 930099103
- 930099104
- 930099188

- 930117100
- 930117101

## Technical Data

Contact Type  
Connection Type  
Voltage Rating  
Measurement Category (IEC61010)  
Current Rating\*  
Contact Resistance  
Mounting Type

jack Ø 4 mm, cross hole Ø 2 mm  
M 4 thread terminal  
30 VAC / 60 VDC  
CAT I  
16 A  
2 mOhm  
screw thread M4

## Material Specifications

Jack Body  
Contact Spring  
Housing

nickel plated brass  
nickel  
PF

## Environmental Conditions

Temperature Range

-25°C to +100 °C (-13 to 212°F)

## Flamability Rating

Housing

-

jack Ø 4 mm, cross hole Ø 2,6 mm

M6 thread, solder terminal  
30 VAC / 60 VDC  
CAT I  
63 A  
2 mOhm  
screw thread M6



brass  
nickel plated nickel  
PF

-25°C to +100 °C (-13 to 212°F)

UL 94 HB

## Drawing

Measurements are shown in millimeters.  
Multiply by 0.03937 to convert to inches.



\* Please consider derating graph on page 80.



# Test Jacks 4 mm System



## Type

### PKNI 10 B

4mm insulated panel mount binding post with 2.6mm cross hole, nickel plated brass, M6 thread/ solder terminal, max. panel thickness 3.5mm

Pin Diameter

4 mm

PART NO. / Housing color

● 930136100

● 930136101



### PKNI 20 B

4mm insulated panel mount binding post with 2.6mm cross hole, nickel plated brass, M6 thread/ solder terminal, max. panel thickness 3.5mm

4 mm

● 930144100

● 930144101

## Technical Data

|                                 |                                  |
|---------------------------------|----------------------------------|
| Contact Type                    | jack Ø 4 mm, cross hole Ø 2.6 mm |
| Connection Type                 | M6 thread, solder terminal       |
| Voltage Rating                  | 30 VAC / 60 VDC                  |
| Measurement Category (IEC61010) | CAT I                            |
| Current Rating*                 | 63 A                             |
| Contact Resistance              | 2 mOhm                           |
| Mounting Type                   | screw thread M6                  |

## Material Specifications

|                |                     |
|----------------|---------------------|
| Jack Body      | nickel plated brass |
| Contact Spring | -                   |
| Housing        | PF                  |

## Environmental Conditions

|                   |                                 |
|-------------------|---------------------------------|
| Temperature Range | -25°C to +100 °C (-13 to 212°F) |
|-------------------|---------------------------------|

## Flamability Rating

|         |          |
|---------|----------|
| Housing | UL 94 HB |
|---------|----------|

jack Ø 4 mm, cross hole Ø 2.6 mm

|                            |
|----------------------------|
| M6 thread, solder terminal |
| 30 VAC / 60 VDC            |
| CAT I                      |
| 63 A                       |
| 2 mOhm                     |
| screw thread M6            |

nickel plated brass

-



PF

-25°C to +100 °C (-13 to 212°F)

UL 94 HB

## Drawing

Measurements are shown in millimeters.  
Multiply by 0.03937 to convert to inches.



\* Please consider derating graph on page 80.



# Test Jacks 4 mm System

Type

## KUN S

4mm Safety adapter, nickel plated brass with screw terminal 0.5-1.5mm2, IEC61010 1000V system



Pin Diameter

PART NO. / Housing color

4 mm

- 934096100
- 934096101
- 934096102
- 934096103
- 934096104

## SEB 2600 G M4

4mm panel mount safety Jack, touch proof, gold plated brass with M4 thread/ solder terminal, max. panel thickness 6mm



4 mm

- 972354100
- 972354101
- 972354102
- 972354103
- 972354104
- 972354105
- 972354106
- 972354107
- 972354109
- 972354188

### Technical Data

|                                 |                                        |
|---------------------------------|----------------------------------------|
| Contact Type                    | jack Ø 4 mm                            |
| Connection Type                 | screw terminal max. 1.5mm <sup>2</sup> |
| Voltage Rating                  | AC/DC 1000 V                           |
| Measurement Category (IEC61010) | CAT III                                |
| Current Rating*                 | 24 A                                   |
| Contact Resistance              | –                                      |
| Mounting Type                   | –                                      |

### Material Specifications

|                |                     |
|----------------|---------------------|
| Jack Body      | nickel plated brass |
| Contact Spring | –                   |
| Housing        | Polyamide           |

### Environmental Conditions

|                   |                             |
|-------------------|-----------------------------|
| Temperature Range | -15°C to +70°C (5 to 158°F) |
|-------------------|-----------------------------|

### Flamability Rating

|         |           |
|---------|-----------|
| Housing | UL 94 V-2 |
|---------|-----------|

jack Ø 4 mm

|                            |
|----------------------------|
| M4 thread, solder terminal |
| AC/DC 1000 V               |
| CAT III                    |
| 32 A                       |
| 5 mOhm                     |
| screw thread M12           |

gold plated brass



|           |
|-----------|
| –         |
| Polyimide |

-40°C to +80°C (-40 to 176°F)

UL 94 V-2

### Drawing

Measurements are shown in millimeters.  
Multiply by 0.03937 to convert to inches.



\* Please consider derating graph on page 80.

# Test Jacks 4 mm System



## Type

### SEB 2610 F4,8

4mm panel mount safety Jack, touch proof, gold plated brass with flat 4.8x0.8mm DIN46244 terminal, max. panel thickness 6mm

Pin Diameter

PART NO. / Housing color

4 mm

- 972355100
- 972355101
- 972355102
- 972355103
- 972355104
- 972355105
- 972355106
- 972355107
- 972355109
- 972355188



### SEB 2620 F6,3

4mm panel mount safety Jack, touch proof, gold plated brass with flat 6.3x0.8mm DIN46244 terminal, max. panel thickness 6mm

4 mm

- 972356100
- 972356101
- 972356102
- 972356103
- 972356104
- 972356105
- 972356106
- 972356107
- 972356109
- 972356188



## Technical Data

|                                 |                               |
|---------------------------------|-------------------------------|
| Contact Type                    | jack Ø 4 mm                   |
| Connection Type                 | flat 4.8 x 0.8 mm tab         |
| Voltage Rating                  | AC/DC 1000 V                  |
| Measurement Category (IEC61010) | CAT III                       |
| Current Rating*                 | 25 A                          |
| Contact Resistance              | 5 mOhm                        |
| Mounting Type                   | screw thread M12              |
| <b>Material Specifications</b>  |                               |
| Jack Body                       | gold plated brass             |
| Contact Spring                  | -                             |
| Housing                         | Polyamide                     |
| <b>Environmental Conditions</b> |                               |
| Temperature Range               | -40°C to +80°C (-40 to 176°F) |
| <b>Flamability Rating</b>       |                               |
| Housing                         | UL 94 V-2                     |

|                                 |                               |
|---------------------------------|-------------------------------|
| Contact Type                    | jack Ø 4 mm                   |
| Connection Type                 | flat 6.3 x 0.8 mm tab         |
| Voltage Rating                  | AC/DC 1000 V                  |
| Measurement Category (IEC61010) | CAT III                       |
| Current Rating*                 | 32 A                          |
| Contact Resistance              | 5 mOhm                        |
| Mounting Type                   | screw thread M12              |
| <b>Material Specifications</b>  |                               |
| Jack Body                       | gold plated brass             |
| Contact Spring                  | -                             |
| Housing                         | Polyamide                     |
| <b>Environmental Conditions</b> |                               |
| Temperature Range               | -40°C to +80°C (-40 to 176°F) |
| <b>Flamability Rating</b>       |                               |
| Housing                         | UL 94 V-2                     |

## Drawing

Measurements are shown in millimeters.  
Multiply by 0.03937 to convert to inches.



\* Please consider derating graph on page 80.



# Test Jacks 4 mm System



## SEB 2630 S1,9

4mm panel mount safety Jack, touch proof, gold plated brass with soldering pin 1.9mm, max. panel thickness 6mm



## MW SEB

Installation tool for 4mm panel mount safety jacks.

Type

Pin Diameter  
PART NO. / Housing color

- 4 mm
- 972359100
  - 972359101
  - 972359102
  - 972359103
  - 972359104
  - 972359105
  - 972359106
  - 972359107
  - 972359109
  - 972359188

- 4 mm
- 973929000

### Technical Data

|                                 |                  |
|---------------------------------|------------------|
| Contact Type                    | jack Ø 4 mm      |
| Connection Type                 | solder pin 1.9mm |
| Voltage Rating                  | AC/DC 1000 V     |
| Measurement Category (IEC61010) | CAT III          |
| Current Rating*                 | 24 A             |
| Contact Resistance              | 5 mOhm           |
| Mounting Type                   | screw thread M12 |

### Material Specifications

|                |                   |
|----------------|-------------------|
| Jack Body      | gold plated brass |
| Contact Spring | -                 |
| Housing        | Polyamide         |

### Environmental Conditions



|                   |                               |
|-------------------|-------------------------------|
| Temperature Range | -40°C to +80°C (-40 to 176°F) |
|-------------------|-------------------------------|

### Flamability Rating

|         |           |
|---------|-----------|
| Housing | UL 94 V-2 |
|---------|-----------|

### Drawing

Measurements are shown in millimeters.  
Multiply by 0.03937 to convert to inches.



\* Please consider derating graph on page 80.



# Test Jacks 4 mm System

## Type

Pin Diameter

PART NO. / Housing color



### SEP 2610 F4,8

Safety press-in socket, 4 mm diameter, contact-protected, with 4.8 x 0.8 tab connector complying with DIN 46 244, gold-plated brass. For rapid installation into switch panels with wall thicknesses between 1-10 mm. Installation hole: 12.2 +/- 0.1 mm diameter. Entry chamfer: 0.5 x 45 degree.

2 mm

- 972361100
- 972361101
- 972361102
- 972361103
- 972361104
- 972361188



### SEP 2620 F6,3

Safety press-in socket, 4 mm diameter, contact-protected, with 6.3 x 0.8 tab connector complying with DIN 46244, gold-plated brass. For rapid installation into switch panels with wall thicknesses between 1-10 mm. Installation hole: 12.2 +/- 0.1 mm diameter. Entry chamfer: 0.5 x 45 degree.

2 mm

- 972362100
- 972362101
- 972362102
- 972362103
- 972362104
- 972362188



### SEP 2630 S1,9

Gold-plated brass safety press-in socket, 4 mm diameter, contact-protected, with 1.9 mm soldering spike. For installation into switch panels with wall thicknesses between 1 mm and 10 mm. Installation hole: 12.2 +/- 0.1 mm diameter. Entry chamfer: 0.5 x 45 degree.

2 mm

- 972363100
- 972363101
- 972363102
- 972363103
- 972363104
- 972363188

## Technical Data

Contact Type jack Ø 4 mm

Connection Type flat 4.8 x 0.8 mm tab

Voltage Rating AC/DC 1000 V

Measurement Category (IEC61010) CAT III

Current Rating\* 24 A

Contact Resistance 5 mOhm

Mounting Type press in

### Material Specifications

Jack Body gold plated brass

Contact Spring -

Housing PA

### Environmental Conditions

Temperature Range -40°C to +80°C (-40 to 176°F)

### Flamability Rating

Housing UL 94 V-2

jack Ø 4 mm

flat 6.3 x 0.8 mm tab

AC/DC 1000 V

CAT III

32 A

5 mOhm

press in

gold plated brass

-

PA

-40°C to +80°C (-40 to 176°F)

UL 94 V-2

jack Ø 4 mm

solder pin 1.9mm

AC/DC 1000V

CAT III

24 A

5 mOhm

press in

gold plated brass

-




PA

-40°C to +80°C (-40 to 176°F)

UL 94 V-2

## Drawing

Measurements are shown in millimeters.  
Multiply by 0.03937 to convert to inches.



\* Please consider derating graph on page 80.

# Test & Measurement Sets



Altech offers a variety of Test & Measurement Sets consisting of suitable components for certain System Types and specific applications. Comprehensive Service cases include extensive line of products for in-field installation, testing and service.

- 0.64 System
- 2mm System
- 4mm System
- 4mm Retractable Sleeve System
- 4mm Safety System
- Automobile Test Kit
- Service cases for Electronic or Electrical applications





Type  
**PART No.**  
**Description**

**PMS 0.64**  
**932959001**

Micro Test Equipment Set for SMD Components and 0.64mm systems.

- 1 x Plunger Style Test Probe MICRO-KLEPS black 973972100
- 1 x Plunger Style Test Probe MICRO-KLEPS red 973972101
- 1 x Test Probe MICRO-PRUEF MPS 2/0,64 FT black 973995100
- 1 x Test Probe MICRO-PRUEF MPS 2/0,64 FT red 973995101
- 1 x Alligator Clip AGF 1 930476001
- 1 x Measuring Lead MAL N 4-0,64/100-0,25 black 934160100
- 1 x Measuring Lead MAL N 4-0,64/100-0,25 red 934160101



Type  
**PART No.**  
**Description**

**PMS 2**  
**932961001**

Test Equipment Set for 2mm systems.

- 1 x Plunger Style Test Probe KLEPS 2 BU black 973501100
- 1 x Plunger Style Test Probe KLEPS 2 BU red 973501101
- 1 x Test Probe MPS 1 black 973531100
- 1 x Test Probe MPS 1 red 973531101
- 1 x Alligator Clip MA 1 black 930317800
- 1 x Alligator Clip MA 1 red 930317801
- 1 x Measuring Lead MVL 2/100 black 973596100
- 1 x Measuring Lead MVL 2/100 red 973596101



Type  
**PART No.**  
**Description**

**PMS 2 S LMLH**  
**975604001**

Laboratory Test Holder with 10 measuring leads in various colors for 2mm safety system.

- 1 x Test Lead Holder LMLH 973919001
- 2 x Test Lead MVL S WS 100/1 AU black 975696700
- 2 x Test Lead MVL S WS 100/1 AU red 975696701
- 2 x Test Lead MVL S WS 100/1 AU blue 975696702
- 2 x Test Lead MVL S WS 100/1 AU yellow 975696703
- 2 x Test Lead MVL S WS 100/1 AU green 975696704



Type  
**PART No.**  
**Description**

**PMS 4**  
**932793001**

Test Equipment Set for 4mm systems.

- 1 x Plunger Style Test Probe KLEPS 30 black 930113100
- 1 x Plunger Style Test Probe KLEPS 30 red 930113101
- 1 x Test Probe PRUEF 2 black 973368100
- 1 x Test Probe PRUEF 2 red 973368101
- 1 x Alligator Clip AK 2 S black 932146100
- 1 x Alligator Clip AK 2 S red 932146101
- 1 x Measuring Lead MLN 100/1 black 934062100
- 1 x Measuring Lead MLN 100/1 red 934062101



# Test & Measurement Sets



Type  
PART No.  
Description



## PMS 4 KFZ 933003001

Test Equipment Set for Automobiles, Service and repair shops.

- 1 x Safety Plunger Style Test Probe KLEPS 2700 black 972307100
- 1 x Safety Plunger Style Test Probe KLEPS 2700 red 972307101
- 1 x Test Probe PRUEF 2610 FT black 972318100
- 1 x Test Probe PRUEF 2610 FT red 972318101
- 1 x Safety Alligator Clip AK 2 B 2540 I black 972405100
- 1 x Safety Alligator Clip AK 2 B 2540 I red 972405101
- 1 x Silicone Test Lead MLN SIL 150/1 black 934093100
- 1 x Silicone Test Lead MLN SIL 150/1 red 934093101

Type  
PART No.  
Description

## PMS 4 SKS 932794001

Test Equipment Set for 4mm systems.



- 1 x Measuring Lead MLN 50/1 black 934060100
- 1 x Measuring Lead MLN 50/1 red 934060101
- 2 x Measuring Lead MLN 100/1 black 934062100
- 2 x Measuring Lead MLN 100/1 red 934062101
- 1 x Measuring Lead MLN 200/1 black 934065100
- 1 x Measuring Lead MLN 200/1 red 934065101
- 1 x Plunger Style Test Probe KLEPS 30 black 930113100
- 1 x Plunger Style Test Probe KLEPS 30 red 930113101
- 1 x Alligator Clip AK 2 S black 932146100
- 1 x Alligator Clip AK 2 S red 932146101
- 1 x Test Probe PRUEF 2 black 973368100
- 1 x Test Probe PRUEF 2 red 973368101

Type  
PART No.  
Description

## PMS 4 LMLH 972604001

Laboratory Test Holder with 10 measuring leads in various colors for 4mm safety system.



- 1 x Test Lead Holder LMLH 973919001
- 2 x Test Lead MLN 100/1 black 934062100
- 2 x Test Lead MLN 100/1 red 934062101
- 2 x Test Lead MLN 100/1 blue 934062102
- 2 x Test Lead MLN 100/1 yellow 934062103
- 2 x Test Lead MLN 100/1 green 934062104

Type  
PART No.  
Description

## PMS 250 932827001

Sliding Sleeve Test Equipment Set for 4mm systems.



- 1 x Plunger Style Test Probe KLEPS 250 black 973528100
- 1 x Plunger Style Test Probe KLEPS 250 red 973528101
- 1 x Test Probe PRUEF 2 S black 973659100
- 1 x Test Probe PRUEF 2 S red 973659101
- 1 x Alligator Clip AK 2 B black 932435100
- 1 x Alligator Clip AK 2 B red 932435101
- 1 x Measuring Lead MLB 100/1 V black 973646100
- 1 x Measuring Lead MLB 100/1 V red 973646101





Type  
**PART No.**  
Description

**PMS PMS 2600**  
**972338001**

Test Equipment Set Safety Applications for 4mm system (Accessory for measuring instruments)

- 1 x Plunger Style Test Probe KLEPS 2600 black 972306100
- 1 x Plunger Style Test Probe KLEPS 2600 red 972306101
- 1 x Test Probe PRUEF 2600 black 972317100
- 1 x Test Probe PRUEF 2600 red 972317101
- 1 x Alligator Clip AK 2 B black 932435100
- 1 x Alligator Clip AK 2 B red 932435101
- 1 x Measuring Lead MLS GG 100/1 black 934074100
- 1 x Measuring Lead MLS GG 100/1 red 934074101



Type  
**PART No.**  
Description

**PL 2600 S Set**  
**972337002**

Test Probe Set for measuring devices with straight connectors.

- 1 x Measuring Lead PL 2600 S black 934159100
- 1 x Measuring Lead PL 2600 S red 934159101



Type  
**PART No.**  
Description

**PL 2600 S W Set**  
**972425002**

Test Probe Set for measuring devices with angled connectors.

- 1 x Measuring Lead PL 2600 S W black 934158100
- 1 x Measuring Lead PL 2600 S W red 934158101



Type  
**PART No.**  
Description

**MMS 2010**  
**972339001**

Test Equipment Set for Safety Applications – Plunger Test Clips KLEPS 2800, Test probes, Measuring Leads.

- 1 x Safety Plunger Style Test Probe KLEPS 2800 black 972308100
- 1 x Safety Plunger Style Test Probe KLEPS 2800 red 972308101
- 1 x Safety Test Probe PRUEF 2700 black 972319100
- 1 x Safety Test Probe PRUEF 2700 red 972319101
- 1 x Safety Test Lead MLS WG 100/1 black 934082100
- 1 x Safety Test Lead MLS WG 100/1 red 934082101



Type  
**PART No.**  
Description

**MMS 2020**  
**972340001**

Test Equipment Set for Safety Applications – Alligator Clips, Test probes, Measuring Leads.

- 1 x Safety Alligator Clip AK 2 B 2540 I black 972405100
- 1 x Safety Alligator Clip AK 2 B 2540 I red 972405101
- 1 x Safety Test Probe PRUEF 2700 black 972319100
- 1 x Safety Test Probe PRUEF 2700 red 972319101
- 1 x Safety Test Lead MLS WG 100/1 black 934082100
- 1 x Safety Test Lead MLS WG 100/1 red 934082101

# Test & Measurement Sets



Type  
PART No.  
Description



## MMS 2030 972341001

Test Equipment Set for Safety Applications – Plunger Test Clips KLEPS 2600, Test probes, Measuring Leads.

- 1 x Safety Test Probe PRUEF 2700 black 972319100
- 1 x Safety Test Probe PRUEF 2700 red 972319101
- 1 x Plunger Style Test Probe KLEPS 2600 black 972306100
- 1 x Plunger Style Test Probe KLEPS 2600 red 972306101
- 1 x Safety Test Lead MLS WG 100/1 black 934082100
- 1 x Safety Test Lead MLS WG 100/1 red 934082101

Type  
PART No.  
Description



## MMS 2040 972342100

Test Equipment Set for Safety Applications – Plunger Test Clips KLEPS 2600, Alligator Clips, Measuring Leads.

- 1 x Plunger Style Test Probe KLEPS 2600 black 972306100
- 1 x Plunger Style Test Probe KLEPS 2600 red 972306101
- 1 x Alligator Clip AK 2 B black 932435100
- 1 x Alligator Clip AK 2 B red 932435101
- 1 x Measuring Lead PL 2600 S black 934159100
- 1 x Measuring Lead PL 2600 S red 934159101
- 1 x Safety Test Lead MLS WG 100/1 black 934082100
- 1 x Safety Test Lead MLS WG 100/1 red 934082101

Type  
PART No.  
Description



## PMS SKS Safety 932795001

Safety Test Equipment Set – Plunger Test Clips KLEPS 2600, Alligator Clips, Test Leads.

- 1 x Plunger Style Test Probe KLEPS 2600 black 972306100
- 1 x Plunger Style Test Probe KLEPS 2600 red 972306101
- 1 x Test Probe PRUEF 2600 black 972317100
- 1 x Test Probe PRUEF 2600 red 972317101
- 1 x Alligator Clip AK 2 B black 932435100
- 1 x Alligator Clip AK 2 B red 932435101
- 1 x Test Lead MLS WS 50/1 black 934068100
- 1 x Test Lead MLS WS 50/1 red 934068101
- 2 x Test Lead MLS WS 100/1 black 934095100
- 2 x Test Lead MLS WS 100/1 red 934095101
- 1 x Test Lead MLS WS 200/1 black 934069100
- 1 x Test Lead MLS WS 200/1 red 934069101

Type  
PART No.  
Description



## PMS 4 S LMLH 972605001

Laboratory Test Holder with 10 measuring leads in various colors for 4mm safety system.

- 1 x Test Lead Holder LMLH 973919001
- 2 x Test Lead MLS WS 100/1 black 934095100
- 2 x Test Lead MLS WS 100/1 red 934095101
- 2 x Test Lead MLS WS 100/1 blue 934095102
- 2 x Test Lead MLS WS 100/1 yellow 934095103
- 2 x Test Lead MLS WS 100/1 green 934095104



Type  
PART No.  
Description

**PMS SKS Elektronik**  
**932791001**  
Service Case Electronic

1 x Safety Test Probe PRUEF 2610 FT black 972318100  
1 x Safety Test Probe PRUEF 2610 FT red 972318101  
1 x Test Probe MICRO-PRUEF MPS 2/0,64 FT black 973995100  
1 x Test Probe MICRO-PRUEF MPS 2/0,64 FT red 973995101  
1 x Plunger Style Test Probe MICRO-KLEPS black 973972100  
1 x Plunger Style Test Probe MICRO-KLEPS red 973972101  
1 x Mini Alligator Clip KLEPS 064 PCH black 974201100  
1 x Mini Alligator Clip KLEPS 064 PCH red 974201101  
1 x Mini Alligator Clip KLEPS 064 PCH blue 974201102  
1 x Mini Alligator Clip KLEPS 064 PCH yellow 974201103  
1 x Mini Alligator Clip KLEPS 064 PCH green 974201104  
1 x Mini Alligator Clip KLEPS 064 PCH gray 974201106  
1 x Mini Alligator Clip KLEPS 064 PCH white 974201107  
1 x Adapter MZS 4 black 973599100  
1 x Adapter MZS 4 red 973599101  
1 x 2 pole Test Clip MICRO-SMD CLIP 1 972416100  
1 x Mini Alligator Clip MA 260 SH black 973889100  
1 x Mini Alligator Clip MA 260 SH red 973889101  
1 x Alligator Clip AK 2 B 2540 I yellow-green 972405188  
1 x Test Lead MLS WS 50/2,5 black 934087100  
1 x Test Lead MLS WS 50/2,5 red 934087101  
1 x Test Lead MLS WS 50/2,5 yellow-green 934087188  
1 x Measuring Lead MAL N 4-0,64/100-0,25 black 934160100  
1 x Measuring Lead MAL N 4-0,64/100-0,25 red 934160101  
1 x Test Lead MKL 0,64/25-0,25 black 973604100  
1 x Test Lead MKL 0,64/25-0,25 red 973604101  
1 x Adapter BNC AL 0,64 black 933844001  
1 x Passive Divider Probe TKO 5 – PMS 221 A 974312000  
1 x 2 foot positioner for oscilloscope test probes 974401000

# Test & Measurement Sets



**Type**  
**PART No.**  
**Description**

## **PMS SKS Electrical** **932791001**

Service Case Electric (Industrial, Utility Management, Training, etc...)

- 1 x Plunger Style Test Probe KLEPS 2 BU black 973501100
- 1 x Plunger Style Test Probe KLEPS 2 BU red 973501101
- 1 x Test Probe PRUEF 2600 black 972317100
- 1 x Test Probe PRUEF 2600 red 972317101
- 1 x Safety Test Probe PRUEF 2700 black 972319100
- 1 x Safety Test Probe PRUEF 2700 red 972319101
- 1 x Safety Plunger Style Test Probe KLEPS 2800 black 972308100
- 1 x Safety Plunger Style Test Probe KLEPS 2800 red 972308101
- 1 x Adapter MZS 4 black 973599100
- 1 x Adapter MZS 4 red 973599101
- 1 x Test Lead MLS WS 25/2,5 black 934086100
- 1 x Test Lead MLS WS 25/2,5 red 934086101
- 1 x Test Lead MLS WS 200/2,5 black 934089100
- 1 x Test Lead MLS WS 200/2,5 red 934089101
- 1 x Test Lead MLS WS 520/2,5 black 934089188
- 1 x Alligator Clip AK 2 B 2540 I yellow-green 972405188
- 1 x Test Lead MVL 2/50 black 973595100
- 1 x Test Lead MVL 2/50 red 973595101
- 1 x Adapter MZS 2 black 973600100
- 1 x Adapter MZS 2 red 973600101





# Test & Measurement Glossary

## Clearance Distance

Clearance Distance is the directly measured distance between two conducting parts, acts as an insulator and should be dimensioned according to IEC 61010.

## Contact Material

Contact Material is the base Material of the part.

## Contact Resistance

Contact Resistance is the resistance measured between the connections of connected contact parts. It consists of resistivity and contact-circuit resistance. Given values are according to DIN EN 60512.

## Contact Surface Material

Contact Surface Material is the material on the surface of the electrical contact. For Test & Measurement purposes special nickel or gold plating is used for ideal electrical and mechanical conditions.

## Creepage Distance

Creepage Distance is the shortest path between two conductive parts (or between a conductive part and the bounding surface of the equipment) measured along the surface of the insulation. It is defined in IEC 61010.

## Pollution Degree Rating

The pollution degree is the numerical index of the degree of pollution that can exist in the environment. IEC/EN 61010-031 defines 3 Pollution Degrees:

*Pollution Degree 1:* No pollution or only dry, non-conductive pollution occurs. The pollution has no influence.


Example: Inside closed pieces of equipment.

*Pollution Degree 2:* Normally only non-conductive pollution occurs. Occasionally, however, a temporary conductivity caused by condensation is to be expected. Examples: Laboratory, light industry.

*Pollution Degree 3:* Conductive pollution occurs, or dry non-conductive pollution, which becomes conductive due to condensation, is to be expected. Examples: Heavy industry, short service outdoors.

## Derating Curve

According to the derating Curve (load reduction curve acc. to DIN EN 60512-5-2), the operating current at higher ambient temperatures is reduced. The current loading capacity of measurement accessories is limited by the thermal load-bearing capacity of the contact material or insulating parts and by the upper temperature limit of measurement accessories acc. to IEC 61010. Therefore, the derating graph applies as a function of environmental temperature to currents that may continuously pass through each contact element without exceed the upper temperature limit.



The derating graph describes the relation between currents, thereby caused increase of temperature (power loss on contact resistance) and environmental temperature of the measurement accessory. The Graph ends with the upper temperature limit of the measurement accessory. Upper temperature limits for measurement accessories are according to IEC 61010:

Non-metallic Material 70C (158F), Metallic Material 55C (131F)

GRAPH from Hirschmann Catalog

## Handle Area

The Handle Area is the area in which the user can touch a measuring device during operation without being exposed to electrical currents.

## IEC 61010-31

Title of the IEC/EN 61010:

“Safety requirements for electrical equipment for measurement, control and laboratory use”

Part 031:

“Safety requirements for hand-held probe assemblies for electrical measurement and test”

All products of the Hirschmann Test & Measurement Range are designed and approved according to this standard.

## Insulation

*Basic insulation* - is the insulation applied to live parts to provide basic protection against electric shock, eg. the failure of the basic insulation could cause the risk of electric shock.


*Double insulation* - Insulation comprising both basic insulation and supplementary insulation.

*Reinforced insulation* - Insulation which provides protection against electric shock not less than that provided by double insulation.

## Measurement Categories acc. to IEC 61010-031

To facilitate the assignment of test accessories to the appropriate applications, standard IEC 61010-031 has established a number of categories which define where they can be used in the power supply network and to lay down appropriate requirements for each category.

In standard EN 61010-031 there are four different test categories, abbreviated "CAT". The category CAT followed by a number from I to IV is stated in our catalog with the rated voltage. As a general rule, the higher the CAT rating, the higher the safety requirement that applies to the product.



### CAT I

Applies to test objects that are not connected to the mains. E.g. electronic devices, batteries, etc. in which only minor over voltages occur.

CAT I will also include all test objects that cannot be assigned to CAT II to CAT IV.

### CAT II

Applies to measurements on equipment that is connected to the mains or supplied from the mains without constituting a part of the mains installation. Electrical equipment between appliance and power socket, or inside electrical equipment such as domestic appliances.

### CAT III

Applies to measurements inside the house or building installation. Installations in buildings, contactors, protective devices, switches, power sockets (Electricians).

### CAT IV

Applies to measurements at the supply source of the installation (input side). Secondary side of medium-voltage transformers, electricity meters, cable networks, connection to overhead lines (employees of power distribution companies).

## Current Rating

The rated current is the current which the test & measurement devices can carry continuously without the temperature exceeding the upper limit.

## Voltage Rating

Voltage Rating is the voltage at which the product can be used safely, if used properly. The specified rated voltage always relates to Pollution Degree 2. Each Voltage also refers to the appropriate Measuring Category.

## Safety Color Indicator

All the measuring leads of the 2 mm & 4 mm safety system have a safety colour indicator. The cable insulation consists of two separated insulation layers. The first layer is directly installed on the conductor and it is white in all measuring leads (except of white ones >red colour indicator). In a subsequent manufacturing stage, a second insulation layer is applied in the respective cable colour. If the insulation is damaged while using the measuring lead, the first insulating layer becomes visible. For safety reasons, the lead should be immediately replaced with a new SKS measuring lead.

## Sliding Sleeve System

The Sliding Sleeve System has a retraceable protective insulation to avoid short circuits and electric shocks while not connected. It is not allowed to use this system for dangerous voltages during use. Adapter test leads for the connection to equipment that (still) cannot take fully insulated plugs are an exception. For this reason the Sliding Sleeve System is classified according to IEC 61010, CAT I up to 60V.

## Temperature range (environmental conditions)

The temperature range is the allowed range in which the products may be used without damaging the materials.

## Voltage details

The voltage details for the products mentioned in the catalog indicate the voltage range for which they can be used. SKS has designed the entire 2 mm & 4 mm safety system, unless otherwise specified, for 1,000V, Measurement Category III (CAT III) with Pollution Degree 2. The largest range of measuring tasks in the higher voltage range is safely covered.

# Index By Type Number

| Type No.      | Part No.  | Page |
|---------------|-----------|------|
| AGF 1         | 930476001 | 21   |
| AGF 2         | 9312721xx | 23   |
| AGF 20        | 930120000 | 23   |
| AGF 30        | 930122000 | 23   |
| AGS 20        | 603006001 | 24   |
| AK 10         | 9301261xx | 24   |
| AK 2 B 2540 I | 9724051xx | 25   |
| AK 2 B        | 9324351xx | 25   |
| AK 2 S        | 9321461xx | 24   |
| BIL 20        | 9301761xx | 62   |
| BIL 20 Au     | 9301767xx | 62   |
| BIL 30        | 930166100 | 63   |
| BIL 30 Au     | 9301667xx | 63   |
| BNC AL 0,64   | 933844001 | 27   |
| BO 10         | 930160000 | 61   |
| BSB 20 K      | 9307291xx | 47   |
| BSB 300       | 9312941xx | 48   |
| BU 10         | 930147000 | 61   |
| BU 10 Au      | 930147700 | 61   |
| BU 20         | 930177000 | 62   |
| BUELA 20 K    | 9307261xx | 45   |
| BUELA 30 K    | 9307271xx | 46   |
| BUELA 300 K   | 9316671xx | 46   |
| BUG 10        | 9301751xx | 63   |
| BUG 10 Au     | 9301757xx | 63   |
| KB 2          | 9305841xx | 44   |
| KD 10         | 9301091xx | 60   |
| KLEPS 064 PCH | 9742011xx | 6    |
| KLEPS 2       | 9314671xx | 7    |
| KLEPS 2 BU    | 9735011xx | 7    |
| KLEPS 250     | 9735281xx | 9    |
| KLEPS 1600    | 9751061xx | 8    |
| KLEPS 2600    | 9723061xx | 9    |
| KLEPS 2700    | 9723071xx | 10   |
| KLEPS 2800    | 9723081xx | 10   |
| KLEPS 2900    | 9723091xx | 10   |
| KLEPS 60      | 9730531xx | 8    |
| KLEPS 3 ST    | 9735921xx | 5    |
| KLEPS 30      | 9301131xx | 8    |
| KLEPS FP 2B   | 974101188 | 6    |
| KST S WS      | 9322001xx | 53   |
| KUN 10        | 9301891xx | 60   |
| KUN 30        | 9318041xx | 59   |
| KUN 30 Au     | 9318047xx | 59   |
| KUN S         | 9340961xx | 68   |
| LAS 30        | 9725181xx | 45   |
| LAS 30 Au     | 9725187xx | 45   |
| LAS N WS      | 9341001xx | 47   |
| LAS N WS Au   | 9341007xx | 47   |
| LAS S G       | 9340971xx | 53   |
| LAS S W       | 9340981xx | 52   |
| LAS S WS      | 9340991xx | 53   |
| LMLH 50       | 973919001 | 38   |

| Type No.                  | Part No.  | Page |
|---------------------------|-----------|------|
| MA 1                      | 9303178xx | 22   |
| MA 1 Crimp                | 9303181xx | 22   |
| MA 1 S                    | 9735841xx | 22   |
| MA 260 SH                 | 9738891xx | 25   |
| MAL N 4-0,64/100-0,25     | 9341601xx | 27   |
| MAL S WS 2-4 100/1        | 9751631xx | 28   |
| MBI 1                     | 9303081xx | 55   |
| MBI 1 Au                  | 9303087xx | 55   |
| MBU 1                     | 930312000 | 56   |
| MBU 2                     | 931337000 | 56   |
| MICRO-KLEPS               | 9739721xx | 5    |
| MICRO-PRUEF MPS 2 0,64 FT | 9739951xx | 13   |
| MICRO-SMD CLIP 1          | 972416100 | 21   |
| MKL 0,64/25-0,25          | 9736041xx | 27   |
| MKU 1                     | 9303201xx | 55   |
| MLB 25/1 V                | 9736441xx | 31   |
| MLB 50/1 V                | 9736451xx | 31   |
| MLB 100/1 V               | 9736461xx | 31   |
| MLB 200/1 V               | 9736471xx | 31   |
| MLN 25/1                  | 9340581xx | 32   |
| MLN 25/2,5                | 9340591xx | 33   |
| MLN 25/2,5 Au             | 9340597xx | 33   |
| MLN 50/1                  | 9340601xx | 32   |
| MLN 50/2,5                | 9340611xx | 33   |
| MLN 50/2,5 Au             | 9340617xx | 33   |
| MLN 100/1                 | 9340621xx | 32   |
| MLN 100/2,5               | 9340631xx | 33   |
| MLN 100/2,5 Au            | 9340637xx | 33   |
| MLN 150/1                 | 9340641xx | 32   |
| MLN 150/2,5               | 9345071xx | 33   |
| MLN 150/2,5 Au            | 9345077xx | 33   |
| MLN 200/1                 | 9340651xx | 32   |
| MLN 200/2,5               | 9340661xx | 33   |
| MLN 200/2,5 Au            | 9340667xx | 33   |
| MLN SIL 25/1              | 9340901xx | 30   |
| MLN SIL 50/1              | 9340911xx | 30   |
| MLN SIL 100/1             | 9340921xx | 30   |
| MLN SIL 150/1             | 9340931xx | 30   |
| MLN SIL 200/1             | 9340941xx | 30   |
| MLS GG 25/1               | 9340701xx | 34   |
| MLS GG 25/2,5             | 9340711xx | 34   |
| MLS GG 50/1               | 9340721xx | 34   |
| MLS GG 50/2,5             | 9340731xx | 34   |
| MLS GG 100/1              | 9340741xx | 34   |
| MLS GG 100/2,5            | 9340751xx | 34   |
| MLS GG 200/1              | 9340761xx | 34   |
| MLS GG 200/2,5            | 9340771xx | 34   |
| MLS WG 25/1               | 9340781xx | 35   |
| MLS WG 25/2,5             | 9340791xx | 35   |
| MLS WG 50/1               | 9340801xx | 35   |
| MLS WG 50/2,5             | 9340811xx | 35   |
| MLS WG 100/1              | 9340821xx | 35   |
| MLS WG 100/2,5            | 9340831xx | 35   |



# Index By Type Number

| Type No.          | Part No.  | Page |
|-------------------|-----------|------|
| MLS WG 200/1      | 9340841xx | 35   |
| MLS WG 200/2,5    | 9340851xx | 35   |
| MLS WS 25/1       | 9340671xx | 36   |
| MLS WS 25/2,5     | 9340861xx | 36   |
| MLS WS 50/1       | 9340681xx | 36   |
| MLS WS 50/2,5     | 9340871xx | 36   |
| MLS WS 100/1      | 9340951xx | 36   |
| MLS WS 100/2,5    | 9340881xx | 36   |
| MLS WS 200/1      | 9340691xx | 36   |
| MLS WS 200/2,5    | 9340891xx | 36   |
| MMS 2010          | 972339001 | 75   |
| MMS 2020          | 972340001 | 75   |
| MMS 2030          | 972341001 | 76   |
| MMS 2040          | 972342001 | 76   |
| MPB 1             | 9302241xx | 57   |
| MPK 1             | 9302681xx | 57   |
| MPS 1             | 9735311xx | 14   |
| MSEB 2600 G M3 Au | 9754547xx | 58   |
| MSEB 2610 F2,8 Au | 9754557xx | 58   |
| MSEB 2630 S1,9 Au | 9754597xx | 58   |
| MST 201           | 931338001 | 41   |
| MST 3             | 9735091xx | 41   |
| MST S WS 30 Au    | 9750907xx | 42   |
| MVL 2/25          | 9735941xx | 28   |
| MVL 2/50          | 9735951xx | 28   |
| MVL 2/100         | 9735961xx | 28   |
| MVL S WS 25/1 Au  | 9756947xx | 29   |
| MVL S WS 50/1 Au  | 9756957xx | 29   |
| MVL S WS 100/1 Au | 9756967xx | 29   |
| MVL S WS 200/1 Au | 9756977xx | 29   |
| MW SEB            | 973929000 | 70   |
| MZS 1 - PRUEF     | 9736011xx | 15   |
| MZS 2             | 9736001xx | 42   |
| MZS 4             | 9735991xx | 44   |
| PB 4              | 9735821xx | 59   |
| PK 10 A           | 9300991xx | 66   |
| PK 110            | 9317131xx | 64   |
| PKI 10 A          | 9301031xx | 65   |
| PKI 10 A Au       | 9301037xx | 65   |
| PKI 100           | 9307571xx | 65   |
| PKI 110           | 9317141xx | 64   |
| PKN 10 B          | 9301171xx | 66   |
| PKNI 10 B         | 9301361xx | 67   |
| PKNI 20 B         | 9301441xx | 67   |
| PL 2600 S         | 9341591xx | 37   |
| PL 2600 S Set     | 972337002 | 75   |
| PL 2600 S W       | 9341581xx | 37   |
| PL 2600 S W Set   | 972425002 | 75   |
| PMS 0,64          | 932959001 | 73   |
| PMS 2             | 932961001 | 73   |
| PMS 2 S LMLH      | 975604001 | 73   |
| PMS 250           | 932827001 | 74   |
| PMS 2600          | 972338001 | 75   |

| Type No.                    | Part No.  | Page |
|-----------------------------|-----------|------|
| PMS 4                       | 932793001 | 73   |
| PMS 4 KFZ                   | 933003001 | 74   |
| PMS 4 LMLH                  | 972604001 | 74   |
| PMS 4 S LMLH                | 972605001 | 76   |
| PMS SKS                     | 932794001 | 74   |
| PMS SKS Elektronik          | 932791001 | 77   |
| PMS SKS Elektroinstallation | 932792001 | 78   |
| PMS SKS safety              | 932795001 | 76   |
| PRUEF 1                     | 9313761xx | 13   |
| PRUEF 2                     | 9733681xx | 15   |
| PRUEF 1600 Au               | 9750177xx | 14   |
| PRUEF 1610 FT Au            | 9750187xx | 14   |
| PRUEF 2600                  | 9723171xx | 17   |
| PRUEF 2600 C2               | 9723271xx | 16   |
| PRUEF 2610 FT               | 9723181xx | 16   |
| PRUEF 2700                  | 9723191xx | 17   |
| SEB 2600 G M4               | 9723541xx | 68   |
| SEB 2610 F4,8               | 9723551xx | 69   |
| SEB 2620 F6,3               | 9723561xx | 69   |
| SEB 2630 S1,9               | 9723591xx | 70   |
| SEP 2610 F4,8               | 9723611xx | 71   |
| SEP 2620 F6,3               | 9723621xx | 71   |
| SEP 2630 S1,9               | 9723631xx | 71   |
| SLS 10 B                    | 9318241xx | 51   |
| SLS 20 B                    | 9318251xx | 51   |
| SLS 200                     | 9321531xx | 52   |
| SML 100/1                   | 9733881xx | 39   |
| SS 260                      | 973865001 | 16   |
| TKL 065 BAN                 | 974340000 | 39   |
| TKO 2,5 - PML 711A          | 974301000 | 19   |
| TKO 5 - PMS 221A            | 974312000 | 18   |
| TKO 5 - PMT 221A            | 974311000 | 19   |
| TW 120 BAN                  | 974330000 | 38   |
| VON 20                      | 9300461xx | 49   |
| VON 30                      | 9300471xx | 49   |
| VQ 20                       | 9300581xx | 50   |
| VQ 30                       | 9300611xx | 50   |
| VSF 20                      | 9304351xx | 48   |
| VST 100                     | 930581000 | 43   |
| VST 20                      | 930050000 | 43   |

## Instructions for Index and Part No.

### Example Part No. 9340621xx

|               |                      |
|---------------|----------------------|
| 00 = ● black  | 05 = ● brown         |
| 01 = ● red    | 06 = ● grey          |
| 02 = ● blue   | 07 = ○ white         |
| 03 = ● yellow | 09 = ● violet        |
| 04 = ● green  | 88 = ●● yellow/green |

# Index By Part Number

| Part No.  | Type No.    | Page | Part No.  | Type No.                    | Page |
|-----------|-------------|------|-----------|-----------------------------|------|
| 603006001 | AGS 20      | 24   | 9318041xx | KUN 30                      | 59   |
| 9300461xx | VON 20      | 49   | 9318047xx | KUN 30 Au                   | 59   |
| 9300471xx | VON 30      | 49   | 9318241xx | SLS 10 B                    | 51   |
| 930050000 | VST 20      | 43   | 9318251xx | SLS 20 B                    | 51   |
| 9300581xx | VQ 20       | 50   | 9321461xx | AK 2 S                      | 24   |
| 9300611xx | VQ 30       | 50   | 9321531xx | SLS 200                     | 52   |
| 9300991xx | PK 10 A     | 66   | 9322001xx | KST S WS                    | 53   |
| 9301031xx | PKI 10 A    | 65   | 9324351xx | AK 2 B                      | 25   |
| 9301037xx | PKI 10 A Au | 65   | 932791001 | PMS SKS Elektronik          | 77   |
| 9301091xx | KD 10       | 60   | 932792001 | PMS SKS Elektroinstallation | 78   |
| 9301131xx | KLEPS 30    | 8    | 932793001 | PMS 4                       | 73   |
| 9301171xx | PKN 10 B    | 66   | 932794001 | PMS 4 SKS                   | 74   |
| 930120000 | AGF 20      | 23   | 932795001 | PMS SKS safety              | 76   |
| 930122000 | AGF 30      | 23   | 932827001 | PMS 250                     | 74   |
| 9301261xx | AK 10       | 24   | 932959001 | PMS 0,64                    | 73   |
| 9301361xx | PKNI 10 B   | 67   | 932961001 | PMS 2                       | 73   |
| 9301441xx | PKNI 20 B   | 67   | 933003001 | PMS 4 KFZ                   | 74   |
| 930147000 | BU 10       | 61   | 933844001 | BNC AL 0,64                 | 27   |
| 930147700 | BU 10       | 61   | 9340581xx | MLN 25/1                    | 32   |
| 930160000 | BO 10       | 61   | 9340591xx | MLN 25/2,5                  | 33   |
| 9301661xx | BIL 30      | 63   | 9340597xx | MLN 25/2,5 Au               | 33   |
| 9301667xx | BIL 30 Au   | 63   | 9340601xx | MLN 50/1                    | 32   |
| 9301751xx | BUG 10      | 63   | 9340611xx | MLN 50/2,5                  | 33   |
| 9301757xx | BUG 10 Au   | 63   | 9340617xx | MLN 50/2,5 Au               | 32   |
| 9301761xx | BIL 20      | 62   | 9340621xx | MLN 100/1                   | 32   |
| 9301767xx | BIL 20 Au   | 62   | 9340631xx | MLN 100/2,5                 | 33   |
| 930177000 | BU 20       | 62   | 9340637xx | MLN 100/2,5 Au              | 33   |
| 9301891xx | KUN 10      | 60   | 9340641xx | MLN 150/1                   | 32   |
| 9302241xx | MPB 1       | 57   | 9340651xx | MLN 200/1                   | 32   |
| 9302681xx | MPK 1       | 57   | 9340661xx | MLN 200/2,5                 | 33   |
| 9303081xx | MBI 1       | 55   | 9340667xx | MLN 200/2,5 Au              | 33   |
| 9303087xx | MBI 1 Au    | 55   | 9340671xx | MLS WS 25/1                 | 36   |
| 930312000 | MBU 1       | 56   | 9340681xx | MLS WS 50/1                 | 36   |
| 9303178xx | MA 1        | 22   | 9340691xx | MLS WS 200/1                | 36   |
| 9303181xx | MA 1 Crimp  | 22   | 9340701xx | MLS GG 25/1                 | 34   |
| 9303201xx | MKU 1       | 55   | 9340711xx | MLS GG 25/2,5               | 34   |
| 9304351xx | VSU 20      | 48   | 9340721xx | MLS GG 50/1                 | 34   |
| 930476001 | AGF 1       | 21   | 9340731xx | MLS GG 50/2,5               | 34   |
| 930581000 | VST 100     | 43   | 9340741xx | MLS GG 100/1                | 34   |
| 9305841xx | KB 2        | 44   | 9340751xx | MLS GG 100/2,5              | 34   |
| 9307261xx | BUELA 20 K  | 45   | 9340761xx | MLS GG 200/1                | 34   |
| 9307271xx | BUELA 30 K  | 46   | 9340771xx | MLS GG 200/2,5              | 34   |
| 9307291xx | BSB 20 K    | 47   | 9340781xx | MLS WG 25/1                 | 35   |
| 9307571xx | PKI 100     | 65   | 9340791xx | MLS WG 25/2,5               | 35   |
| 9312721xx | AGF 2       | 23   | 9340801xx | MLS WG 50/1                 | 35   |
| 9312941xx | BSB 300     | 48   | 9340811xx | MLS WG 50/2,5               | 35   |
| 931337000 | MBU 2       | 56   | 9340821xx | MLS WG 100/1                | 35   |
| 931338001 | MST 201     | 41   | 9340831xx | MLS WG 100/2,5              | 35   |
| 9313761xx | PRUEF 1     | 13   | 9340841xx | MLS WG 200/1                | 35   |
| 9314671xx | KLEPS 2     | 7    | 9340851xx | MLS WG 200/2,5              | 35   |
| 9316671xx | BUELA 300 K | 46   | 9340861xx | MLS WS 25/2,5               | 36   |
| 9317131xx | PK 110      | 64   | 9340871xx | MLS WS 50/2,5               | 36   |
| 9317141xx | PKI 110     | 64   | 9340881xx | MLS WS 100/2,5              | 36   |

# Index By Part Number

| Part No.  | Type No.              | Page |
|-----------|-----------------------|------|
| 9340891xx | MLS WS 200/2,5        | 36   |
| 9340901xx | MLN SIL 25/1          | 30   |
| 9340911xx | MLN SIL 50/1          | 30   |
| 9340921xx | MLN SIL 100/1         | 30   |
| 9340931xx | MLN SIL 150/1         | 30   |
| 9340941xx | MLN SIL 200/1         | 30   |
| 9340951xx | MLS WS 100/1          | 36   |
| 9340961xx | KUN S                 | 68   |
| 9340971xx | LAS S G               | 53   |
| 9340981xx | LAS S W               | 52   |
| 9340991xx | LAS S WS              | 53   |
| 9341001xx | LAS N WS              | 47   |
| 9341007xx | LAS N WS Au           | 47   |
| 9341581xx | PL 2600 S W           | 37   |
| 9341591xx | PL 2600 S             | 37   |
| 9341601xx | MAL N 4-0,64/100-0,25 | 27   |
| 9345071xx | MLN 150/2,5           | 33   |
| 9345077xx | MLN 150/2,5 Au        | 33   |
| 9723061xx | KLEPS 2600            | 9    |
| 9723071xx | KLEPS 2700            | 10   |
| 9723081xx | KLEPS 2800            | 10   |
| 9723091xx | KLEPS 2900            | 10   |
| 9723171xx | PRUEF 2600            | 17   |
| 9723181xx | PRUEF 2610 FT         | 16   |
| 9723191xx | PRUEF 2700            | 17   |
| 9723271xx | PRUEF 2600 C2         | 16   |
| 972337002 | PL 2600 S Set         | 75   |
| 972338001 | PMS 2600              | 75   |
| 972339001 | MMS 2010              | 75   |
| 972340001 | MMS 2020              | 75   |
| 972341001 | MMS 2030              | 76   |
| 972342001 | MMS 2040              | 76   |
| 9723541xx | SEB 2600 G M4         | 68   |
| 9723551xx | SEB 2610 F4,8         | 69   |
| 9723561xx | SEB 2620 F6,3         | 69   |
| 9723591xx | SEB 2630 S1,9         | 70   |
| 9723611xx | SEP 2610 F4,8         | 71   |
| 9723621xx | SEP 2620 F6,3         | 71   |
| 9723631xx | SEP 2630 S1,9         | 71   |
| 9724051xx | AK 2 B 2540 I         | 25   |
| 972416100 | MICRO-SMD CLIP        | 21   |
| 972425002 | PL 2600 S W Set       | 75   |
| 9725181xx | LAS 30                | 45   |
| 9725187xx | LAS 30 Au             | 45   |
| 972604001 | PMS 4 LMLH            | 74   |
| 972605001 | PMS 4 S LMLH          | 76   |
| 9730531xx | KLEPS 60              | 8    |
| 9733681xx | PRUEF 2               | 15   |
| 9733881xx | SML 100/1             | 39   |
| 9735011xx | KLEPS 2 BU            | 7    |
| 9735091xx | MST 3                 | 41   |
| 9735281xx | KLEPS 250             | 9    |
| 9735311xx | MPS 1                 | 14   |

| Part No.  | Type No.                  | Page |
|-----------|---------------------------|------|
| 9735821xx | PB 4                      | 59   |
| 9735841xx | MA 1 S                    | 22   |
| 9735921xx | KLEPS 3 ST                | 5    |
| 9735941xx | MVL 2/25                  | 28   |
| 9735951xx | MVL 2/50                  | 28   |
| 9735961xx | MVL 2/100                 | 28   |
| 9735991xx | MZS 4                     | 44   |
| 9736001xx | MZS 2                     | 42   |
| 9736011xx | MZS 1 - PRUEF             | 15   |
| 9736041xx | MKL 0,64/25-0,25          | 27   |
| 9736441xx | MLB 25/1 V                | 31   |
| 9736451xx | MLB 50/1 V                | 31   |
| 9736461xx | MLB 100/1 V               | 31   |
| 9736471xx | MLB 200/1 V               | 31   |
| 973865001 | SS 260                    | 16   |
| 9738891xx | MA 260 SH                 | 25   |
| 973919001 | LMLH 50                   | 38   |
| 973929000 | MW SEB                    | 70   |
| 9739721xx | MICRO-KLEPS               | 5    |
| 9739951xx | MICRO-PRUEF MPS 2 0,64 FT | 13   |
| 974101188 | KLEPS FP 2B               | 6    |
| 9742011xx | KLEPS 064 PCH             | 6    |
| 974301000 | TKO 2,5 - PML 711A        | 19   |
| 974311000 | TKO 5 - PMT 221A          | 19   |
| 974312000 | TKO 5 - PMS 221A          | 18   |
| 974330000 | TW 120 BAN                | 38   |
| 974340000 | TKL 065 BAN               | 39   |
| 9750177xx | PRUEF 1600 Au             | 14   |
| 9750187xx | PRUEF 1610 FT Au          | 14   |
| 9750907xx | MST S WS 30 Au            | 42   |
| 9751061xx | KLEPS 1600                | 8    |
| 9751631xx | MAL S WS 2-4 100/1        | 28   |
| 9754547xx | MSEB 2600 G M3 Au         | 58   |
| 9754557xx | MSEB 2610 F2,8 Au         | 58   |
| 9754597xx | MSEB 2630 S1,9 Au         | 58   |
| 975604001 | PMS 2 S LMLH              | 73   |
| 9756947xx | MVL S WS 25/1 Au          | 29   |
| 9756957xx | MVL S WS 50/1 Au          | 29   |
| 9756967xx | MVL S WS 100/1 Au         | 29   |
| 9756977xx | MVL S WS 200/1 Au         | 29   |

## Instructions for Index and Part No.

### Example Part No. 9340621xx

|               |                      |
|---------------|----------------------|
| 00 = ● black  | 05 = ● brown         |
| 01 = ● red    | 06 = ● grey          |
| 02 = ● blue   | 07 = ○ white         |
| 03 = ● yellow | 09 = ● violet        |
| 04 = ● green  | 88 = ●● yellow/green |

# Terms & Conditions

**TITLE** - Title to the products of ALTECH shall remain with ALTECH until payment is made in full by Customer. Such reservation of title is for the purpose of securing the purchase price and shall not relieve Customer of the duty to inspect the products upon receipt, to notify ALTECH of any deficiencies or defects, and to exercise due care in the use, installation, operation, and maintenance of the products when on the premise of the Customer or under the control of the Customer. Notwithstanding any reservation of title by ALTECH, risk of loss shall pass to customer at any time of shipment.

**SHIPMENT AND DELIVERY** - All orders for destination in the mainland United States (less Hawaii, Alaska and non-continental United States possessions) will be shipped F.O.B. Flemington, N.J. All destination, shipping and other charges shall be paid by the Customer in accordance with ALTECH's then current shipping and billing practices.

Delivery dates given in the acceptance of any order are approximate. ALTECH shall not be liable for delays in delivery or in performance due to causes beyond its reasonable control including acts of God, acts of Customer, acts of civil or military authority, fires, strikes or other labor disturbances, war, riot or delays in transportation. In the event of such delay, the date of delivery or performance shall be extended for a period equal to the time lost by reason of the delay.

**PRICE** - PRICES in any ALTECH publication are subject to change without prior notification. Catalog prices are based on prices published in the current price list. All written quotations are valid for thirty (30) days from the date of quotation. Customer shall pay all sales, use, excise or similar taxes whenever ALTECH must itself pay and/or collect such tax from Customer arising out of the sale.

**PAYMENT** - Customer agrees to make payment within thirty (30) days of date of the invoice from ALTECH. Customer agrees to pay a late payment charge of one and one-half percent (1.5% per month, or the maximum late payment charge permitted by applicable law, whichever is less, on any unpaid amount for each calendar month (or fraction thereof) that such payment is in default. Orders amounting to less than \$100.00 will be billed at \$100.00 plus freight. Full carton purchases are required. In the event of referral to an attorney for collection, reasonable attorney's fees for collection of the overdue amount shall be paid by Customer. In the event payment is not received within 30 days from the date of invoice, any discount shall be cancelled and the full list price will be due.

**LIMITED WARRANTY** - ALTECH warrants to Customer that the equipment purchases shall be free from defects in material and workmanship under normal use and service for a period of one year from shipment.

Written notice as an explanation of the circumstances of any claim that the equipment has proved defective in material or workmanship shall be given promptly by the Customer to ALTECH.

ALTECH will not be liable for any misuse, improper operations, improper installation, improper maintenance, alteration, modification, accident or unusual degradation of the equipment or parts due to an unsuitable installation environment.

No representation of other affirmation of facts, including but not limited to statements regarding capacity, suitability for use or performance of the equipment, shall be or be deemed to be a warranty or representation by ALTECH for any purpose, nor give rise to any liability or obligation of ALTECH whatsoever.

Customer's sole and exclusive remedy in the event of breach of warranty, as set forth herein, is expressly limited to (1) the correction of the defect by adjustment, repair, modification, or replacement, or (2) issuance of a credit or refund of the purchase price for the defective equipment at ALTECH's election and sole expense.

EXCEPT AS SPECIFICALLY PROVIDED IN THIS AGREEMENT, THERE ARE NO OTHER WARRANTIES EXPRESSED OR IMPLIED INCLUDING BUT NOT LIMITED TO ANY IMPLIED WARRANTIES OR MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE.

THIS WARRANTY EXTENDS ONLY TO THE CUSTOMER FROM ALTECH OR ITS AUTHORIZED DISTRIBUTOR.

**LIMITATION OF LIABILITY** - IN NO EVENT, SHALL ALTECH BE LIABLE FOR LOSS OF PROFITS, INDIRECT, SPECIAL, CONSEQUENTIAL OR OTHER SIMILAR DAMAGES ARISING OUT OF ANY BREACH OF THIS AGREEMENT OR OBLIGATIONS UNDER THE AGREEMENT.

ALTECH SHALL NOT BE LIABLE FOR ANY DAMAGES CAUSED BY DELAY IN SHIPMENT, INSTALLATION OR FURNISHING OF EQUIPMENT OR SERVICES UNDER THIS AGREEMENT.

No action arising out of any claimed breach of this Agreement may be brought by either party more than two (2) years after the cause of action has accrued.

**PATENT INDEMNITY** - ALTECH shall defend or settle any suit or proceeding brought against Customer based on a claim that any equipment made to ALTECH design and furnished hereunder constitutes an infringement of any existing United States patent, provided (ALTECH) is notified promptly in writing and is given complete authorization and information required for the defense, and ALTECH shall pay all damages and costs awarded against Customer, but shall not be responsible for any costs, expense or compromise incurred or made by Customer without ALTECH's prior written consent. If any equipment is in ALTECH's opinion likely to or does become the subject of a claim for patent infringement, ALTECH may at its option and expense procure for Customer the right to continue using the device, modify it to become non-infringing, but in the event ALTECH is not reasonably able to modify, substitute, or otherwise procure for Customer the right to continue using it, ALTECH will remove such equipment and refund to Customer the amount paid in excess of a reasonable rental for past use.

ALTECH shall not be liable for any infringement or claim based upon use of the equipment in combination with other equipment not supplied by ALTECH or with modifications made by Customer.

The foregoing states the entire liability of ALTECH to Customer arising from patent infringement.

**SELLER'S REMEDIES** - Should Customer fail to make any payment within ten (10) days of its due date, or fail to perform any other of the Customer's obligation hereunder upon thirty (30) days written notice, or should Customer be or become insolvent or be a party to any bankruptcy receivership proceeding prior to full payment of all amounts payable hereunder, ALTECH may: (a) with or without demand or notice to customer declare the entire amount unpaid immediately due and payable; (b) enter upon the premises where the equipment may be found and remove it (Customer shall assemble the equipment and make it available to ALTECH at a place reasonably convenient to both parties and shall permit and assist ALTECH in effecting the retaking and removal of the equipment); and (c) sell any or all the equipment as permitted under applicable law, applying the proceeds of the sale to payment of the expenses of retaking, repairing and selling the equipment, reasonable attorney fees and to the satisfaction of all indebtedness then due and unpaid under this Agreement. Any surplus shall be paid to Customer and any deficiency shall be paid to ALTECH by Customer.

The remedies provided herein shall be cumulative and in addition to all other remedies provided by law or equity or under the Uniform Commercial Code.

**GOVERNING LAW** - This agreement will be governed by the Laws of the State of New Jersey.

**GENERAL** - This Agreement shall only become effective and binding when either (a) it has been accepted and executed by an authorized representative of ALTECH, or (b) the equipment has been shipped to Customer, with or without acceptance in writing hereon. Notice of acceptance is hereby waived by Customer. Customer hereby acknowledges receipt of a true and complete copy hereof.

No addition to or modification of any of the Terms and Conditions of Sale as they appear herein shall be binding upon ALTECH unless signed in writing by duly authorized representative of ALTECH in Flemington, N.J.

Typographical and clerical errors in quotations, orders and acknowledgments are subject to correction.

This Agreement is not assignable without the prior written consent of ALTECH. Any attempt to assign any of the rights, duties or obligations of this Agreement without such consent is void.

If any provision or provisions of this Agreement shall be held to be invalid, illegal or unenforceable, the validity, legality and enforceability, of the remaining provisions shall not in any way be affected or impaired thereby.

ALTECH is not responsible for failure to fulfill its obligation under this Agreement due to causes beyond its control, or except as agreed herein.

THE CUSTOMER ACKNOWLEDGES THAT HE HAS READ THE AGREEMENT, UNDERSTANDS IT, AND AGREES TO BE BOUND BY ITS TERMS AND CONDITIONS. FURTHERMORE, THE CUSTOMER AGREES THAT IT IS THE COMPLETE AND EXCLUSIVE STATEMENT OF THE AGREEMENT BETWEEN THE PARTIES, WHICH SUPERSEDES ALL PROPOSALS OR PRIOR AGREEMENTS, ORAL OR WRITTEN, EXPRESSED OR IMPLIED, AND ALL OTHER COMMUNICATIONS BETWEEN THE PARTIES RELATING TO THE SUBJECT MATTER OF THIS AGREEMENT.



# Some Other Altech Products



## Circuit Protection Devices



Altech the market leader in UL508 Manual Motor Controllers/ Miniature Circuit Breakers now introduces UL489 Miniature Circuit Breakers and UL1077 Supplementary Protectors. The UL489 versions are DIN rail mounted, 17.5mm wide, thermal magnetic, 240V, 480Y/277V AC, 50/60Hz, 125 and 250 VDC models, with short circuit interrupt capacity of 10kA, a positive trip indicator, and are line/load reversible. The UL1077 versions are DIN rail mounted, 17.5mm wide, thermal magnetic, 480Y/277V AC, 50/60Hz, a short circuit withstand capacity 10kA, have a positive trip indicator.

**Altech Corp.®**  
35 Royal Rd., Flemington, NJ 08822  
908-806-9400  
FAX 908-806-9490  
[www.altechcorp.com](http://www.altechcorp.com)

## Interface Modules and Industrial Relays



Altech offers a wide range of DIN Rail or panel mount cable interface modules, relay interface modules, power supplies, carrier modules, and custom designed modules. Cable to connector models include: D-Sub connectors, ribbon cable connectors, and Dip socket connectors to terminals. Standard relay modules from 1 to 16 channels, and safety relay modules from 1 to 16 channels and up to 10 poles are included. The catalog also contains a large selection of industrial relays, and custom designed interface modules.

**Altech Corp.®**  
35 Royal Rd., Flemington, NJ 08822  
908-806-9400  
FAX 908-806-9490  
[www.altechcorp.com](http://www.altechcorp.com)

## Contactors and More!



Altech's now carries contactors, mini contactors, definite purpose contactors & overload relays. The contactors come in 3 and 4 pole configurations at 9A to 800A. Available in Single Phase (115 -230V) and Three Phase (200 - 575V) AC and DC models. A large variety of coil voltages are supported and the accessories are auxiliary contacts and overload relays. The mini contactors come in screw clamp, fast-on, cage clamp and solder pin types.

**Altech Corp.®**  
35 Royal Rd., Flemington, NJ 08822  
908-806-9400  
[www.altechcorp.com](http://www.altechcorp.com)

## Terminal Blocks



Altech offers a NEW Terminal Block catalog with the most competitively priced blocks in the industry. We feature screw and spring clamp models for DIN rail and panel mount applications. This advanced line of wire termination products will increase your design options and help to get the job done more efficiently. Our line of blocks include feed-through (single, double or triple level), distribution, ground, fuse, disconnect, thermocouple, surge suppressor and indicator. A wide variety of accessories, tools and ferrules are available.

**Altech Corp.®**  
35 Royal Rd., Flemington, NJ 08822  
908-806-9400  
[www.altechcorp.com](http://www.altechcorp.com)

## Motor Disconnect Switches



Altech's line of Motor Disconnect Switches are UL 508 listed as Manual Motor Controllers for AC Motor Starting Across-the-line and AC General use. This new 16 page catalog includes the 3 different handle designs, which are all available in gray/black or yellow/red housings. Electrical ratings are 25-150A / 600V. The switches are non-fused DIN Rail mountable. Neat features include: snap-on auxiliary switches, door mounting kit and a retrofit 30A fuse holder. Also featured are Enclosed Motor Disconnect Switches & Fused Enclosed Motor Disconnect Switch (30A) in plastic or stainless housings.

**Altech Corp.®**  
35 Royal Rd., Flemington, NJ 08822  
908-806-9400  
[www.altechcorp.com](http://www.altechcorp.com)

## Liquid Tight Strain Reliefs



This 64-page catalog introduces Altech's full line Liquid Tight Strain Reliefs (Cord Grips) which are used to seal cable entries, keep contaminants from entering enclosures, provide strain relief and thus reduce stress on components and termination points inside enclosures. Available in standard, high-performance, and economy versions, functions include Straight-Through, Increased Strain Relief, Bend Protection, Pull/Bend Protection, Multi-conductor, Flat Cable and EMI/RFI. They can be used with almost any type of cable, cord or conductor - solid, stranded, flat, shielded, high temperature, etc.

**Altech Corp.®**  
35 Royal Rd., Flemington, NJ 08822  
908-806-9400  
[www.altechcorp.com](http://www.altechcorp.com)



# altechcorp.com

## Altech Corp.®

Quality  
Endorsed  
Company



ISO 9001:2008  
CERTIFICATE



Altech Search  
Google™ Custom Search

[Home](#)[Stock Check](#)[Distributors](#)[Information](#)[News](#)[Contact](#)[Rep/Dist Login](#)[Altech Mexico](#)

### WEB TOOLS

[Product Crossings](#)[Request for Quote](#)[Sample Request](#)[Catalog Request](#)

### PRODUCT MENU

[Circuit Protection / Control >](#)[Connectors >](#)[Enclosures >](#)[European Spare Parts >](#)[Foot Switches](#)[Interface Modules >](#)[Power Supplies](#)[Push Buttons & Pilot Lights >](#)[Relays >](#)[Sensors >](#)[Terminal Blocks >](#)[Tower Lights](#)[Wire & Cable Management >](#)[Home](#)

### New Products and Promotions

## Serving the Automation & Control Industry Since 1984

### Circuit Protection



Circuit  
Protection  
Devices



Busbar  
and Power  
Distribution



Contactors,  
Overload  
Relays, Manual  
Motor Starters



Motor  
Disconnect  
Switches



European  
Fuses

### Connectors



Industrial  
Rectangular  
Connectors



Pin & Sleeve  
Devices



Receptacles

### Foot Switches



Foot  
Switches

### Sensors



Inductive  
Proximity  
Sensors

### Enclosures



Industrial  
Enclosures



DIN  
Enclosures

### Modules & Relays



Interface  
Modules



Safety  
Relays



Slimline  
Relays

### Power Supplies



Power  
Supplies

### Push Buttons



22 & 30 mm  
Push Buttons

### DIN Rail




DIN  
Rail

### Wire & Cable Management



Liquid Tight  
Strain Reliefs/  
Corrugated  
Tubes



Wire Duct

### Terminal Blocks



Din Rail  
Terminal  
Blocks



Panel Mount  
Terminal  
Blocks



Printed Circuit  
Board Terminal  
Blocks



Eurostrips



Distribution  
Blocks

### Miscellaneous



Ferrules




Custom  
Assembly



Marking &  
Engraving  
Systems



Power  
Semi-  
conductors



European  
Spare Parts

Altech Corporation  
35 Royal Road  
Flemington, NJ 08822-6000  
P 908.806.9400 • F 908.806.9490  
www.altechcorp.com  
Altech Corp.® 970-032015-5M  
Printed March 2015

