

SIGN	DATE	DESCRIPTION	APPROVER
△	04/06/10	Add the 2P mark & Wire strip length is changed	RUNNER
THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!!			

Material

- Ltem 1 Insulating top body Thermoplastic (UL94V-0)
- Ltem 2 Insulating down body Thermoplastic (UL94V-0)
- Ltem 3 Insulating lever Thermoplastic (UL94V-0)
- Ltem 4 Wire guard Stainless Steel
- Ltem 5 Contaits PIN PhBz (CuSn) Tin plated



Electrical

cULus



- Voltage rating: 300V
- Current rating: 10A
- Solid wire(AWG): 12-26
- Stranded wire(AWG): 12-26
- △ ● Wire strip length: 9-10mm
- Withstanding Voltage: 1.6KV
- Operating temperature: -40°C to +115°C

HW xx 70 x 1 xxxx G

02 2 CONTACTS	0 Black	0000 Standard @ Logo	RoHS
03 3 CONTACTS	5 Green	000A Standard ANY Logo	Pb<40,000ppm
... ..	6 Blue	Any special item by	
24 24 CONTACTS	8 Grey	customer request,	
		please contact sales	
		department.	



2P mark



SECTION A-A

Poles	02	03	04	05	06	07	08	09	10	11	12	13
Dim L	10.10	15.10	20.10	25.10	30.10	35.10	40.10	45.10	50.10	55.10	60.10	65.10
Dim B	5.00	10.00	15.00	20.00	25.00	30.00	35.00	40.00	45.00	50.00	55.00	60.00
TOL	±0.15					±0.20					±0.25	
Poles	14	15	16	17	18	19	20	21	22	23	24	
Dim L	70.10	75.10	80.10	85.10	90.10	95.10	100.10	105.10	110.10	115.10	120.10	
Dim B	65.00	70.00	75.00	80.00	85.00	90.00	95.00	100.0	105.0	110.0	115.0	
TOL	±0.25					±0.30						

ANYTEK

CUSTOMER COPY

ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD

TITLE		HW 5.0 Series W/O flange(Contact on up side)									
PART NO.		HWxx70x1xxxxG				DWG NO.		8HW0701			
APPROVED	CHECKED	DESIGNED	DRAWN		CUST NO.					Tolerance	
		Runner 2010.04.06	Runner 2010.04.06				UNIT: mm		X. ±0.50		
							SCALE: NONE		X.X ±0.30		
					SHEET: 01/01		REV: C		X.XX ±0.10		
									X° ±1°		