

SIGN	DATE	DESCRIPTION	APPROVER
△			
△			


THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!!

Material

- Item ① Insulating body: Thermoplastic (UL94V-0)
- Item ② Insulating lever: Thermoplastic (UL94V-0) Orange RAL 2011/P
- Item ③ Spring clamp: Stainless steel Matte Tin plated.
- Item ④ Insulating cover : Thermoplastic (UL94V-0)
- Item ⑤ Terminal side body: Thermoplastic (UL94V-0)

Electrical: cULus

- Voltage rating: 150V
- Current rating: 2A
- Solid wire(AWG): 16-22
- Stranded wire(AWG): 16-22
- Wire strip length: 9.0-10.0mm
- Withstanding Voltage: 1.3KV
- Operating temperature: -40°C to +115°C
- Safety Approval:
- Critical dimension: ▽



Section A-A


NY xx 10 x 0 xxxx G

No. OF POLES
02: 2 POLES
03: 3 POLES
:
24: 24 POLES

Body Color
0 Black (RAL9005)
2 Red (RAL3001/D)
3 Orange(RAL2011/P)
4 Yellow(RAL1018/A)
5 Green(RAL6018/T)
6 Blue (RAL5015/A)
8 Grey(RAL7004/P)
9 White(RAL1102)
C Multiple colors

0000 Standard @ Logo
000A Standard ANY Logo
Any special item by
customer request,
please contact sales
department.

RoHs compliant
(lead<4%)
in copper Alloy



N = Number of poles

Dim L=(N×3.5)+1.5

Dim P=(N-1)×3.5

POLES	Dim L	Dim P
2p-6p	±0.15	±0.15
7p-12p	±0.2	±0.2
13p-18p	±0.3	±0.3
19p-24p	±0.4	±0.4

ANYTEK

CUSTOMER COPY

ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD

TITLE		NY-3.5mm Series (W/O top cover)						
PART NO.		NYxx10x0xxxxG			DWG NO.		8NY0003	
APPROVED		CHECKED	DESIGNED	DRAWN	CUST NO.			
		Guoxue 2014.08.06	Guoxue 2014.08.06			Tolerance		
						X. ±0.50		
						X.X ±0.30		
				SHEET: 01/01		REV: B		X.XX ±0.10
						X* ±1*		