



DUAL-IN-LINE SOCKETS

SERIES 299 • RIGHT ANGLE MOUNT • CLOSED FRAME



- Ideal for mounting components, such as LED displays, where the face must be parallel to the PCB surface
- Sockets have solder tail termination and are available with either .300" (standard) or .100" row spacing
- Series 299 uses MM #1103/0903, #1103/1610 or #1103/0904 pins. See pages 166 & 167 for details
- Hi-Rel, 4-finger BeCu #30 contact is rated at 3 amps. See page 253 for details
- Insulators are high temperature thermoplastic, suitable for all soldering operations
- For Electrical, Mechanical and Environmental Data, see page 264 for details



Total number of pins				Quantity per tube	ORDERING INFORMATION		
	A	B	C		E = .100	E = .300	
6	0.3	0.3	0.4		299-XX-306-11-001000	* 299-XX-306-10-001000	
8	0.4	0.3	0.4		299-XX-308-11-001000	* 299-XX-308-10-001000	
10	0.5	0.3	0.4		299-XX-310-11-001000	* 299-XX-310-10-001000	
12	0.6	0.3	0.4	33	299-XX-312-11-001000	* 299-XX-312-10-001000	
14	0.7	0.3	0.4	29	299-XX-314-11-001000	* 299-XX-314-10-001000	
16	0.8	0.3	0.4	25	299-XX-316-11-001000	* 299-XX-316-10-001000	
18	0.9	0.3	0.4	22	299-XX-318-11-001000	* 299-XX-318-10-001000	
20	1.0	0.3	0.4	20	299-XX-320-11-001000	* 299-XX-320-10-001000	
24	1.2	0.3	0.4	16	299-XX-324-11-001000	* 299-XX-324-10-001000	
8	0.4	0.6	0.7	50		299-XX-608-10-002000	
10	0.5	0.6	0.7	40		299-XX-610-10-002000	
12	0.6	0.6	0.7	34		299-XX-612-10-002000	
14	0.7	0.6	0.7	28		299-XX-614-10-002000	
16	0.8	0.6	0.7	25		299-XX-616-10-002000	
18	0.9	0.6	0.7	22		299-XX-618-10-002000	
20	1.0	0.6	0.7	20		299-XX-620-10-002000	
22	1.1	0.6	0.7	18		299-XX-622-10-002000	
24	1.2	0.6	0.7	16		299-XX-624-10-002000	
26	1.3	0.6	0.7	15		299-XX-626-10-002000	
28	1.4	0.6	0.7	14		299-XX-628-10-002000	
30	1.5	0.6	0.7	13		299-XX-630-10-002000	
32	1.6	0.6	0.7	12		299-XX-632-10-002000	
36	1.8	0.6	0.7	11		299-XX-636-10-002000	
40	2.0	0.6	0.7	10		299-XX-640-10-002000	
SPECIFY PLATING CODE XX =							
Sleeve (Pin)					93		43
Contact (Clip)					200 μ" Sn/Pb		200 μ" Sn
					30 μ" Au		30 μ" Au

RoHS-2
2011/65/EU

XX=Plating Code
See Below

* Not available in tubes

