



SIGN	DATE	DESCRIPTION	APPROVER
△	8/07'06	Added VDE and standard	梁仁松
△	2010.11.26	The tolerance is changed	Jacke
THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!!			



Material

- Item⑥ Clamp: Brass(CuZn),Nickel plated
- Item⑥ Terminal screw: Steel Zinc plating "--" slot type
- Item⑥ Female contact: PhBz, Tin plated
- Item⑥ Terminal (housing): Thermoplastic (UL94V-0)
- Item⑥ Terminal (cover): Thermoplastic (UL94V-0)

△ Electrical cULus/VDE

- Voltage rating: 300VAC/300VAC
- Current rating: 8A/10A
- Wire range: 1.5mm²
- Solid wire(AWG): 16-28
- Stranded wire(AWG): 16-28
- Torque: 1.7Lb-In./0.2Nm
- Screw: M2
- Wire strip length: 6-7mm
- Withstanding Voltage: 1.6KV/2.5KV
- Operating temperature: -40°C to +115°C
- Safety approval:

TS xx 3 1 x B xxxx G

No. OF POLES
02: 2 POLES
:
24: 24 POLES

Color
0 Black (RAL9005)
2 Red (RAL3001/D)
3 Orange(RAL2011/P)
4 Yellow(RAL1018/A)
5 Green(RAL6018/T)
6 Blue (RAL5015/A)
8 Grey(RAL7035/D)

RoHS pb<40 , 000ppm
0000: "@" Logo
000A: "ANYTEK" Mark
Any special item by customer request. please contact sales department.

DIMENSION
N = Number of contacts

A	NX3.81
B	(N-1)X3.81

Poles	Tolerance
2p-6p	±0.15
7p-12p	±0.20
13p-16p	±0.25
17p-24p	±0.30

ANYTEK

CUSTOMER COPY

ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD

TITLE	TS-3.81mm Series Without flange (for latch on back side)						
PART NO.	TSxx31xBxxxxG			DWG NO.	8TS0302		
APPROVED	CHECKED	DESIGNED	DRAWN	CUST NO.			
		Jacke 2010.11.26	Marvin 2010.11.26		UNIT: mm	X.	±0.50
					SCALE: NONE	X.X	±0.30
					REV.: F	X.XX	±0.10
				SHEET: 01/01		X°	±1°