






| SIGN                                           | DATE   | DESCRIPTION                                                                | APPROVER |
|------------------------------------------------|--------|----------------------------------------------------------------------------|----------|
| △                                              | 3/6'07 | 增加溝槽尺寸規範                                                                   | Marvin   |
| △                                              | 4/7'09 | Voltage,wirerange,torque,operating temperature safety approval are changed | Jody     |
| △                                              | 4/7'09 | Name changed                                                               | Jody     |
| THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!! |        |                                                                            |          |

### Material

- Item① Terminal body(metal housing): Steel stamped clamp
- Item② Terminal screw: Steel Zinc plating "+/-" slot type
- Item③ Wire guard: Stainless steel
- Item④ Insulator (housing): Thermoplastic (UL94V-0)

### Electrical cULus

- △ ● Voltage rating: 300VAC
- Current rating: 57A
- Wire range:
- △ ● Solid wire(AWG): 6-22
- △ ● Stranded wire(AWG): 6-22
- △ ● Torque: 13 Lb-In
- Screw: M4
- Wire strip length: 8-9mm
- △ ● Withstanding Voltage: 1.6KV
- △ ● Operating temperature: -40°C to +115°C
- △ ● Safety Approval: US

$$A = (N-1) \times 12.5 + 10.5$$
$$B = (N-1) \times 12.5$$

N=NUMBER OF POLES

| POLES | DIM A | DIM B | TOL            |
|-------|-------|-------|----------------|
| 2P    | 23.0  | 12.5  | +0.40<br>-0.40 |
| 3P    | 35.5  | 25.0  |                |
| 4P    | 48.0  | 37.5  |                |
| 5P    | 60.5  | 50.0  |                |
| 6P    | 73.0  | 62.5  |                |

EN xx 04 x 0 xxxx G

02 2 Poles    0 Black    000 0 @ logo    G: Pb<40,000ppm  
03 3 Poles    4 Yellow    000 A ANY logo  
...    5 Green    Any special item by  
06 6 Poles    8 Grey    customer request,  
                         please contact sales  
                         department.

# ANYTEK

## CUSTOMER COPY

ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD

|          |                         |                  |                  |              |             |      |       |
|----------|-------------------------|------------------|------------------|--------------|-------------|------|-------|
| TITLE    | EN-12.5 Series (2~6P) △ |                  |                  |              |             |      |       |
| PART NO. | ENxx04x00000G           |                  |                  | DWG NO.      | 8EN0001     |      |       |
| APPROVED | CHECKED                 | DESIGNED         | DRAWN            | CUST NO.     |             |      |       |
|          |                         | JODY<br>2009.4.7 | JODY<br>2009.4.7 |              | Tolerance   |      |       |
|          |                         |                  |                  |              | UNIT: mm    | X.   | ±0.50 |
|          |                         |                  |                  |              | SCALE: NONE | X.X  | ±0.30 |
|          |                         |                  |                  | SHEET: 01/01 | REV.: D     | X.XX | ±0.10 |
|          |                         |                  |                  |              |             | X°   | ±1°   |