



750-191 Flexible Metal-Core EMI/RFI Conduit with External Braid

Flexible metal-core conduit plus a single shield of EMI/RFI braiding



How To Order




Table I: Dash No./Dimensions

Dash No.	Glenair Brass		SST, Nickel/Iron	
	A I.D. Min	B O.D. Max	A I.D. Min	B O.D. Max
06	.175 (4.45)	.330 (8.40)	.175 (4.45)	.330 (8.40)
08	.260 (6.60)	.430 (10.9)	.245 (6.22)	.434 (11.0)
09	.294 (7.47)	.458 (11.6)	.294 (7.47)	.458 (11.6)
10	.308 (7.82)	.485 (12.3)	.308 (7.82)	.485 (12.3)
12	.380 (9.65)	.550 (14.0)	.370 (9.40)	.558 (14.2)
16	.505 (12.8)	.680 (17.3)	.495 (12.6)	.707 (18.0)
20	.630 (16.0)	.800 (20.3)	.620 (15.7)	.830 (21.1)
24	.760 (19.3)	.935 (23.7)	.745 (18.9)	.950 (24.1)
32	1.012 (25.7)	1.201 (30.5)	.995 (25.3)	1.270 (32.3)
40	1.265 (32.1)	1.561 (39.6)	1.245 (31.6)	1.532 (38.9)
48	1.510 (38.4)	1.816 (46.1)	1.495 (38.0)	1.782 (45.3)
56	1.760 (44.7)	2.061 (52.3)	1.760 (44.7)	2.053 (52.1)
64	2.010 (51.1)	2.326 (59.1)	1.995 (50.7)	2.292 (58.2)
80	2.515 (63.9)	2.821 (71.7)	2.495 (63.4)	2.792 (70.9)
96	2.995 (76.1)	3.290 (83.6)	2.995 (76.1)	3.282 (83.4)

Table II: Conduit Core


SYM	Core Material
B	Brass, Per A-A-52440 Type I, Grade B
C	Stainless Steel
N	80% Nickel, 20% Iron

Table III: Braided Shield

SYM	Shield/Braid
B	Bronze (Standard for Brass Core)
C	Stainless Steel (Standard for SST and Nickel/Iron Core)
T	Tin Copper
N	Nickel Copper
S	SnCuFe
A	Silver Copper
L	Armorlite™
D	Dacron
M	Nomex
E	AmberStrand® 100%
F	AmberStrand® 75%/25%

Std. Conduit Tolerances

Length (Inches)	Tolerance (Inches)
Up To 18	± .50
19 - 36	± 1.0
37 - 72	± 1.5
73 - 144	± 2.0
145 - 300	± 3.0
301 - 600	± 4.0
601 - 1200	± 5.0
1201 - Up	± 6.0



Packaging

Long-length orders of 750-191 braided conduit are subject to carrier weight and box size restrictions. For example, UPS air shipments are currently limited to 50 lbs. per box. Unless otherwise specified, Glenair standard practice is to ship optimal lengths of product based on weight, size, and individual carrier specifications. Consult factory for additional information or to specify packaging requirements.