






Δ
 N = Number of poles
 Dim A = $N \times 8.25 + 2.0$
 Dim B = $(N - 1) \times 8.25$

Poles	Tol.	Dim A & B
2-5p		± 0.20
6-10p		± 0.25
11-16p		± 0.35
17-24p		± 0.40
25-30p		± 0.50

SIGN	DATE	DESCRIPTION	APPROVER
Δ	20/10'06	added cULus approval	Steady
Δ	03/17'09	Add stipulation	Seamus
Δ	03/17'09	Dimension is changed	Seamus
Δ	06/04'11	Critical dimension is changed.	Tason
Δ	06/04'11	The Wire Range is changed from 20-12AWG to 22-12AWG	Tason
Δ	06/04'11	The tolerance table is changed.	Tason
Δ	11/27'12	Change the screw plating specification	Jacky
Δ	12/07'13	Change the withstand voltage and current	Jacky
THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!!			

MATERIALS ELECTRICAL
 RATED VOLTAGE & CURRENT: 300 V, 20 A/300 V, 32 A Δ
 WITHSTAND VOLTAGE: AC 2500 V/Min Δ
 INSULATION RESISTANCE: 1000 M Ω OR MORE AT DC 500 V
 OPERATING TEMPERATURE RANG: -40 °C ~ +115 °C
 SCREW TORQUE VALUE: 8.8 Lb-In..
 WIRE RANGE: 22 - 12 AWG. Δ
 1) MOLDED PARTS: POLYIMIDE 66, UL 94 V-0 BLACK
 2) TERMINAL: BRASS, 0.8t, Tin PLATED
 3) TERMINAL SCREWS: STEEL, M3

Δ 3) TERMINAL SCREWS:
 Δ Critical dimension:
 Δ APPROVAL: Δ

YK 334 xx 0 x x 00G G:RoHS compliant (lead<4%) in copper alloy
 NO. OF POLES MARK
 02: 2 POLES
 03: 3 POLES
 04: 4 POLES
 :
 30: 30 POLES
 TERMINAL & SCREW PLATED
 0: TERMINAL & SCREW: G/F
 1: TERMINAL: G/F, SCREW: Zinc
 2: TERMINAL: Sn, SCREW: G/F
 3: TERMINAL: Sn, SCREW: Zinc

ANYTEK

CUSTOMER COPY

ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD

TITLE		YK-334 Series						
PART NO.		YK334xx0xx00G			DWG NO.	8YK0001-334		
APPROVED	CHECKED	DESIGNED	DRAWN	CUST NO.			Tolerance	
		Jacky 2013.12.07	Jacky 2013.12.07		UNIT: mm		X.	±0.50
					SCALE: NONE		X.X	±0.30
				SHEET: 01/01	REV: F		X.XX	±0.10
							X°	±1°