

1

2


3

4

5

6

7



Solid Block
02 2 CONTACTS
03 3 CONTACTS
...
24 24 CONTACTS



TY xx 01 x 0 xxxx G Δ_6

G RoHS compliant
(lead<4%)
In copper Alloy

0000:"@ "Logo (Standard)
000A:"ANYTEK"Logo
Any special item by
customer request,
please contact sales
department.

0 Black (RAL9005)
2 Red (RAL3001/D)
3 Orange(RAL2011/P)
4 Yellow(RAL1018/A)
5 Green(RAL6018/T)
6 Blue (RAL5015/A)
8 Grey(RAL7035/D)
9 White(RAL1102)
C Green(RAL6018/U)

$\phi 3.60$ (Screw hole diameter)



SECTION C-C



Dimension

Dim L	N×5.0
Dim B	(N-1)×5.0

N= Number of poles

Poles	Tolerance
2P-6P	±0.15
7P-12P	±0.20
13P-18P	±0.25
19P-24P	±0.30

SIGN	DATE	DESCRIPTION	APPROVER
Δ_1	2008.12.02	Add the tolerance table	Jacke
Δ_2	2008.12.02	Add the inspection dimension	Jacke
Δ_3	2008.12.02	The temperature changed from -30°C, +105°C to -40°C, +115°C	Jacke
Δ_4	2008.12.16	The dimension changed from 1.1mm to 1.06mm+0.05/-0	Jacke
Δ_5	2009.04.19	Add TUV standard	Jacke
Δ_6	2013.11.19	Update the drawing	Chen Bo

THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!!

Material

- Item (a) Terminal body(metal housing): Brass (Cu Zn)
- Item (b) Terminal screw: Steel Zinc plating "-" slot type
- Item (c) Wire guard: PhBz, tin plated
- Item (d) Terminal (housing): Thermoplastic (UL94V-0)

Electrical cULus TUV

- Voltage rating: 300VAC /300VAC
- Current rating: 10A /10A
- Wire range: 0.2-2.5mm
- Solid wire(AWG): 14-26/14-26
- Stranded wire(AWG): 14-26/14-26
- Torque: 3.5Lb-In /0.4Nm
- Screw: M2.6
- Wire strip length: 6-7mm
- Withstanding Voltage: 1.6KV/2.5KV
- Operating temperature: -40°C to +115°C
- Safety Approval: cULus Δ_{TUV}
- Critical dimension: Δ_4

ANYTEK

CUSTOMER COPY

ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD

TITLE	TY-5.0mm Series (two beam contact)						
PART NO.	TYxx01x0xxxxG			DWG NO.	8TY0001		
APPROVED	CHECKED	DESIGNED	DRAWN	CUST NO.			
		Chen Bo 11/19`13	Chen Bo 11/19`13			Tolerance	
						X.	±0.50
						X.X	±0.30
						X.XX	±0.10
						X°	±1°
				SHEET: 01/01	REV.: E		

1

2

3

4

5

6

7