


3

2

1

GENERAL TOLERANCE									
	10 MAX	50 MAX	100 MAX	250 MAX	250 OVR	R5 MAX	R10 MAX	R20 MAX	R20 OVR
A	±0.15	±0.2	±0.3	±0.5	±0.75				
B	±0.2	±0.3	±0.55	±0.95	±1.4	±0.2	±0.3	±0.5	±2.5
C	±0.3	±0.5	±0.8	±1.4	±2	±0.3	±0.5	±1.0	±3.0

ASSEMBLY PART NO. AND CH. CODE	NO.	PART NO. AND CH. CODE	PART NAME	MATERIAL	COLOR	QTY.
△ 7327-3115, A	①	7157-8059	△ HIGH CURRENT FUSE LINKS (大電流ヒューズ) COVER 60A	PES	—	1
△ 7327-3115, A	②	7122-3622-70	△ HIGH CURRENT FUSE LINKS (大電流ヒューズ) B ₁ -TYPE HOUSING 60A	PA6T-G	YELLOW	1
△ 7327-3115, A	③	7227-6051	△ HIGH CURRENT FUSE LINKS (大電流ヒューズ) B ₁ -TYPE FUSE ELEMENT SUB ASSEMBLY 60A	—	—	1




△ VIEW B

△ 注記

1. 使用ボルト : M6

△ NOTE

1. APPLICABLE BOLT:M6



LET	DATE	REVISION RECORD	NO.	CHKD	VENDOR	OFFICE	CUSTOMER PART NO.	CUSTOMER	CUSTOMER DWG NO.	MATL. SPEC.	SEE TABLE	TREAT. & FIN.	ISSUE MARK
△ 3	13.05.16	ADDITION OF RATED VOLTAGE ETC., A	C13-Z189	E. M									
△ 2	10.09.27	ADDED NOTES & DELETED PART NO. ETC	C10-Y129	H. T									
△ 1	92.05.13	CH. TABLE & NOTES	C92-6474	T. S									
	90.03.27	NEW	C90-L329	M. T									
GENERAL TOLERANCE													
10MAX	50MAX	100MAX	250MAX	250OVR	ANGLE	ECCENT	DWG TYPE	DWG SOURCE	DWG DATE	UNIT	SQL	ANGLE	PART NO. CH. CODE
A ±0.15	±0.2	±0.3	±0.5	±0.75	±30°	O. 1	R	NEW	90.03.27	mm	2:1	3	△ 7327-3115, A
B ±0.2	±0.3	±0.55	±0.95	±1.4	±30°	O. 1	APPROVED	CHECKED	DESIGN				7327-3115:R
C ±0.3	±0.5	±0.8	±1.4	±2	±30°	O. 15	S. ONODA		M. TOTSUKA				E. MESA
SPECIFIED													
MASS													
13.05.16													
90.02.08													
13.05.16													
YAZAKI CORPORATION													

2

3