

D

C

B

A

D

C

B





A

© 2019 TE Connectivity. All Rights Reserved.

REVISIONS


P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	RELEASE TO PRODUCTION	26AUG2019	AY	PS
	B	CHANGED P AND P CAP LENGTH FROM 6.5 TO 7.0	16DEC2019	AY	PS

- NOTES:
- MATERIAL
HOUSING & P&P CAP : HIGH TEMPERATURE THERMOPLASTIC, UL94-V0; COLOR- BLACK
CONTACT PIN : COPPER ALLOY
FINISH :
MATING SIDE: MIN. 0.1 µm GOLD OVER NICKEL UNDER PLATING
SOLDER SIDE: MIN. 2.0 µm BRIGHT TIN OVER NICKEL UNDER PLATING
 - PACKAGING: TUBE (WITH PICK & PLACE CAP).
 - TOLERANCE NOT CUMULATIVE.
 - CUTTING BURR MAX. 0.25 mm.




48.0	50.0	25	2-2355104-5
46.0	48.0	24	2-2355104-4
44.0	46.0	23	2-2355104-3
42.0	44.0	22	2-2355104-2
40.0	42.0	21	2-2355104-1
38.0	40.0	20	2-2355104-0
36.0	38.0	19	1-2355104-9
34.0	36.0	18	1-2355104-8
32.0	34.0	17	1-2355104-7
30.0	32.0	16	1-2355104-6
28.0	30.0	15	1-2355104-5
26.0	28.0	14	1-2355104-4
24.0	26.0	13	1-2355104-3
22.0	24.0	12	1-2355104-2
20.0	22.0	11	1-2355104-1
18.0	20.0	10	1-2355104-0
16.0	18.0	9	2355104-9
14.0	16.0	8	2355104-8
12.0	14.0	7	2355104-7
10.0	12.0	6	2355104-6
8.0	10.0	5	2355104-5
6.0	8.0	4	2355104-4
DIM "F"	DIM "E"	POS	TE PN

1-2355104-0 AS SHOWN



RECOMMENDED PCB HOLE PATTERN FOR THROUGH HOLE WAVE



RECOMMENDED PCB HOLE PATTERN FOR THROUGH HOLE REFLOW / PIN-IN-PASTE

PICK AND PLACE CAP	3
CONTACT PIN	2
HOUSING	1
DESCRIPTION	ITEM NO.

THIS DRAWING IS A CONTROLLED DOCUMENT.	
DIMENSIONS: mm	TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± 1 PLC ±0.2 2 PLC ±0.15 3 PLC ± 4 PLC ± ANGLES ±2° FINISH
SEE NOTES	SEE NOTES

DWN RAGHAVENDRA.K CHK KARTHIK.JK APVD PRASHANTH	09APR2019 14AUG2019 16AUG2019
PRODUCT SPEC 108-64040 APPLICATION SPEC 114-32259 WEIGHT -	
CUSTOMER DRAWING	

TE Connectivity	
NAME AMPMODU 2mm BREAKAWAY HEADER, SINGLE ROW, VERTICAL, 0.1 Au, TUBE, PICK AND PLACE CAP	
SIZE A2	CAGE CODE 00779
DRAWING NO C-2355104	RESTRICTED TO -
SCALE 10:1	SHEET 1 OF 1
REV B	