






D






1-2348455-2
(4POS: X-KEY)




RECOMMEND PC BOARD HOLE PATTERN
: CONNECTOR MOUNT SIDE (NOT ACCUMULATE TOLERANCE)
PC BOARD THICKNESS : 1.0~1.6±0.1

ONLY 4POS

C



B



A

THIS DRAWING IS A CONTROLLED DOCUMENT

DIMENSIONS:
mm

TO CHANGES UNLESS
OTHERWISE SPECIFIED:

1. PLC ±

2. PLC ±

3. PLC ±

4. PLC ±

ANGLES ±

FINISH ±

THIS DRAWING IS A CONTROLLED DOCUMENT

DWN FISHER.ZHU 05DEC2018

CHK RICK.BIAN 05DEC2018

APVD RICK.BIAN 05DEC2018

PRODUCT SPEC 108-78298

APPLICATION SPEC 114-5377

WEIGHT -

RESTRICTED CUSTOMER

TE Connectivity

NAME DYNAMIC D1200D 2.5mmPITCH
HDR ASSY (H-TYPE) TIN PLATING
4-20POS

SIZE A200779

CAGE CODE C-2348455

DRAWING NO


RESTRICTED TO

SCALE 6:1


SHEET 2 OF 3

REV A


LOC	DIST	REVISIONS						
		P	LTR	DESCRIPTION	DATE	DWN	APVD	
	-		-	SEE SHEET 1	-	-	-	









I-2348455-3
(6POS:X-KEY)



I-2348455-4
(8POS:X-KEY)



I-2348455-6
(12POS:X-KEY)



THIS DRAWING IS A CONTROLLED DOCUMENT

DWN
FISHER, ZHU
05DEC2018

CHK
RICK, BIAN
05DEC2018

APVD
RICK, BIAN
05DEC2018

PRODUCT SPEC

108-78298

APPLICATION SPEC

114-5377

WEIGHT

-

RESTRICTED CUSTOMER

TE Connectivity

DYNAMIC D1200D 2.5mmPITCH
HDR ASSY (H-TYPE) TIN PLATING
4-20POS

SIZE

CAGE CODE

DRAWING NO

RESTRICTED TO

A200779

C-2348455

SCALE 6:1

SHEET 3 OF 3

REV A