







SIGN	DATE	DESCRIPTION	APPROVER
△	04/28'11	Add is cULus	Aaron
THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!!			

Material:

- Item a Terminal(housing): Thermoplastic (UL94V-0)
- Item b Terminal(cover): Thermoplastic (UL94V-0)
- Item c Male contact pin of short: Copper Tin plated
- Item d Male contact pin of long: Copper Tin plated

Electrical:

- cULus
- Voltage rating: 300V
- Current rating: 12A
- Withstanding Voltage: 1.6KV
- Operating temperature: -40°C to +115°C
- Soldering temperature: 250°C±10°C/5 Sec

△ ● Safety Approval:

KE xx 7 3 x 3 xxxx G

No. OF POLES		G: Pb<4000ppm
04: 2x2 POLES		
06: 2x3 POLES		
...		
48: 2x24 POLES		
	COLOR	0000: "@" Logo (Standard)
		000A: "ANYTEK" Mark
		Any special item by customer request, please contact sales department.
	0 Black (RAL9005)	
	2 Red (RAL3001/D)	
	3 Orange(RAL2011/P)	
	4 Yellow(RAL1018/A)	
	5 Green(RAL6018/T)	
	6 Blue (RAL5015/A)	
	8 Grey(RAL7035/D)	
	9 White(RAL1102)	
	C Green(RAL6018/U)	

Poles	Dim L	Dim P
2x2-2x6p	±0.15	±0.15
2x7-2x12p	±0.25	±0.25
2x13-2x18p	±0.35	±0.35
2x19-2x24p	±0.40	±0.40

N = Number of poles
Dim L=Nx5.0+2.8
Dim P=(N-1)x5.0

ANYTEK

CUSTOMER COPY

ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD

TITLE	KE 5.0mm With latch holder Series (Right-angle) DIP type						
PART NO.	KExx73x3xxxxG			DWG NO.	8KE0105		
APPROVED	CHECKED	DESIGNED	DRAWN	CUST NO.			
		Jacke 2010.03.30	Jacke 2009.08.26		UNIT: mm	Tolerance	
					SCALE: NONE	X.	±0.50
					REV.: B	X.X	±0.30
						X.XX	±0.10
						X°	±1°

SHEET: 01/01