

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

© COPYRIGHT 2002

ALL RIGHTS RESERVED.

LOC

DIST

REVISIONS

IR

—

P

LTR

DESCRIPTION

DATE

DWN

APVD

A1

Text hinzu

29JUL2003

Ba.

PL.

A2

RELEASED TO GENERAL SALES

18JUL2011

PKS

RRP




A3

COPPER WIRE RANGE UPDATED

08MAR2018

SV

PKS



THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN 08JAN2002

M. Neitzel

CHK

H. Ploesser

APVD

—

PRODUCT SPEC

—

APPLICATION SPEC

—

WEIGHT

A3

00779

©1534686

CUSTOMER DRAWING

SCALE 10:1

SHEET 1 OF 2

REV A3

TE

TE Connectivity

NAME

MAG-MATE Kontakt
mit Loetpin
Baugroesse .300 mod.

SIZE


CAGE CODE

DRAWING NO

RESTRICTED TO

DIMENSIONS:

mm



TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC

±0.2

1 PLC

±0.2

2 PLC

±0.2

3 PLC

±0.2

4 PLC

±0.2

ANGLES

±1°


FINISH

SEE TABLE

MATERIAL

SEE TABLE

LOC	DIST	REVISIONS				
		P	LTR	DESCRIPTION	DATE	APVD
A1	-		-	SEE SHEET 1	-	-



Bemerkungen:
NOTES:

- 1

Geeignet fuer Kupferlackdraht
Einzel- $\varnothing 0.45...0.63\text{mm}$ oder Doppeldraht $\varnothing 0.45...0.56\text{mm}$
SLOT ACCEPTS:
COPPER SINGLE MAGNET WIRE $\varnothing 0.45...0.63\text{mm}$ DIA
OR COPPER DOUBLE MAGNET WIRE $\varnothing 0.45...0.56\text{mm}$ DIA
- 2

Anlieferungszustand: Kontakte fortlaufend mit
Papierzwischenlage auf Kunststoffspule aufgewickelt
Max. 5 Splice Stellen pro Spule
Splice Stellen nicht miteinander verbunden
DELIVERYSTATE: CONTACTS CONTINUOUS REELED WITH
PAPER INTERLAYER ON PLASTIC-REEL.
MAX. 5 SPLICES PER REEL
SPLICES BE NOT BONDED TOGETHER.
- 3

Kontaktkammer nach Zeichnung
CAVITY ACCORDING DWG.

411-18516
- 4

Kennziffer fuer Drahtgroessenbereich (12)
IDENTIFICATION NO. FOR MAGNET WIRE RANGE (12)
- 5

Materialdicke
STOCK THICKNESS

0.32 ± 0.02

OBSOLETE	10	A	CuNiSi	Ag OVER Ni	1-1534686-8
	10	A	CuNiSi	Au OVER Ni	1-1534686-7
	10	A	CuNiSi	BLANK	1-1534686-2
	10	A	CuSn	PRETINNED	1-1534686-1
	9	B	CuNiSi	Ag OVER Ni	1534686-8
	9	B	CuNiSi	Au OVER Ni	1534686-7
	9	B	CuNiSi	BLANK	1534686-2
	9	B	CuSn	PRETINNED	1534686-1
	REELING	REV.	5 MATERIAL	SURFACE COLOR	TE PART NO

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN M. Neitzel	08JAN2002	TE TE Connectivity	
DIMENSIONS: mm		CHK H. Ploesser	-		
		APVD -	-	NAME MAG-MATE Kontakt mit Loetpin Baugroesse .300 mod.	
TOLERANCES UNLESS OTHERWISE SPECIFIED:		PRODUCT SPEC -	-		
0 PLC ± 0.2 1 PLC ± 0.2 2 PLC ± 0.2 3 PLC ± 0.2 4 PLC ± 0.2 ANGLES $\pm 1^\circ$		APPLICATION SPEC -	-	SIZE A3	CAGE CODE 00779
MATERIAL SEE TABLE		FINISH SEE TABLE	WEIGHT -	DRAWING NO C-1534686	RESTRICTED TO
CUSTOMER DRAWING				SCALE 10:1	SHEET 2 OF 2
				REV A3	