




Material

- Item a Clamp: Brass (CuZn) Ni plated
- Item b Female contact :pHbZ(CuSn) Tin plated
- Item c Terminal screw:Steel Zinc plating"-slot type
- Item d Terminal (housing):Thermoplastic (UL 94 V-0)
- Item e Terminal cover:Thermoplastic (UL 94 V-0)

Electrical cULus

- Voltage rating:300V
- Current rating:8A
- Wire range:
- Solid wire(AWG):16-28
- Stranded wire(AWG):16-28
- Torque(Lb-In):1.7
- Screw:M2
- Wire strip length:6-7mm
- Withstanding Voltage:1.6KV
- Operating temperature:-40°C to +115°C
- Safety Approval: us
- Critical dimension: 

VD xx 31 x 0 xxxx G

△ Solid Block –

02	2 POLES
03	3 POLES
...	...
24	24 POLES

- G RoHS compliant (lead<4%)
In copper Alloy

— 0000 Standard @ Logo
000A Standard ANY Logo
0091 Standard ANY Logo
Any special item by
customer request,
please contact sales
department.

0 Black (RAL9005)
2 Red (RAL3001/D)
3 Orange(RAL2011/P)
4 Yellow(RAL1018/A)
5 Green(RAL6018/T)
6 Blue (RAL5015/A)
8 Grey(RAL7035/D)
9 White(RAL1102)
C Green(RAL6018/U)

N=Number of contacts
Dim L=N $\times$ 3.81
Dim B=(N-1) $\times$ 3.81

	Dim L	Dim B
2P-5p	± 0.15	± 0.15
6P-10p	± 0.20	± 0.20
11P-15p	± 0.25	± 0.25
16P-20p	± 0.30	± 0.30
21P-24p	± 0.35	± 0.35



ANYTEK

CUSTOMER COPY

ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD

TITLE		VD-3.81 SERIES				VD-3.81 SERIES	
PART NO.		VDxx31x0xxxxG		DWG NO.		8VD0001	
APPROVED		CHECKED	DESIGNED	DRAWN	CUST NO.	Tolerance	
				Ji long 2014.06.10		UNIT: mm	X. ±0.50
						SCALE: NONE	X.X ±0.30
				SHEET: 01/01		REV: E	X.XX ±0.10
							X° ±1°