







PCB Layout

N = Number of poles.
Dim.A = $N \times 5.08 + 1.0$
Dim.B = $(N-1) \times 5.08$

POLE	4x2 ~ 4x6	4x7 ~ 4x12	4x13 ~ 4x18	4x19 ~ 4x24
Dim.A	±0.15	±0.25	±0.35	±0.45
Dim.B	±0.15	±0.25	±0.30	±0.40

SIGN	DATE	DESCRIPTION	APPROVER
△	07/02'11	No. OF POLES is changed	Runner
△	09/24'11	Add is "cULus" mark	Runner

THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!!

Material:

- Item ① Insulator(Cover): Thermoplastic (UL94V-0)
- Item ② Insulator(housing): Thermoplastic (UL94V-0)
- Item ③ Spring clamp: Stainless steel
- Item ④ Contact pin (fourth level): Brass, Tin plated
- Item ⑤ Contact pin (third level): Brass, Tin plated
- Item ⑥ Contact pin (second level): Brass, Tin plated
- Item ⑦ Contact pin (first level): Brass, Tin plated

Electrical:

- Voltage rating: 300V
- Current rating: 10A
- Wire range:
- Solid wire(AWG): 12-28
- Stranded wire(AWG): 12-28
- Wire strip length: 6-7mm
- Withstanding Voltage: 1.6KV
- Operating temperature: -40°C to +115°C
- Soldering temperature: 250°C±10°C/5 Sec

△ ● Safety Approval: cULus

● Critical dimension: ▽

HS xx 3 0 x 1 xxxx G

No. OF POLES

G: Pb<4000ppm

△ 08: 4x2 POLES

92: 4x23 POLES

96: 4x24 POLES

COLOR

- 0: BLACK
- 5: GREEN (RAL 6018/T)
- 6: BLUE
- 8: GREY (RAL 7004/P)

0000: "@" Logo (Standard)
000A: "ANYTEK" Mark
Any special item by customer request, please contact sales department.

ANYTEK

CUSTOMER COPY

ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATSOEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD

TITLE	HS 5.08mm Series (Solder pins staggered by half the pin spacing)						
PART NO.	HSxx30x1xxxxG			DWG NO.	8HS0004		
APPROVED	CHECKED	DESIGNED	DRAWN	CUST NO.			
		Runner 2011.09.24	Tony 2007.12.19			UNIT: mm	X. ±0.50
						SCALE: NONE	X.X ±0.30
				SHEET: 01/01	REV.: D		X.XX ±0.10
							X° ±1°