





P.C.B. LAYOUT



CIRCUIT: SPST ▲



## NOTES:

1. ALL DIMENSIONS IN MM
2. GENERAL TOLERANCE: X.X=±0.4  
X.XX=±0.25
3. TERM. NOS. FOR REFERENCE ONLY.
4. RATING: 12VDC, 50mA
- ▲5. OPERATING FORCE: 160 ± 50 gf
6. TRAVEL: 0.25mm +0.20/-0.10MM
7. CONTACT RESISTANCE: 100 MILLI OHMS MAX. (INITIAL)
8. MECHANICAL/ELECTRICAL LIFE 100,000 CYCLES MIN.
- ▲9. CONTACT MATERIAL: GOLD
10. ▲ DENOTES CRITICAL PARAMETER
11. OPERATING TEMP: -40°C TO 85°C

| REV                                                                                                          | ECO NO     | DESCRIPTION  | DATE     | BY | E-SWITCH®          |           |     |         | OBJECT ID |
|--------------------------------------------------------------------------------------------------------------|------------|--------------|----------|----|--------------------|-----------|-----|---------|-----------|
| D                                                                                                            | ECO-102204 | PRINT UPDATE | 09/15/23 | JS | TITLE TL1105DF160R |           |     |         | 000019859 |
|                                                                                                              |            |              |          |    |                    |           |     |         |           |
| THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED |            |              |          |    | SCALE              | DATE      | DR  | DWG     | REV       |
|                                                                                                              |            |              |          |    | 4:1                | 6/14/2001 | CJB | P060005 | D         |