





Dimension A&B

DIM A	N×5.08
DIM B	(N-1)×5.08



N=Number of contacts

Poles	A&B Tolerance
2P-8P	±0.15
9P-14P	±0.25
15P-20P	±0.35
21P-24P	±0.40



N=Number of contacts

P.C.B LAYOUT



SIGN	DATE	DESCRIPTION	APPROVER
△	01/18/07	Soldering temperature changed from 245° to 250°	Tason
△	01/18/07	Part NO is Changed	Tason

THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!!

Material:

- Item 1 Terminal housing :Thermoplastic (UL 94V-0)
- Item 2 Clamp : Brass ,Ni plated
- Item 3 Wire guard solder pin : Brass ,Tin plated
- Item 4 Terminal screw: Steel Zinc plating"-slot type

Electrical cULus

- Voltage rating: 300VAC
- Current rating: 10A
- Wire range:
- Solid wire(AWG): 12-24
- Stranded wire(AWG): 12-24
- Torque(Lb-In): 3.5
- Screw: M2.5
- Wire strip length: 6-7mm
- Withstanding Voltage: 1.6KV
- Operating temperature: -40°C to +115°C
- Soldering temperature: 250°C±10°C/5 Sec
- Safety Approval: cULus

△ YM xx 61 x 0 xxxx G

04 2×2 CONTACTS
06 2×3 CONTACTS
...
48 2×24 CONTACTS

0 Black
5 Green
6 Blue
8 Grey

0000:"@Logo (Standard) Pb < 40,000ppm (RoHS)
000A:"ANYTEK"Logo
Any special item by customer request, please contact sales department.

ANYTEK

CUSTOMER COPY

ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATSOEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD

TITLE		YM-5.08mm -R Series				PART NO.			
PART NO.		YMxx61x0xxxxG				DWG NO.		8YM0102	
APPROVED	CHECKED	DESIGNED	DRAWN	CUST NO.	Tolerance				
		Aaron 2009.11.30	Aaron 2009.11.30		UNIT: mm		X.	±0.50	
					SCALE: NONE		X.X	±0.30	
					REV: D		X.XX	±0.10	
					SHEET: 01/01		X°	±1°	