

ShockWatch® 2 Impact Indicators

ShockWatch® 2 impact indicators alert

reduce damage by 40-60%.



Reduce costs without sacrificing quality.

Shipping docks are busy places with everyone rushing to get product shipped or received on time. Loading and unloading creates opportunities for products to get dropped and damaged. Carriers, manufacturers, and receivers are all impacted by damage-related costs. Often the question becomes who is responsible for the damage

Damaged products benefit no one.

ShockWatch 2 indicators assist handlers in the supply chain refine their processes so

occurs. The goal of the ShockWatch program is to reduce damage related incidents and ultimately drive down costs.

ShockWatch 2 impact indicators indicate when products have been exposed to a potentially damaging impact during transit or in storage. ShockWatch devices are tamperproof, field-armable, mechanically-activated devices that turn bright red when an



ShockWatch 2 with ring label.



ShockWatch 2 shown with companion label.



ShockWatch 2 shown with companion label to accommodate the ring label.

Benefits

- Confirms effectiveness of packaging
- Helps identify trouble spots in supply chain, from production to transportation and storage
- Helps increase quality of product from dock to dock

SpotSee® Impact Indicator Technical Data

Selection Guide

Selecting the right indicator is a simple process. Start with your shipment size and weight. The selection guide provides a starting point for sensitivity selection. The indicator best suited to your application will also take into account product fragility and packaging. More fragile products may require a more sensitive (lower G) indicator while products with more robust packaging may need a less sensitive (higher G) indicator.

ShockWatch 2	5 - 15 ft³ 0.14-0.42m³	15 - 50 ft³ 0.42 - 1.42 m³	50 - 100 ft³ 1.42 - 2.83 m³	100 - 250 ft³ 2.83 - 7.08 m³	250 - 500 ft³ 7.08 - 14.16 m³	500 - 1,000 ft³ 14.16 - 304.8 m³	1,000+ ft³ 304.8+ m³
0 - 10 lbs 0 - 5 kg	75G	75G	50G	37G	---	---	---
10 - 25 lbs 5 - 11 kg	75G	50G	50G	37G	25G	---	---
25 - 50 lbs 11 - 23 kg	50G	50G	37G	25G	25G	15G	---
50 - 100 lbs 23 - 45 kg	50G	37G	37G	25G	15G	15G	10G
100 - 250 lbs 45 - 113 kg	37G	37G	25G	25G	15G	15G	10G
250 - 1,000 lbs 113 - 454 kg	37G	25G	25G	15G	15G	10G	10G
1,000 - 2,000 lbs 454 - 907 kg	25G	25G	25G	15G	15G	10G	5G
2,000 - 5,000 lbs 907 - 2,268 kg	25G	25G	15G	15G	10G	10G	5G
5,000 - 10,000 lbs 2,268 - 4,536 kg	25G	15G	15G	15G	10G	10G	5G
10,000 - 15,000 lbs 4,536 - 6,804 kg	---	15G	15G	10G	10G	5G	5G
15,000 - 20,000 lbs 6,804 - 9,072 kg	---	---	10G	10G	5G	5G	5G
20,000 - 30,000 lbs 9,072 - 13,608 kg	---	---	---	5G	5G	5G	5G
30,000+ lbs 13,608+ kg	---	---	---	---	5G	5G	5G

Key Specifications		Product Description	Part Number
Sensitivity range	5 - 75G	ShockWatch 2 - 5G	45000K
Impact duration	0.5 - 50ms	ShockWatch 2 - 10G	46000K
Tolerance	±15% a 20°C / 68°F, 1 ATM	ShockWatch 2 - 15G	47000K
Operating temperature	-25°C to 80°C / -13°F a 176°F	ShockWatch 2 - 25G	48000K
Dimensions	1.69in x 1.69in x 0.25in (42.93mm x 42.93mm x 6.35mm)	ShockWatch 2 - 37G	49000K
Security	Tamperproof, Serialized	ShockWatch 2 - 50G	50000K
Adhesive	Acrylic	ShockWatch 2 - 75G	51000K
Product Life	2 years when stored at 20°C/68°F, 1 ATM	Companion Label - 200/roll	26106
Storage recommendations	20°C/68°F, 1 ATM, 0%-99% RH Non-condensing	Companion Label - 500/roll	26107
Weight (varies by sensitivity)	~5.05g		