







2170753-2 AS SHOWN

- | | | | |
|-------|-------------|-------------|-------------|
| 23.0 | 1 | NETWORKING | 2170753-9 |
| 16.0 | 1 | SAN | 2170753-8 |
| 13.7 | 1 | PCI | 2170753-7 |
| 23.0 | 0 | NETWORKING | 2170753-6 |
| 16.0 | 0 | SAN | 2170753-5 |
| 13.7 | 0 | PCI | 2170753-4 |
| 23.0 | 2 | NETWORKING | 2170753-3 |
| 16.0 | 2 | SAN | 2170753-2 |
| 13.7 | 2 | PCI | 2170753-1 |
| DIM A | # REAR PINS | APPLICATION | PART NUMBER |


4805 (3/11)

LOC		DIST		REVISIONS			
P	LTR	DESCRIPTION			DATE	DWN	APVD
		- SEE SHEET 1			-	-	-


HEAT SINK OPTIONS



PCI HEAT SINK
SCALE 3:1




SAN HEAT SINK
SCALE 3:1




NETWORKING HEAT SINK
SCALE 3:1


OF REAR LEGS OPTIONS



2 REAR LEGS
SCALE 5:1







1 REAR LEG
SCALE 5:1



0 REAR LEG
SCALE 5:1

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN: JASON YANG 01APR2014		 TE Connectivity	
		CHK: SEAN HAN 30DEC2015			
DIMENSIONS:		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME: CAGE ASSEMBLY, QSP28 1X1, THRU BEZEL, WITH EMI GASKET HEAT SINK	
mm					
		PRODUCT SPEC: 108-19428			
		APPLICATION SPEC: 114-32023			
MATERIAL:		FINISH:		SIZE: A1	
-		-		CAGE CODE: 00779	
				DRAWING NO: C=2170753	
		WEIGHT: -		RESTRICTED TO: -	
		Customer Drawing		SCALE: 4:1	
				SHEET 2 OF 5	
				REV: A	

LOC		DIST		REVISIONS			
P	LTR	DESCRIPTION		DATE	DWN	APVD	
-	-	SEE SHEET 1		-	-	-	



THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN: JASON YANG 01APR2014	TE Connectivity
		CHK: SEAN HAN 30DEC2015	
DIMENSIONS:		PRODUCT SPEC	NAME: CAGE ASSEMBLY, QSP28 1X1, THRU BEZEL, WITH EMI GASKET HEAT SINK
mm		108-19428	
		APPLICATION SPEC	SIZE: CAGE CODE DRAWING NO. RESTRICTED TO
		114-32023	
MATERIAL		WEIGHT	A100779C=2170753
		Customer Drawing	
		SCALE: 4:1	SHEET 3 OF 5
		REV: A	




LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
		-		SEE SHEET 1	-	-	-

D

C


B

A



RECOMMENDED PCB LAYOUT
SINGLE TYPE OF 1 REAR HOLES OF LEGS
PCB TOLERANCE: ±0.05
SCALE 6:1

RECOMMENDED PCB LAYOUT
SINGLE TYPE OF 0 REAR HOLES OF LEGS
PCB TOLERANCE: ±0.05
SCALE 6:1



DETAIL B
SCALE 8:1

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN: JASON YANG 01APR2014	TE Connectivity	
DIMENSIONS:		CHK: SEAN HAN 30DEC2015		
mm	TOLERANCES UNLESS OTHERWISE SPECIFIED:	APVD: -	NAME	
0 PLC ±0.25	1 PLC ±0.25	PRODUCT SPEC	CAGE ASSEMBLY, QSP28 1X1, THRU BEZEL, WITH EMI GASKET HEAT SINK	
2 PLC ±0.20	3 PLC ±0.100	108-19428	SIZE	
4 PLC ±	ANGLES ±	APPLICATION SPEC	CAGE CODE DRAWING NO	
MATERIAL	FINISH	114-32023	A100779C=2170753	
-	-	WEIGHT	RESTRICTED TO	
-	-	Customer Drawing	SCALE 4:1 SHEET 4 OF 5 REV A	

D

C

B

A

