


DESCRIPTION: 2B // QUIK-LOQ // M // PANEL MOUNT // SOLDER CUP // NON-LATCH*



822BYYY-103R001

SERIES _____
POSITIONS _____
YYY = SEE POSITION CHART
GENDER _____
1 = MALE
TYPE _____
0 = SOLDER CUP PANEL MOUNT (NON-LATCH)
KEY ORIENTATION _____
3 = 1 KEY // 0°
CONTACT PLATING _____
1 = 7μ" GOLD PLATED

SPECIFICATIONS:

MATERIALS:
SHELL: NICKEL/CHROME PLATED BRASS
CONTACTS: 7u" GOLD PLATED BRASS
NUT: NICKEL/CHROME PLATED BRASS
INSULATOR: PPS (HIGH TEMPERATURE)

MECHANICAL:
MATING CYCLES: 5000 CYCLES
OPERATING TEMPERATURE: -40°C TO +200°C
PROCESS TEMPERATURE: 260°C FOR 5 SECONDS
SHIELDING: 75dB @ 10MHz // 40dB @ 1GHz
IP RATING: 50
MAX TORQUE: 4.5 Nm

POSITION CHART // ELECTRICAL/WIRE SPECIFICATIONS						
*solder side view of insulator						
POSITIONS	CONTACTS*	CONTACT Ø	MAX CONTACT mΩ	WORKING VOLTAGE	MAX AMPERAGE	MAX WIRE AWG
002		2.00mm	3.0 mΩ	700 V	25.0 A	16
003		1.60mm	4.0 mΩ	800 V	17.0 A	18
004		1.30mm	5.0 mΩ	615 V	15.0 A	20
006		1.30mm	5.0 mΩ	450 V	12.0 A	20
008		0.90mm	6.0 mΩ	500 V	10.0 A	22
010		0.90mm	6.0 mΩ	500 V	8.0 A	22
012		0.70mm	7.5 mΩ	480 V	7.0 A	24
014		0.70mm	7.5 mΩ	380 V	6.5 A	24
016		0.70mm	7.5 mΩ	315 V	6.0 A	24
019		0.70mm	7.5 mΩ	315 V	5.0 A	24
026		0.50mm	10.0 mΩ	315 V	2.0 A	28

*WILL NOT LATCH WITH NORCOMP 822B SERIES FEMALE CABLE MOUNT CONNECTORS DUE TO NO LATCH MECHANISM WITHIN CONNECTOR.

RoHS COMPLIANT



THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF NorComp AND SHALL NOT BE REPRODUCED, COPIED OR USED AS THE BASIS FOR THE MANUFACTURE OR SALE OF APPARATUS WITHOUT WRITTEN PERMISSION.

DRAWN:
M. SIGMON

DATE:
02/05/2016

UNITS = mm

DO NOT SCALE FROM DRAWING

NorComp

SCALE:
NTS

SHEET OF
1 1

REV
5

DWG NO.

822BYYY-103R001