







RECOMMENDED PCB LAYOUT



N = Number of poles
 Dim A = $N \times 5.0 + 2.0$
 Dim B = $(N - 1) \times 5.0$

Poles	Dim A	Dim B
2-6p	± 0.20	± 0.15
7-12p	± 0.25	± 0.20
13-18p	± 0.30	± 0.25
19-24p	± 0.35	± 0.30

SIGN	DATE	DESCRIPTION	APPROVER
△	8/16'06	Added VDE and TUV standard	Steady
△	8/16'06	Current rating (cULus) changed from 10A to 20A	Steady
△	1/19'07	Dimension changed from 4.0 to 3.5	Tony
△	1/19'07	Soldering temperature changed from 245° to 250°	Tony
△	12/17'08	Add the tolerance table	Jacke
△	2009.10.21	The material is changed from Brass to Copper	Jacke
△	2009.10.21	The operating temperature is changed	Jacke
△	2010.05.29	The design is changed	Jacke
△	2012.12.03	Update the drawing	Chen Bo

THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!!

Material:

- Item ⑥ Male contact pin: Copper Tin plated
- Item ① Terminal(housing): Thermoplastic (UL94 V-0)

- ① Electrical: cULus /VDE /TUV
- ② Voltage rating: 300V/300V/300V
- ② Current rating: 20A/20A/20A
- ① Withstanding Voltage: 1.6 KV/2.5KV/2.5KV
- ① Operating temperature: -40°C to +115°C
- ⑨ ④ Soldering temperature: 260°C±5°C/5 Sec
- ⑨ Safety Approval: cULus VDE TÜV
- ⑨ Critical dimension: △

OQ xx 7 1 x 1 xxxx G

No. OF POLES
 02: 2 POLES
 :
 24: 24 POLES

- G RoHS compliant (lead<4%)
- In copper Alloy
- 0000: "①" Logo (Standard)
- 000A: "ANYTEK" Mark
- Any special item by customer request, please contact sales department.
- 0 Black (RAL9005)
- 2 Red (RAL3001/D)
- 3 Orange(RAL2011/P)
- 4 Yellow(RAL1018/A)
- 5 Green(RAL6018/T)
- 6 Blue (RAL5015/A)
- 8 Grey(RAL7035/D)
- 9 White(RAL1102)
- C Green(RAL6018/U)

ANYTEK

CUSTOMER COPY

ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD

TITLE		OQ 5.0mm 90° /Close Series 2p-24p				
PART NO.	OQxx71x1xxxxG			DWG NO.	80Q0504	
APPROVED	CHECKED	DESIGNED	DRAWN	CUST NO.	Tolerance	
		Chen Bo 12/03`12	Chen Bo 12/03`12		UNIT: mm	X. ±0.50
					SCALE: NONE	X.X ±0.30
					SHEET: 01/01	REV.: J
					X° ±1°	