

Actuator

71-641.0



<https://eao.com/p/71-641.0>

Your product:



71-641.0 Actuator

OPERATING-/INDICATION PART

Lever material:	plastic
Lever shape:	short

ELECTRICAL CHARACTERISTICS

Recommended minimum operational data:	Voltage	5 VAC/DC		
	Current	10 mA		
Surge voltage resistance:	2500 VAC, 50 Hz, 1 minute, as per DIN / IEC 60512-2 between all terminals and earth			
Switching voltage and switching current:	Switch rating AC cosφ 0,7 ... 0,8 gemäss EN IEC 60947-5-1			
	Voltage	250 VAC		
	Current	3 A		
	Switch rating DC gemäss EN IEC 60947-5-1			
	Voltage	24 VDC	250 VDC	
	Current	3 A	0.5 A	

MECHANICAL CHARATERISTIC

Switching system:	Self-cleaning, double-break snap action switching system, 1 normally closed and 1 normally open contact per element.
Weight:	0.003 kg
Switching positions:	2 positions
Switching action:	Momentary - Rest
Tightening torque:	Fixing nut max. 0.5 Nm
Switching angle:	42° left
Mechanical lifetime:	100 000 cycles of operation

AMBIENT CONDITION

Storage temperature:	– 40 °C ... + 85 °C
Climate resistance:	Damp heat, steady: 56 days, + 40 °C/93 % relative humidity, according to EN IEC 60068-2-78
Operating temperature:	– 25 °C ... + 55 °C
Vibration resistance:	Max. 100 m / s ² from 10 Hz ... 500 Hz, (sinusoidal EN IEC 60068-2-6)
Shock resistance:	Max. 500 m/s ² , pulse width, 3-axis (sinusoidal EN IEC 60068-2-27)
IP Protection:	IP65 front side

CERTIFICATE

Conformities:	CE, UKCA, 2011 / 65 / EC (RoHS), 2014 / 35 / EU (LVD)
----------------------	---


OTHER

Hints:	Pitch of the front plate mounting holes must agree with the printed circuit board holes Ø 3.5 mm
---------------	--



Housing material:	Plastic, according to UL 94 V0
--------------------------	--------------------------------

Short Description:	Actuator, optional illuminative, short, Momentary - Rest
---------------------------	--

Dimension drawings:



Mounting cut-outs:



Wiring diagrams:



Switching positions:

