






SIGN	DATE	DESCRIPTION	APPROVER
△	05/28/11	Voltage rating is changed from 160 V to 300 V	Steven
△	05/28/11	Withstanding Voltage is changed from 1.32 Kv to 1.6 Kv	Steven
△	05/28/11	Add "cULus" Safety Approval logo	Steven
△	05/28/11	The dimension is added	Steven
THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!!			



Section Q-Q

2P ~ 6P Ribs on both sides,
7P ~ 24P No rib



Dimension

DIM.P	$(N-1) \times 3.81$
DIM.L	$N \times 3.81 + 0.39$

N=Number of poles

	TOL			
	2p-6p	7p-12p	13p-16p	17p-24p
Dim.P	±0.15	±0.20	±0.25	±0.30
Dim.L	±0.15	±0.25	±0.30	±0.40

Material:

- Item ④ Terminal lever: Thermoplastic (UL94V-0)
 - Item ⑤ Terminal top housing: Thermoplastic (UL94V-0)
 - Item ⑥ Female contact : PbZn Tin Plated.
 - Item ⑦ Spring clamp : Stainless steel
 - Item ⑧ Terminal down housing: Thermoplastic (UL94V-0)
- Electrical: cULus

- | | |
|---------------------------|--|
| ⚠ ● Voltage rating: | 300 V |
| ● Current rating: | 5.5 A |
| ● Wire range: | |
| ● Solid wire(AWG): | 16-24 |
| ● Stranded wire(AWG): | 16-24 |
| ● Wire strip length: | 9-10 mm |
| ⚠ ● Withstanding Voltage: | 1.6 KV |
| ● Operating temperature: | -40°C to +115°C |
| ⚠ ● Safety Approval: |  US |
| ● Critical dimension: |  |

KD xx 3 0 x 0 xxxx G

No. OF POLES

02: 2 POLES

24: 24 POLES

COLOR

0: BLACK

5: GREEN (RAL 6018/T)