



THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.




SEE SHEETS 2 AND 3
FOR ARTWORK DETAILS

FRONT VIEW

SHOWN W/O DUSTCAPS

NOTES:

1. SEE CURRENT CATALOG FOR PART NUMBER SUFFIXES TO INDICATE COLOR AND/OR PACKAGE QUANTITIES.
2. SEE CATALOG FOR COMPLETE LIST OF PARTS APPLICABLE FOR USE WITH THIS PRODUCT.
3. PART NUMBERS:
 - A. SEE SHEET 2 FOR METHOD A.
 - B. SEE SHEET 3 FOR METHOD A, PAIR FLIPPED.
4. THESE CASSETTES COMPLY WITH ANSI/TIA-568-C.0. SEE ANSI/TIA-568-C.0 FOR POLARITY DETAILS AND EXAMPLES OF BASIC LINK.
5. MATERIALS:
 - A. BOX AND LID: PLASTIC
 - B. ADAPTER: COMPOSITE PLASTIC
6. CASSETTE WEIGHT: 4.16oz [118g]
7. DIMENSIONS IN BRACKETS ARE METRIC.



TITLE		24 FIBER DUPLEX LC CASSETTE METHOD A AND METHOD A, PAIR FLIPPED	
		CUSTOMER DRAWING	
		ITEM REVISION NAME	10F113AB/00
		DATASET FILE NAME	10F113AB_DC/00A
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [mm]		.x : .03 [.8]	.xxx : .005 [.127]
		.xx : .01 [.25]	ANGLES : 5 °
THIRD ANGLE PROJECTION		MATERIAL:	
DRAWN BY SAT		DATE 10-01-12	
		CHK TMSE	
SCALE NONE		DRAWING NUMBER: 10F113AB-DC	
SHT 1 OF 3		SIZE A	


REV						DESCRIPTION		ECN	
R	10-01-12	SAT	TMSE			RELEASED TO PRODUCTION		10F113AB-DC	

2

1

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

24 FIBER DUPLEX LC CASSETTE - METHOD A	
PART NUMBER	DESCRIPTION
FC2Z0-24-10AS	24 FIBER 50/125um OM4 OPTIMIZED
FC2ZN-24-10AS	24 FIBER 50/125um OM4
FC2X0-24-10AS	24 FIBER 50/125um 10 GbE OM3 OPTIMIZED
FC2XN-24-10AS	24 FIBER 50/125um 10 GbE OM3
FC25N-24-10AS	24 FIBER 50/125um OM2
FC26N-24-10AS	24 FIBER 62.5/125um OM1
FC29N-24-10AS	24 FIBER 9/125um OS1




FIBER INPUT/OUTPUT CHANNELS

DUPLEX ADAPTER PORT IDENTIFICATION

METHOD A, SEE NOTE 4

METHOD A - FIBER LAYOUT

							TITLE 24 FIBER DUPLEX LC CASSETTE METHOD A CUSTOMER DRAWING					
							ITEM REVISION NAME 10F113AB/00			PANDUIT TM		
							DATASET FILE NAME 10F113AB_DC/00A					
							UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [mm] .x ± .03 [.8] .xxx ± .005 [.127] .xx ± .01 [.25] ANGLES ± 5 °  THIRD ANGLE PROJECTION			MATERIAL: SEE NOTES SHEET 1		
R	10-01-12	SAT	TMSE		RELEASED TO PRODUCTION	10F113AB-DC				DRAWING NUMBER: 10F113AB-DC		
REV	DATE	BY	CHK	APR	DESCRIPTION	ECN	DRAWN BY SAT	DATE 10-01-12	CHK TMSE	SCALE NONE	SHT 2 OF 3	SIZE A

2


1

2


1

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

24 FIBER DUPLEX LC CASSETTE - METHOD A, PAIR FLIPPED	
PART NUMBER	DESCRIPTION
FC2Z0-24-10AF	12 FIBER 50/125um OM4 OPTIMIZED
FC2ZN-24-10AF	12 FIBER 50/125um OM4
FC2X0-24-10AF	12 FIBER 50/125um 10 GbE OM3 OPTIMIZED
FC2XN-24-10AF	12 FIBER 50/125um 10 GbE OM3
FC25N-24-10AF	12 FIBER 50/125um OM2
FC26N-24-10AF	12 FIBER 62.5/125um OM1
FC29N-24-10AF	12 FIBER 9/125um OS1



METHOD A, PAIR FLIPPED - FIBER LAYOUT

							TITLE 24 FIBER DUPLEX LC CASSETTE METHOD A, PAIR FLIPPED CUSTOMER DRAWING					
							ITEM REVISION NAME 10F113AB/00			PANDUITTM		
							DATASET FILE NAME 10F113AB_DC/00A					
							UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN (mm) .x ± .03 (.8) .xxx ± .005 (.127) .xx ± .01 (.25) ANGLES ± 5 ° THIRD ANGLE PROJECTION			MATERIAL: SEE NOTES SHEET 1		
R	10-01-12	SAT	TMSE		RELEASED TO PRODUCTION	10F113AB-DC						
REV	DATE	BY	CHK	APR	DESCRIPTION	ECN	DRAWN BY SAT	DATE 10-01-12	CHK TMSE	SCALE NONE	SHT 3 OF 3	SIZE A

2

1