





N=Number of contacts

Dimension A&B

DIM A	(N+2)×9.5+2.0
DIM B	(N-1)×9.5

Dimension A&B	Tolerance
>6~30	±0.30
>30~120	±0.40
>120~400	±0.60

SIGN	DATE	DESCRIPTION	APPROVER
△	09.4.13	Current,,wire range,approval are changed	JODY
△	10/22'12	Change the screw plating specification	Jacky
△	10/22'12	Change the dimensional tolerance	Jacky
△	10/22'12	Add the dimensional label	Jacky
THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!!			

MATERIALS ELECTRICAL

RATED VOLTAGE & CURRENT:

300 V, 30A △

WITHSTAND VOLTAGE:

AC 2000 V/Min

INSULATION RESISTANCE:

1000 MΩ OR MORE AT DC 500 V

OPERATING TEMPERATURE RANG:

-40 °C ~+115 °C

SCREW TORQUE VALUE:

8.8 Lb-In.

WIRE RANGE:

10-22 AWG △

1) MOLDED PARTS:

Thermoplastic, UL 94 V-0 BLACK

2) TERMINAL:

BRASS, 0.8t, Tin PLATED

△ 3) TERMINAL SCREWS:

STEEL,M3.5

△ APPROVAL: C&US

Critical dimension: ∇

YK 515 xx 3 x x 00G

G:RoHS compliant(lead<4%)
in copper alloy

MARK

0: "@" MARK

1: "ANY" MARK

TERMINAL & SCREW PLATED

0: TERMINAL & SCREW: G/F

△ 1: TERMINAL: G/F, SCREW: Zinc

2: TERMINAL: Sn, SCREW: G/F

△ 3: TERMINAL: Sn, SCREW: Zinc

ANYTEK

CUSTOMER COPY

ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATSOEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD

TITLE	YK-515 With Flange Series								
PART NO.	YK515xx3xx00G				DWG NO.	8YK0002-515			
APPROVED	CHECKED	DESIGNED	DRAWN	CUST NO.				Tolerance	
		Jacky 2012.10.22	Jacky 2012.10.22					UNIT: mm	X. ±0.50
						SCALE: NONE	X.X ±0.30		
					SHEET: 01/01	REV.: D	X.XX ±0.10		
							X° ±1°		