





E T 04 0 2 x 3 xxxx G

- G RoHS compliant (lead<4%)

In copper Alloy

- 0000: "@" Logo (Standard)

000A: "ANYTEK" Mark

Any special item by
customer request.
please contact sales
department.

COLOR

- 0 Black (RAL9005)
- 2 Red (RAL3001/D)
- 3 Orange(RAL2011/P)
- 4 Yellow(RAL1018/A)
- 5 Green(RAL6018/T)
- 6 Blue (RAL5015/A)
- 8 Grey(RAL7035/D)

SIGN	DATE	DESCRIPTION	APPROVER
△	03/23'09	modify specification	Jacke
△	2009.09.18	The design is changed	Jacke
△	2009.12.25	The Material is changed from PhBz to Copper	Jacke
△	2010.05.26	The flange screw is changed from"- " type to"+/-"type	Jacke
△	2011.05.18	Add is cULus	Aaron
△	2012.09.07	Added TUV standard	Chen Bo
△	2012.12.03	Update the drawing	Chen Bo

THIS IS CAD DRAWING. DO NOT REVISE MANUALLY!!!

Material:

- Item ③ Terminal(housing): Thermoplastic (UL94 V-0)
- Item ④ Terminal(cover): Thermoplastic (UL94 V-0)
- Item ⑤ Clamp: Brass Ni plated
- ③ ● Item ⑥ Female contact : Copper. Tin plated
- Item ⑦ Wire guard: Stainless steel
- Item ⑧ Terminal Screw: Steel , zinc plating " * " slot type
- Item ⑨ Steel: Steel t=1.50mm zinc plated.
- Item ⑩ With flange Screw: Steel Zinc plating M3"+/-" slot type

 Electrical:

cULus TUV

TUV

- | | | |
|--------------------------|---|----------------------|
| ● Voltage rating: | 300 V | 800V |
| ● Current rating: | 32 A | 32A |
| ● Wire range: | | 0.2-6mm ² |
| ● Solid wire(AWG): | 8-24 | |
| ● Stranded wire(AWG): | 8-24 | |
| ● Torque: | 7 LB-In | 0.8N.m |
| ● Screw: | M3.5 | |
| ● Wire strip length: | 10-11 mm | |
| ● Withstanding Voltage: | 1.6KV | 6KV |
| ● Operating temperature: | -40°C to | +115°C |
| ● Safety Approval: |   | |
| ● Critical dimension: |  | |






ANYTEK

CUSTOMER COPY

ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD

TITLE		ET-7.62 4P W/Flange With handle Series							
PART NO.		ET0402x3xxxxG			DWG NO.		8ET0004		
APPROVED		CHECKED	DESIGNED	DRAWN	CUST NO.		Tolerance		
			Chen Bo 12/03 '12	Chen Bo 09/07 '12			UNIT: mm		X. ±0.50
							SCALE: NONE		X.X ±0.30
					SHEET: 01/01		REV. I		X.XX ±0.10
									X° ±1°