




SIGN	DATE	DESCRIPTION	APPROVER
△	01/30.07	Soldering temperature changed from 245° to 250°	Tason
△	01/30.07	Part NO is Changed	Tason
△	03/08.08	Dimension from 10.0mm to 10.16mm	Aaron
△	01/08.09	Terminal screw changed from M2.5 to M3.0	Kind
△	01/08.09	Safety Approval: cULus	Kind
THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!!			

- Material:
- Item 1 Terminal housing :Thermoplastic (UL 94V-0)
 - Item 2 Clamp : Brass , Ni plated
 - Item 3 Wire guard solder pin , Brass , Tin plated
 - Item 4 Terminal screw: Steel Zinc plating"-slot type
- Electrical
- Voltage rating: 300V
 - Current rating: 10A
 - Torque(Lb-In): 3.5
 - △ ● Screw: M3.0
 - Wrie range:
 - SOLID WIRE(AWG): 16-26
 - Stranded wire(AWG): 16-26
 - Wire strip length: 6-7mm
 - Withstanding Voltage:1.6kv
 - Operating temperature: -40°C to +115°C
 - △ ● Soldering reliability: 250°C±10°C/5 Sec
 - △ ● Safety Approval: cULus
- △ YSxx21x0xxxxG
- 04 2x2 CONTACTS 0 Black 0000:"@Logo (Standard) RoHS
 - 06 2x3 CONTACTS 5 Green 000A:"ANYTEK"Logo Pb<40,000ppm
 - 6 Blue Any special item by
 - 48 2x24 CONTACTS 8 Grey customer request,
 - please contact sales
 - department.

ANYTEK				CUSTOMER COPY ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD			
TITLE	YS-5.08 Series Stackable						
PART NO.	YSxx21x0xxxxG			DWG NO.	8YS0001		
APPROVED	CHECKED	DESIGNED	DRAWN	CUST NO.			Tolerance
		Kind 2009.01.08	Kind 2009.01.08		UNIT: mm		X. ±0.50
					SCALE: NONE		X.X ±0.30
				SHEET: 01/01	REV.: F		X.XX ±0.10
							X° ±1°