







SECTION P-P

N = Number of poles

Dim.A	$N \times 7.62$
Dim.B	$(N-1) \times 7.62$
Dim.C	$(N+1) \times 7.62$
Dim.D	$(N+2) \times 7.62$

Poles	Tolerance
3P	± 0.20
4P	

SIGN	DATE	DESCRIPTION	APPROVER
△			
△			
△			

THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!!

Material

- Item ① Terminal(housing) : PA66 (UL94V-0)
- Item ② Terminal(cover) : PA66 (UL94V-0) (ET 7.62)
- Item ③ Terminal screw : Steel Zinc plating " - " slot type (ET 7.62)
- Item ④ Clamp : Brass, Ni plated (ET 7.62)
- Item ⑤ Female contact : Copper, Tin plated
- Item ⑥ With flange Nut : Steel Zinc plating M3 (VC 7.62)
- Item ⑦ Steel : Steel t=1.50mm zinc plated.

Electrical

- Voltage rating: 600VAC
- Current rating: 41A
- Solid wire (AWG): 8-24
- Stranded wire(AWG): 8-24
- Torque: 9.0 Lb-In
- Screw: M3.5
- Wire strip length: 10-11mm
- Withstanding Voltage: 1.6KV
- Operating temperature: -40°C to $+115^{\circ}\text{C}$
- Safety Approval:
- Critical dimension:

KT xx 0 1 x 3 xxxx G

No. OF POLES
03: 3 POLES
04: 4 POLES

G: Pb<40000ppm

0000: "@" Logo (Standard)
000A: "ANYTEK" Mark

Any special item by customer request. please contact sales department.

COLOR

- 0 Black (RAL9005)
- 5 Green(RAL6018/T)
- 6 Blue (RAL5015/A)
- 8 Grey(RAL7035/D)
- C Green(RAL6018/U)

ANYTEK

CUSTOMER COPY

ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD

TITLE		KT 7.62 Series Flange With Nut (With handle) Only 3P & 4P					
PART NO.		KTxx01x3xxxxG		DWG NO.		8KT0017	
APPROVED	CHECKED	DESIGNED	DRAWN	CUST NO.		Tolerance	
		Aaron 2011.10.18	Aaron 2011.10.18			UNIT: mm	X. ±0.50
						SCALE: NONE	X.X ±0.30
				SHEET: 01/01		REV: B	X.XX ±0.10
						X° ±1°	