





APPROVED: _____
DATE: _____ TITLE: _____



RECOMMENDED PCB LAYOUT



SPECIFICATIONS:

Material: Insulator: Hi-temp thermoplastic, rated UL 94V-0
Insulator color: Black
Contacts: Phosphor Bronze
Plating: Gold flash over Nickel underplate overall
Electrical: Current rating: 1 Amp max.
Contact resistance: 20 mohms max.
Insulation resistance: 1,000 Mohms min.
Dielectric withstanding voltage: 500 VAC/DC for 1 minute
Temperature Rating: Operating temperature: -40°C to +105°C
Environmental: Lead free, RoHS compliant

Rev	AWO #	Description	Date	Appr
-		RELEASED	5/25/05	
A		REDRAWN	8/3/12	
B		REVISED DIM.	06/13/13	
C		UPDATE DRAWING	9/10/15	AV/RT

Positions: 04 thru 100
A = .050 [1,27] x No. of Positions per Row +.016 [0,40]
B = .050 [1,27] x No. of Spoces

UNLESS OTHERWISE SPECIFIED
ALL DIMENSIONS ARE INCHES [MM]
TOLERANCES: EXCEPT AS NOTED
INCHES Holes

.X ± .10 ØXX ± .10
.XX ± .020 ØXXX ± .015
.XXX ± .015 ØXXX ± .010

APPROVALS DATE

DRAWN SS 5/25/05

CHECKED

APPROVED

ADAM TECH

909 Railway Avenue, Union, NJ 07083
Phone: 908-687-5000 Fax: 908-687-5710

TITLE .050 x .100 DUAL ROW RECEPTACLE STRIP
LOW PROFILE

SIZE PART NO. HRS-2B-XX-GA REV. C
REF: S00019C SCALE: NTS SHEET 1 OF 1