


# Actuator

704.010.5



<https://eao.com/p/704.010.5>

Your product:

---



704.010.5  
Actuator

#### FRONT

<b>Front dimension:</b>	Ø 29 mm
<b>Front form:</b>	round
<b>Front bezel colour:</b>	Grey
<b>Front bezel material:</b>	Plastic

#### MOUNTING

<b>Design:</b>	raised
----------------	--------

#### OPERATING-/INDICATION PART

<b>Lens optics:</b>	transparent
<b>Lens shape:</b>	flush
<b>Lens material:</b>	Plastic
<b>Lens illumination:</b>	non illuminative
<b>Lens colour:</b>	Green

#### ELECTRICAL CHARACTERISTICS

<b>Standards:</b>	The switches comply with the "Standards for low-voltage switching devices" DIN EN 60947-1
-------------------	---

#### MECHANICAL CHARACTERISTIC

<b>Operating force:</b>	8 N
<b>Operating Travel:</b>	ca. 5.8 mm ± 0.2 mm
<b>Mechanical lifetime:</b>	≤3 Mio. cycles of operation

**Weight:** 0.04 kg

**Switching action:** Momentary

## AMBIENT CONDITION

**IP Protection:** IP65 front side

**Storage temperature:** - 40 °C ... + 85 °C

**Operating temperature:** - 40 °C ... + 55 °C

## OTHER

**Housing material:** Plastic


**Hints:** Frontring with protective cover to be mounted with a torque of 0.4 Nm onto actuator, Max. 3 switching elements can be clipped on

**Housing colour:** Grey

**Short Description:** Actuator, Ø 29 mm, flush, non illuminative, Green, Plastic, transparent, round, Grey, Plastic, Momentary


**max. number of switching elements:** 3

**Dimension drawings:**



A = Screw terminal

**Mounting cut-outs:**



A = Screw terminal

B = Push-in terminal (PIT)

C = Plug-in terminal 6.3 mm x 0.8 mm

D = Double plug-in terminal 6.3 mm x 0.8 mm

**Wiring diagrams:**

E---