

Test Plugs 4 mm System



Type

LAS N WS / LAS N WS Au

4mm stackable plug, nickel/ gold plated contact spring, screw terminal 0.5-1.5mm².

Pin diameter

4 mm (0.157")

PART NO. / Housing color

Nickel Plated

- 934100100
- 934100101
- 934100102
- 934100103
- 934100104
- 934100105
- 934100106
- 934100107
- 934100109

Gold Plated

- 934100700
- 934100701
- 934100702
- 934100703
- 934100704
- 934100705
- 934100706
- 934100707
- 934100709



BSB 20 K

4mm multi spring plug with cable gland, nickel plated brass, screw terminal max. 2.5mm².

4 mm (0.157")

- 930729100
- 930729101
- 930729102
- 930729103
- 930729104

Technical Data

Contact Type
Connection Type
Voltage Rating
Measurement Category (IEC61010)
Current Rating*
Contact Resistance

spring loaded pin
screw terminal max. 1.5mm²
30 VAC / 60 VDC
CAT I
24A
3 mOhm

Material Specifications

Plug
Contact Spring
Housing

nickel plated brass; gold plated brass
nickel pl. copper-beryllium; gold pl. copper-beryllium
Polyamide

Environmental Conditions

Temperature range

-15 °C to +70°C (5 to 158°F)

Flamability Rating

Housing

UL 94 V-2

spring loaded pin
screw terminal max. 2.5mm²
30 VAC / 60 VDC
CAT I
30A
3 mOhm



brass
nickel
PP

-25 °C to +100°C (-13 to 212°F)

UL 94 HB

Drawing

Measurements are shown in millimeters.
Multiply by 0.03937 to convert to inches.



* Please consider derating graph on page 80.