








N=NUMBER OF POLES

DIM	TOL			
	1P--6P	7P--12P	13P--16P	
Dim P	(N-1)×7.5	±0.15	±0.25	±0.35
Dim L	N×7.5+1.8	±0.15	±0.25	±0.35

P.C.B Layout
Top view

SIGN	DATE	DESCRIPTION	APPROVER
△	09/15`11	The color is changed from RAL7035/D to RAL7004/P	Runner
△	09/15`11	The dimension is changed from 2.1 to 2.2	Runner
△	09/15`11	The Material is changed	Runner
△	09/15`11	The tolerance is changed	Runner
△	09/25`13	change the dimension from 18.6&2.6 to 19.2&3.2	Da cheng
△	09/25`13	change the electrical specification	Da cheng

THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!!

Material:

- Item ① Terminal body: Thermoplastic (UL94V-0)
- Item ② Terminal side body: Thermoplastic (UL94V-0)
- Item ③ Terminal cover: Thermoplastic (UL94V-0)
- Item ④ Contact pin : Copper, Tin Plated.
- Item ⑤ Spring clamp : Stainless steel

- △ Electrical: cULus
- Voltage rating: 300 V
 - Current rating(Sol): 30 A
 - Current rating(Str): 35 A
 - Solid wire(AWG): 10-24
 - Stranded wire(AWG): 8-24
 - Wire strip length: 15-16 mm
 - Withstanding Voltage: 1.6KV
 - Operating temperature: -40°C to +120°C
 - Soldering temperature: 260°C±5°C/5 Sec
 - Safety Approval:
 - Critical dimension:

NK xx A 1 x 0 xxxx G

End Stackable
01: 1 POLES
02: 2 POLES
16: 16 POLES

- △ Body Color
- 0 Black (RAL9005)
 - 2 Red (RAL3001/D)
 - 3 Orange(RAL2011/P)
 - 4 Yellow(RAL1018/A)
 - 5 Green(RAL6018/T)
 - 6 Blue (RAL5015/A)
 - △8 Grey(RAL7004/P)
 - 9 White(RAL1102)
 - C Multiple colors

RoHS compliant
(lead<4%)
In copper Alloy
0000: "@" Logo (Standard)
000A: "ANYTEK" Mark
Any special item by
customer request
please contact sales
department.

ANYTEK

CUSTOMER COPY

ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD

TITLE	NK 7.5mm Series Right angle (Double tail A type)(平行脚)						
PART NO.	NKxxA1x0xxxxG			DWG NO.	8NK0003		
APPROVED	CHECKED	DESIGNED	DRAWN	CUST NO.			
		Da cheng 2013.09.25	Da cheng 2013.09.25		UNIT: mm	Tolerance	
					SCALE: NONE	X.	±0.50
				SHEET: 01/01	REV.: C	X.X	±0.30
						X.XX	±0.10
						X°	±1°