

Actuator

45-

2134.4F50.000

<https://eao.com/p/45-2134.4F50.000>

Your product:



45-2134.4F50.000
Actuator

FRONT

Front dimension:	Ø 38 mm
Front bezel colour:	Sand grey
Front bezel material:	Metal

MOUNTING

Design:	flush
----------------	-------

OPERATING-/INDICATION PART

Lens illumination:	non illuminative
Lens colour:	Green
Lens shape:	flush
Lens material:	Plastic
Lens optics:	opaque

MECHANICAL CHARACTERISTIC

Weight:	0.071 kg
Switching action:	Maintained
Switching system:	Slow-make switching element
Mechanical lifetime:	10 Mio. cycles of operation
Operating frequency:	Max. 1 800/h


AMBIENT CONDITION

Shock resistance:	According to IEC 60068-2-27: Sinusoidal half-wave 50 g / 11 ms
Vibration resistance:	According to IEC 60068-2-6: 20 ... 500 Hz: 5 g
IP front protection:	IP66, IP67, IP69K
Operating temperature:	- 25 °C ... + 70 °C
Storage temperature:	- 40 °C ... + 80 °C
Climate resistance:	During operation according to IEC 60721: 3K6, 3C3, 3S2, 3M6

OTHER

Housing colour:	Silver
Housing material:	Metal
Short Description:	Actuator, Ø 38 mm, flush, non illuminative, Green, Plastic, opaque, Sand grey, Metal, Maintained, IP66, IP67, IP69K
Hints:	Push to unlatch

Dimension drawings:



Wiring diagrams:

