





LOC	DIST	REVISIONS					
CM	00	P	LTR	DESCRIPTION	DATE	DWN	APVD
			A1	REVISED PER ECR-12-003555	19APR2012	RS	DD
			A2	REVISED PER ECR-12-016877	20OCT2012	RS	DD
			B	REVISED PER ECR-15-004054	28JUL2015	RS	DD
			C	REVISED PER ECR-15-017995	18DEC2015	RS	DD



2 POSITION
SHOWN AS SHIPPED



FOR 2, 3 AND
4 POSITIONS



FOR 1 POSITION
ONLY


- ① MATERIALS AND FINISH:
- HOUSING: LCP, COLOR: NATURAL
- CONTACTS: COPPER ALLOY, FINISH: Sn OVER Ni
2. COMPLY WITH DIRECTIVE 2002/95/EC (ROHS)
3. 18-24AWG SOLID OR STRANDED WIRE.
PLEASE REFER TO APPLICATION SPEC 114-13266
FOR RECOMMENDED STRAND COUNT.
- | | | | | |
|--------|-----|------------|----|------|
| 18 AWG | MAX | INSULATION | OD | 2.20 |
| 20 AWG | MAX | INSULATION | OD | 1.90 |
| 22 AWG | MAX | INSULATION | OD | 1.70 |
| 24 AWG | MAX | INSULATION | OD | 1.45 |

4. PACKAGE IN TAPE AND REEL PER EIA-481 SPECIFICATION

 WIRE SIZE MARKING IN APPROXIMATE LOCATION SHOWN.

 COLOR CODE MARKING, STRAIGHT LINE.

7 ONE POSITION ASSEMBLY DOES NOT COMPLY WITH EIA 481 SPECIFICATION.




2 POSITION
SHOWN CLOSED
SCALE 8:1


RED	17.70	24 AWG	4	3-2106751-4
	13.70	24 AWG	3	3-2106751-3
	9.70	24 AWG	2	3-2106751-2
	5.70	24 AWG	1	 3-2106751-1
GREEN	17.70	22 AWG	4	2-2106751-4
	13.70	22 AWG	3	2-2106751-3
	9.70	22 AWG	2	2-2106751-2
	5.70	22 AWG	1	 2-2106751-1
BLUE	17.70	20 AWG	4	1-2106751-4
	13.70	20 AWG	3	1-2106751-3
	9.70	20 AWG	2	1-2106751-2
	5.70	20 AWG	1	 1-2106751-1
YELLOW	17.70	18 AWG	4	2106751-4
	13.70	18 AWG	3	2106751-3
	9.70	18 AWG	2	2106751-2
	5.70	18 AWG	1	 2106751-1
COLOR CODE	DIM D	WIRE SIZE	POSN	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN 26AUG2009 WM VAN SCOY CHR 26AUG2009 O. OSAGIE		 TE Connectivity	
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ±. 1 PLC ±0.5 2 PLC ±0.13 3 PLC ±. 4 PLC ±. ANGLES ±. FINISH		NAME ASSEMBLY, IDC SSL CONNECTOR, THROUGH HOLE, PASS THRU	
		PRODUCT SPEC 108-2404 APPLICATION SPEC 114-13266		SIZE A2	
MATERIAL  -  -		WEIGHT -		CAGE CODE 00779	
		Customer Drawing		DRAWING NO C-2106751	
				RESTRICTED TO -	
				SCALE 8.1 SHEET 1 OF 3 REV C	


LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
			-	SEE SHEET 1	-	-	-




1 POSITION
RECOMMENDED
PCB LAYOUT
SCALE 8:1



3 POSITION
RECOMMENDED
PCB LAYOUT
SCALE 8:1



2 POSITION
RECOMMENDED
PCB LAYOUT
SCALE 8:1




4 POSITION
RECOMMENDED
PCB LAYOUT
SCALE 8:1

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN 26AUG2009 WM VAN SCYOC CHK 26AUG2009 O.OSAGIE	APVD -			
DIMENSIONS:		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME		
mm		0 PLC ± 1 PLC ±0.5 2 PLC ±0.13 3 PLC ± 4 PLC ±		ASSEMBLY, IDC SSL CONNECTOR, THROUGH HOLE, PASS THRU		
MATERIAL		FINISH		SIZE	CAGE CODE	DRAWING NO
material_2		finish_spec_2		A200779	C-2106751	RESTRICTED TO
				Customer Drawing		SCALE 8:1
				SHEET 1 OF 3		REV C


LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
			-	SEE SHEET 1	-	-	-

D




C

B



SECTION Y-Y




D

C

B

2106751-2 SHOWN IN POCKET TAPE

A

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN WM VAN SCYOC 26AUG2009	 TE Connectivity			
DIMENSIONS:		CHK O. OSAGIE 26AUG2009				
mm	TOLERANCES UNLESS OTHERWISE SPECIFIED:	APVD -	NAME ASSEMBLY, IDC SSL CONNECTOR, THROUGH HOLE, PASS THRU			
	0 PLC ± 1 PLC ±0.5 2 PLC ±0.13 3 PLC ± 4 PLC ± ANGLES ±	PRODUCT SPEC 108-2404				
MATERIAL	FINISH	APPLICATION SPEC 114-13266	SIZE A200779	CAGE CODE C-2106751	DRAWING NO	RESTRICTED TO
material_2	finish_spec_2	Customer Drawing	SCALE 8:1	SHEET 1	OF 3	REV C

A