



Section P-P



P.C.B LAYOUT

**4**  
 N = Number of poles  
 Dim A =  $N \times 11.0 + 2.0$   
 Dim B =  $(N - 1) \times 11.0$

Pol.	Tol.	Dim A&B
2-4p		$\pm 0.20$
5-11p		$\pm 0.30$
17-18p		$\pm 0.40$

SIGN	DATE	DESCRIPTION	APPROVER
<b>4</b>	10/14'09	Terminal screw plated is changed from Ni plated to Zinc plated	Aaron
<b>4</b>	05/28'11	Add the P.C.B LAYOUT	Tason
<b>4</b>	05/28'11	Critical dimension is changed.	Tason
<b>4</b>	05/28'11	The tolerance table is changed.	Tason
<b>4</b>	01/04'12	The design is changed.	Chen Bo
<b>4</b>	01/04'12	The Dimension 6.5 are added	Chen Bo
<b>4</b>	12/11'12	Update the drawing	Jacky

*THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!!*

MATERIALS ELECTRICAL  
 RATED VOLTAGE & CURRENT: 300 V, 30 A  
 WITHSTAND VOLTAGE: AC 2000 V/Min  
 INSULATION RESISTANCE: 1000 M $\Omega$  OR MORE AT DC 500 V  
 OPERATING TEMPERATURE RANG: -40 °C ~ +115 °C  
 SCREW TORQUE VALUE: 15 Kgf.cm  
 WIRE RANGE: 22 - 10AWG  
 1) BODY: THERMOPLASTICS, UL94-V0 BLACK  
 2) TERMINAL: BRASS, 0.8t, Tin PLATED  
 3) TERMINAL SCREWS WITH WASHER: STEEL, Zinc PLATED, M4.0 **4**

**4** Critical dimension: **4**  
 APPROVAL:

YK 701 xx 0 x x 00G  
 NO. OF POLES: 02: 2 POLES, 03: 3 POLES, 04: 4 POLES, ..., 18: 18 POLES  
 MARK: 0: "@ " MARK, 1: "ANY " MARK  
 G RoHS compliant (lead<4%) In copper Alloy  
 TERMINAL & SCREW PLATED: 0: TERMINAL & SCREW: G/F, 1: TERMINAL: G/F, SCREW: Zinc, 2: TERMINAL: Sn, SCREW: G/F, 3: TERMINAL: Sn, SCREW: Zinc

**ANYTEK**

**CUSTOMER COPY**

ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATSOEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD

TITLE		YK701 W/o flange and W/o cover SERIES				
PART NO.	YK701xx0xx00G	DWG NO.	8YK0002-701			
APPROVED	CHECKED	DESIGNED	DRAWN	CUST NO.	Tolerance	
			Jacky 2012.12.11		X. $\pm 0.50$ X.X $\pm 0.30$ X.XX $\pm 0.10$ X° $\pm 1^\circ$	
				SHEET: 01/01	REV.: E	