






POLE		2	3	4	5	6	7	8	9	10	11	12
A		10.12	13.93	17.74	21.55	25.36	29.17	32.98	36.79	40.60	44.41	48.22
B		3.81	7.62	11.43	15.24	19.05	22.86	26.67	30.48	34.29	38.10	41.91
Tol.	±0.10						±0.15					
POLE	13	14	15	16	17	18	19	20	21	22	23	24
A	52.03	55.84	59.65	63.46	67.27	71.08	74.89	78.70	82.51	86.32	90.13	93.94
B	45.72	49.53	53.34	57.15	60.96	64.77	68.58	72.39	76.20	80.01	83.82	87.63
Tol.	±0.20						±0.30					

SIGN	DATE	DESCRIPTION	APPROVER
△	10/26'10	Stranded Wire changed from 16-28 AWG to 16- 26 AWG.	Tason
△	10/26'10	Solid wire changed from 16-28 AWG to 16- 26 AWG.	Tason
△	02/22'11	Add the "cULus" Safety Approval	Tason
△	02/23'11	The Torque changed from 1.7 Lb-In to 2 Lb-In	Tason
THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!!			

Material:

- Item ③ Terminal housing: Thermoplastic (UL94V-0)
- Item ④ Terminal cover: Thermoplastic (UL94V-0)
- Item ⑤ Metal housing: Steel , Zinc plated
- Item ⑥ Terminal screw: Steel Zinc plating "- " slot type.
- Item ⑦ Solder pin: Brass,Tin plated.

Electrical:

- Voltage rating: 300V
- Current rating: 8A
- Wire range: 16-26
- Solid wire(AWG): 16-26
- Stranded wire(AWG): 16-26
- Torque: 2Lb-In. △
- Screw: M2
- Wire strip length: 8-9mm
- Withstanding Voltage: 1.6KV
- Operating temperature: -40°C to +115°C
- Soldering temperature: 250°C±10°C/5 Sec
- △ SAFETY APPROVAL DETA: cULus

TR xx 3 5 x 0 xxxx G

No. OF POLES
02: 2 POLES
:
24: 24 POLES

COLOR

- 0: BLACK
- 5: GREEN (RAL 6018/T)
- 6: BLUE
- 8: GREY (RAL 7004/P)

G: Pb<40000ppm

0000: "@" Logo (Standard)
000A: "ANYTEK" Mark

Any special item by
customer request.
please contact sales
department.

ANYTEK

CUSTOMER COPY

ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD

TITLE	TR 3.81mm 90D Series				
PART NO.	TRxx35x0xxxxG			DWG NO.	8TR0201
APPROVED	CHECKED	DESIGNED	DRAWN	CUST NO.	
		Tason 2011.02.22	Kind 2009.12.21		Tolerance
					UNIT: mm
					SCALE: NONE
				SHEET: 01/01	REV.: D