




Technical specification:

Rated voltage:	250 V
IEC 61076-2-101	
Current rating:	4 A at 40°C
IEC 61076-2-101	
Insulation resistance:	>=100 MΩ
IEC 60512	
Pollution degree:	3/2
IEC 60664-1	
Degree of protection:	IP 67, in mated condition
IEC 60529	
Temperature range:	-30°C ... +80°C
EN 60512-11-10	
EN 60512-11-4	-40°C ... +80°C
UL 2238	-30°C ... +65°C
Mating cycles:	>=100
IEC 60512-9a	

Materials:

Contact:	CuZn, Ni b / Au 0,2 gal.
Contact carrier:	PA, UL 94 HB transparent
Sealing:	FPM

Part no:	Description:	Pos	Construction:
43-01636	SAL - 12 - EST4 - P	4	without sealing
43-01681	SAL - 12 - ESTO4 - P	4	with sealing

DO NOT ALTER CAD DRAWING BY HAND	RoHS & REACH compliant	Index: c 11.06.15 fro Ä5678 UL adaptation				dim. in mm				title:	
				date		name				Panel plug M12x1 with dip solder	
				drawn		28.09.10		Franz			
				appd.		28.09.10		Mankopf		dwg no:	
		general tolerance:		0 ± 0,50mm 0,0 ± 0,25mm 0,00 ± 0,10mm ★ ± 1,5°						43K1A1195	
		THIS DRAWING MAY NOT BE COPIED OR REPRODUCED IN ANY WAY, AND MAY NOT BE PASSED ON TO A THIRD PARTY WITHOUT WRITTEN PERMISSION. OWNERSHIP AND COPYRIGHT OF CONEC GmbH		part no:							

general tolerance: 0 ± 0,50mm
0,0 ± 0,25mm
0,00 ± 0,10mm
± 1,5°

THIS DRAWING MAY NOT BE COPIED OR REPRODUCED IN ANY WAY, AND MAY NOT BE PASSED ON TO A THIRD PARTY WITHOUT WRITTEN PERMISSION. OWNERSHIP AND COPYRIGHT OF CONEC GmbH

CONEC®

Panel plug M12x1 with dip solder

43K1A1195