

E

D

C

B

A






E

D

C

B

A



Layout of Hook and Pillar:

2P	Hook+Pillar	△
3P	Hook+Hook+Pillar	△
4P	Hook+Pillar+Pillar+Pillar	△
5P	Hook+Pillar+Pillar+Hook+Pillar	
5P over	Hook+Pillar+Pillar+Pillar+Hook+Pillar	

DIM		TOL				
		2P	3P-6P	7P-12P	13P-18P	19P-24P
Dim L	N×5.0	±0.05	±0.15	±0.20	±0.30	±0.40
Dim P	(N-1)×5.0	±0.05	±0.15	±0.20	±0.30	±0.40
Dim B	N×5.0+1.6	±0.05	±0.15	±0.20	±0.30	±0.40

SIGN	DATE	DESCRIPTION	APPROVER
△	02/08'07	Part No. is changed.	Aaron
△	11/25'09	The Grey code changed from RAL7004/P to RAL7035/D	Kind
△	04/07'10	Add the 2P mark	Runner
△	06/30'10	Layout of Hook and Pillar is changed	Runner
△	05/07'11	The dimensions is Changed from 26.3 & 14.5 to 26.5 & 14.7	Chen Bo
△	08/22'12	Update the drawing	Da cheng

THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!!

Material

- Item 1 Female contact :PhBz Tin plated
- Item 2 Spring Clamp: Stainless steel
- Item 3 Terminal housing (With hook) :Thermoplastic (UL94V-0)
- Item 4 Terminal housing (With Pillar) :Thermoplastic (UL94V-0)
- Item 5 Terminal (cover):Thermoplastic (UL94V-0)

Electrical cULus

- Voltage rating:300V
- Current rating:15A
- Wire range:
 - Solid wire(AWG):12-28
 - Stranded wire(AWG):12-28
- Wire strip length: 8-9mm
- Withstanding Voltage:1.6KV
- Operating temperature:-40°C to +115°C
- Safety approval : cULus
- Critical dimension: △

HI xx 00 x 0 xxxx G △		RoHS compliant (lead<4%) △ In copper Alloy
No. OF POLES		
02: 2 POLES		
...		
24: 24 POLES		
	0 Black	0000: Standard
	5 Green(RAL6018/T)	Any special item by customer request.
	6 Blue	please contact sales department.
	△ 8 Grey(RAL7035/D)	

ANYTEK

CUSTOMER COPY

ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD

TITLE		HI -5.0 SERIES With hook and pillar			
PART NO.	HIxx00x0xxxxG			DWG NO.	8HI0001
APPROVED	CHECKED	DESIGNED	DRAWN	CUST NO.	
		Dacheng 2012.08.22	Dacheng 2012.08.22		
		SHEET: 01/01		UNIT: mm	Tolerance
				SCALE: NONE	X. ±0.50
					X.X ±0.30
					X.XX ±0.10
					X° ±1°