



	A	ECR-14-000387	10JAN2014	LW	PY
	A1	ECR-14-015136	10OCT2014	LW	PY
	A2	ECR-15-005723	13APR2015	KR	TD
	B	ECR-18-001422	26MAR2018	SG	SM



- 1 FLAT SEAL AND O-RING ASSEMBLED ON PIN HOUSING
- 2 NUT ENCLOSE LOOSELY
- 3 RECOMMENDED TIGHTENING TORQUE FOR NUT (ITEM NO.4)1.0-1.2Nm WHEN ASSEMBLING AT PANEL WALL
- 4 USE ONLY CRIMPING TOOL OF TE CONNECTIVITY TO CRIMP CONTACT.
 - A. CRIMPING TOOL PN 6-1579014-9 WILL BE USED FOR CRIMPING THE CONTACTS HAVING WIRE SIZE 2.5mm² and 4.0mm².
 - B. CRIMPING TOOL PN 6-1579014-8 WILL BE USED FOR CRIMPING THE CONTACTS HAVING WIRE SIZE 4.0mm² and 6.0mm².



THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:

mm

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ±

1 PLC ±0.3

2 PLC ±

3 PLC ±

4 PLC ±

ANGLES ±

FINISH

MATERIAL

-

DWN

CHRIS WANG

28MAR2013

CHK

DANIEL TAO

28MAR2013

APVD

PETER YIN

28MAR2013

PRODUCT SPEC

108-106122

APPLICATION SPEC

114-106122

WEIGHT

-

Customer Drawing

TE Connectivity

NAME

SOCKET CONNECTOR KITS

PV4 PANEL MOUNTED CONNECTOR

-

SIZE

A2

CAGE CODE

00779

DRAWING NO

1971920

RESTRICTED TO

-

SCALE

2:1

SHEET

1

OF

1

REV

B