




E

D


C

B

A



P.C.B. LAYOUT



Dimension

DIM A	$(N+1) \times 2.54$
DIM B	$(N-1) \times 2.54$

N=Number of poles

POLES	DIM A	DIM B
2p-8p	± 0.15	± 0.15
9p-12p	± 0.25	± 0.25
13p-18p	± 0.30	± 0.30
19p-24p	± 0.40	± 0.40

SIGN	DATE	DESCRIPTION	APPROVER
	01/20'07	The Soldering temperature from 245° to 250°	Aaron
	10/29'08	ADD Tolerance	Seamus

THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!!

Material

- Terminal body (Contact pin): Brass
- Wire guard: Stainless steel
- Surface of solder tail: Tin plated
- Insulator (housing): Thermoplastic (UL94V-0)

Electrical cULus

- Voltage rating: 150VAC
- Current rating: 2A
- Wire range:
- Solid wire(AWG): 20-26
- Stranded wire(AWG): 20-26
- Pull force:
- Screw:
- Wire strip length: 9-10mm
- Withstanding Voltage: 1.3KV
- Operating temperature: -40°C to +115°C
- Soldering temperature: 250°C $\pm$ 10°C/5 Sec
- Safety Approval:

HA xx 50 x 0 xxxx G

02	2 CONTACTS	2	Red	0000 Standard @ Logo
03	3 CONTACTS	3	Orange	000A Standard ANY Logo
...	...	5	Green(RAL6018/T)	Any special item by customer request, please contact sales department.
24	24 CONTACTS	8	Grey(RAL7004/P)	

G: Pb<40,000ppm

ANYTEK

CUSTOMER COPY

ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD

TITLE	HA-2.54mm 90° Series				DWG NO.	8HA0501	
PART NO.	HAxx50x0xxxxG				CUST NO.		
APPROVED	CHECKED	DESIGNED	DRAWN			Tolerance	
	Seamus 2008.10.29	Seamus 2008.10.29	Aaron 2007.01.20				X. ± 0.50
							X.X ± 0.30
							X.XX ± 0.10
							X° $\pm 1°$
				SHEET: 01/01		UNIT: mm	
						SCALE: NONE	
						REV: E	

1

2

3

4

5

6

7