

Actuator

704.060.2



<https://eao.com/p/704.060.2>

Your product:



704.060.2
Actuator

FRONT

Front bezel material:	Plastic
Front bezel colour:	Grey
Front form:	round
Front dimension:	Ø 29 mm

MOUNTING

Design:	raised
----------------	--------

OPERATING-/INDICATION PART

Lens colour:	Red
Lens material:	Plastic
Lens optics:	transparent
Lens illumination:	illuminative
Lens shape:	flush

ELECTRICAL CHARACTERISTICS

Standards:	The switches comply with the "Standards for low-voltage switching devices" DIN EN 60947-1
-------------------	---

MECHANICAL CHARACTERISTIC

Mechanical lifetime:	≤3 Mio. cycles of operation
Switching action:	Maintained
Terminal:	Screw terminal

Operating Travel:	ca. 5.8 mm \pm 0.2 mm
Weight:	0.056 kg
Operating force:	8 N


AMBIENT CONDITION

Operating temperature:	- 40 °C ... + 55 °C
IP Protection:	IP65 front side
Storage temperature:	- 40 °C ... + 85 °C

OTHER


Short Description:	Actuator, Ø 29 mm, flush, illuminative, Red, Plastic, transparent, round, Grey, Plastic, Maintained, Screw terminal
max. number of switching elements:	3
Housing material:	Plastic
Housing colour:	Grey
Hints:	Frontring with protective cover to be mounted with a torque of 0.4 Nm onto actuator, Max. 3 switching elements can be clipped on

Mounting cut-outs:



A = Screw terminal
 B = Push-in terminal (PIT)
 C = Plug-in terminal 6.3 mm x 0.8 mm
 D = Double plug-in terminal 6.3 mm x 0.8 mm

Dimension drawings:



A = Screw terminal

Wiring diagrams:

