







N=Number of contacts



2-6p	±0.20	±0.20
6-12p	±0.25	±0.25
12-24p	±0.40	±0.40

SIGN	DATE	DESCRIPTION	APPROVER
△	01/20'07	The Soldering temperature from 245° to 250°	Aaron
△	2010.08.12	The design is changed	Chen Bo
THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!!			

Material

- Terminal body (Contact pin): Brass
- Wire guard: Stainless steel
- Surface of solder tail: Tin plated
- Insulator (housing): Thermoplastic (UL94V-0)

Electrical cULus/VDE

- Voltage rating: 300VAC/250VAC
- Current rating: 10A/10A
- Wire range: 0.75-1.5mm²
- Solid wire(AWG): 14-24
- Stranded wire(AWG): 14-24
- Pull force:
- Screw:
- Wire strip length: 9-10mm
- Withstanding Voltage: 1.6KV/2KV
- Operating temperature: -40°C to +115°C
- Soldering temperature: 250°C±10°C/5 Sec △
- Safety Approval:



HA xx 30 x 0 xxxx G

02	2 CONTACTS	2	Red	0000: "@" Logo (Standard)
03	3 CONTACTS	3	Orange	000A: "ANYTEK" Mark
...	...	5	Green(RAL6018/T)	Any special item by customer request.
24	24 CONTACTS	8	Grey(RAL7004/P)	please contact sales department.

ANYTEK

CUSTOMER COPY

ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD

TITLE		HA-5.0mm 90°			DWG NO.			8HA0007	
PART NO.		HAxx30x0xxxxG			DWG NO.		8HA0007		
APPROVED	CHECKED	DESIGNED	DRAWN	CUST NO.			Tolerance		
			Chen Bo 2010.08.12		UNIT: mm		X.	±0.50	
					SCALE: NONE		X.X	±0.30	
				SHEET: 01/01	REV: F		X.XX	±0.10	
							X°	±1°	