

SIGN	DATE	DESCRIPTION	APPROVER
△			
THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!!			

Material:

- Item ① Terminal housing: Thermoplastic (UL94V-0)
- Item ② Terminal cover: Thermoplastic (UL94V-0)
- Item ③ Female contact : Copper. Tin plated
- Item ④ Wire guard : Stainless Steel
- Item ⑤ Clamp : Steel Stamping , Zinc plated
- Item ⑥ Terminal screw: Zinc plating"-slot type,M5

Electrical:

- Voltage rating: 600 V
- Current rating: 115 A
- Wire range:
- Solid wire(AWG): 2-20
- Stranded wire(AWG): 2-20
- Torque(Lb-In): 36.5
- Screw: M5
- Wire strip length: 19-20mm
- Withstanding Voltage: 2.2 KV
- Operating temperature: -40°C to +115°C
- APPROVAL:

KX xx C 1 x 0 xxxx G


No. OF POLES
02: 2 POLES
03: 3 POLES
:
10: 10 POLES

COLOR

0: BLACK
5: GREEN (RAL 6018/T)
6: BLUE
8: GREY (RAL 7035/D)

G: Pb<40000ppm
0000: "@" Logo (Standard)
000A: "ANYTEK" Mark
Any special item by
customer request.
please contact sales
department.

POLE	2	3	4	5	6	7	8	9	10
Dim.P	15.0	30.0	45.0	60.0	75.0	90.0	105.0	120.0	135.0
Tol.	±0.20			±0.35			±0.50		

ANYTEK				CUSTOMER COPY				
				ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD				
TITLE		KX 15.0mm Series (without flange) 2P-10P						
PART NO.		KXxxC1x0xxxxG		DWG NO.		8KX0006		
APPROVED		CHECKED	DESIGNED	DRAWN	CUST NO.		Tolerance	
			Runner 2011.04.25	Runner 2010.05.24			X. ±0.50	
					UNIT: mm		X.X ±0.30	
					SCALE: NONE		X.XX ±0.10	
					SHEET: 01/01		X° ±1°	
					REV: B			