

SIGN	DATE	DESCRIPTION	APPROVER
△	10/12/09	Add is cULus MARK	Aaron
THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!!			

Material:

- Item ① Terminal housing: Thermoplastic (UL94V-0)
- Item ② Clamp : Brass, Ni plated
- Item ③ Wire guard solder pin : Brass, Tin plated
- Item ④ Terminal Screw: "- " slot Steel zinc plated.
- Item ⑤ Terminal cover : Thermoplastic (UL94V-0)

Electrical: cULus

- Voltage rating: 300 V
- Current rating: 30 A
- Wire range:
- Solid wire(AWG): 10-26
- Stranded wire(AWG): 10-26
- Torque: 9 Lb-In
- Screw: M3.5
- Wire strip length: 7-8 mm
- Withstanding Voltage: 1.6KV
- Operating temperature: -40°C to +115°C
- Safety Approval: 

No. OF POLES
02: 2 POLES
:
06: 06 POLES



COLOR
0: BLACK
5: GREEN (RAL 6018/T)
6: BLUE
8: GREY (RAL 7004/P)

E 4 xx 0 1 x 0 xxxx G


G: Pb<40000ppm

0000: "@" Logo (Standard)
000A: "ANYTEK" Mark


Any special item by
customer request.
please contact sales
department.



SECTION B-B



SECTION A-A



POLE	2	3	4	6
A	20.00	31.00	38.00	52.00
B	11.00	18.00	32.00	
Tol.	±0.10	±0.15	±0.20	±0.30

ANYTEK

CUSTOMER COPY

ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD

TITLE	E4 Series							
PART NO.	E4xx01x0xxxxG				DWG NO.	8E40001		
APPROVED	CHECKED	DESIGNED	DRAWN	CUST NO.			Tolerance	
		Aaron 2009.10.12	Aaron 2009.10.12				UNIT: mm	X. ±0.50
					SCALE: NONE		X.X ±0.30	
					SHEET: 01/01		X.XX ±0.10	
					REV: C		X° ±1°	