




P.C.B. LAYOUT
TOP VIEW

N = Number of poles
Dim L = N x 3.5
Dim P = (N - 1) x 3.5

	Dim L	Dim P
2-6p	±0.15	±0.10
7-12p	±0.20	±0.20
13-18p	±0.30	±0.25
19-24p	±0.35	±0.30

SIGN	DATE	DESCRIPTION	APPROVER
△	04.19.10	Add the tolerance table	Tason

Material

- Item (a) Terminal body (metal housing): Brass (CuZn), Tin plated
- Item (b) Terminal screw: Steel Zinc plating "-" slot type
- Item (c) Wire guard: stainless steel
- Item (d) Insulator (housing): Thermoplastic (UL94V-0)

Electrical UL

- Voltage rating: 125V
- Current rating: 10A
- Wire range:
- Solid wire (AWG): 16-26
- Stranded wire (AWG): 16-26
- Torque: 1.7Lb-In
- Screw: M2
- Wire strip length: 5-6mm
- Withstanding Voltage: 1.25KV
- Operating temperature: -40°C to +115°C
- Soldering temperature: 260°C ± 5°C / 5 Sec
- Safety Approval:
- Critical dimension:

TE xx 0 1 x x xxxx G

RoHS compliant
(lead < 4%)
In copper Alloy

POLES	Color	DIM A Length	000 0 @ logo
02 02 POLES	0 Black (RAL9005)	0 4.4mm	000 A ANY logo
03 03 POLES	2 Red (RAL3001/D)	1 3.8mm	Any special item by
...	3 Orange (RAL2011/P)	2 3.5mm	customer request,
24 24 POLES	4 Yellow (RAL1018/A)		please contact sales
	5 Green (RAL6018/T)		department.
	6 Blue (RAL5015/A)		
	8 Grey (RAL7035/D)		
	C Green (RAL6018/U)		

ANYTEK

CUSTOMER COPY

ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD

TITLE	TE 3.5mm series "-"						
PART NO.	TExx01xxxxxG			DWG NO.	8TE0002		
APPROVED	CHECKED	DESIGNED	DRAWN	CUST NO.			Tolerance
		Guoxue 2014.04.01	Guoxue 2014.04.01				UNIT: mm
						SCALE: NONE	X.X ±0.30
				SHEET: 01/01		REV.: C	X.XX ±0.10
							X° ±1°