




Dimension

Dim A= N×3.81
Dim B= (N-1)×3.81

N = Number of poles

Poles	TOLERANCE
2P-5P	±0.15
6P-12P	±0.30
13P-24P	±0.40



SIGN	DATE	DESCRIPTION	APPROVER
	01/26'07	Soldering temperature changed from 245° to 250°	Tason
	01/26'07	Part NO is Changed	Tason
	9/01'08	增加公差标注	Seamus
	9/01'08	Operating temperature changed from -30°C/+105°C to -40°C/+115°C	Seamus
	12/08'10	Add is " TUV "	Aaron
THIS IS CAD DRAWING, DO NOT REVISE MANUALLY Y!!!			

Material:

- Item 1 Terminal housing :Thermoplastic (UL 94V-0)
- Item 2 Clamp : Brass,Ni plated
- Item 3 Wire guard solder pin : Brass,Tin plated
- Item 4 Terminal screw: Steel Zinc plating"-slot type

Electrical cULus / TUV

- Voltage rating: 300V / 300V
- Current rating: 10A / 12A
- Wire range: 0.2~1.5mm²
- Solid wire(AWG): 16-24
- Stranded wire(AWG): 16-24
- Torque: 1.7 Lb.in / 0.2Nm (stackable type: 1.5Kgf cm)
- Screw: M2
- Wire strip length: 5-6mm
- Withstanding Voltage: 1.6KV / 1.25KV
- Operating temperature: -40°C to +115°C
- Soldering temperature: 250°C±10°C/5 Sec
- Safety Approval:

YO xx 21 x 0 xxxx G

			RoHS
			Pb<40,000ppm
No. of poles	0 Black (RAL9005)	0000 Standard @ Logo	
02 2 CONTACTS	5 Green(RAL6018/T)	000A Standard ANY Logo	
03 3 CONTACTS	6 Blue (RAL5015/A)	Any special item by	
... ..	8 Grey(RAL7035/D)	customer request,	
24 24 CONTACTS	C Green(RAL6018/U)	please contact sales	
		department.	

ANYTEK

CUSTOMER COPY

ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD

TITLE		YO 3.81 Series 2p-24p					
PART NO.		YOxx21x0xxxxG		DWG NO.	8Y00101		
APPROVED	CHECKED	DESIGNED	DRAWN	CUST NO.		Tolerance	
			Chen Bo 2011.04.02			UNIT: mm	X. ±0.50
						SCALE: NONE	X.X ±0.30
				SHEET: 01/01		REV.: G	X.XX ±0.10
							X° ±1°